



MS340

Long Range CCD Scanner

Unitech's latest MS340 long range CCD scanner, has been enhanced to provide reliable scanning for rugged applications in field service, industrial production, warehouse and retail. Featuring industrial and military-standards, this affordable handheld scanner delivers unparalleled performance in harsh environments.

Great way of designing

The comfortable and ergonomic design of this scanner makes it easy to operate. MS340 is flexible to operate in multiple scan types: handheld mode and presentation mode. Whether it's picked up once an hour or used consistently for an entire shift, the MS340's compact and lightweight form factor will prevent user-fatigue and simplify scan-intensive applications.

With upgraded features that MS340 offers a long range scanning capability to improve operator efficiency, it can be used in most practical way depending on the scanning task from retail point-of sale to transportation surroundings.

Superior data capture performance

The MS340 is equipped with advanced scanning technology that provides a superior data capture performance to boost the scan speed up to 500 scans per second for incredible responsiveness.

The MS340 is easy to operate in dual modes: trigger mode and presentation mode. This scanner can be used in the most practical way depending on the scanning task. For added flexibility a hands-free stand for the MS340 is also available.

The MS340 also supports maximum compatibility by reading major 1D barcode types including UPC, EAN and GS1 DataBar, as well as damaged or poorly printed bar codes.

Rugged, reliable and affordable.

This barcode scanner is available in three different interface options; USB, keyboard wedge and RS232. The interface cables are easily interchangeable, making it suitable for a wide variety of computer systems. Easy plug-and-play installation means your team will be up and running in no time. Featuring an IP42 environmental sealing against moisture and dust and an impressive 1.5M drop specification to concrete, this scanner is built for durability into business workforce. The MS340 scanner is a cost effective and reliable scanner.

"The affordable MS340 is a high-performance CCD scanner with automatic smart detection, ideal for convenient in-stand counter scanning"

Features:

- Superior data capture performance: up to 500 scans/sec
- Compact, lightweight and ergonomic design with industrial standards
- Versatile scanning modes: supports both manual and presentation scanning (easy reading with auto smart detection)
- High-performance CCD engine: supports major 1D barcode types
- Supported by Unitech Scanner Configuration Management: easy to setup and clone your preferred settings to multiple devices
- Multi-interface communication : USB, K/W and RS232



v1.MS340

Specifications

Operational & Performance

Receiving Device	Linear CCD
Light Source	Linear CCD Sensor
Ambient light	635nm Red LED
Processor type	Up to 100,000 Lux
Max. Resolution	ARM Cortex™-M3, 32-bit
Scan Rate	4mil/0.1mm@PCS90%, Code39
Skew Angle	Smart detection
Pitch Angle	(up to 500 scans per second)
Printing Contrast Scale	± 60°(±5°)
Depth of Field	±10°~65°(±5°)
	30%
	Up to 400 mm@20mil/0.5mm
	PCS90%, Code39

Reading distance

Density	Near	Far
0.1mm / 4mil	80mm	120mm
0.127mm / 5mil	70mm	140mm
0.15mm / 6mil	60mm	170mm
0.26mm / 10mil	40mm	220mm
0.33mm / 13mil	40mm	330mm
0.39mm / 15mil	40mm	370mm
0.5mm / 20mil	40mm	400mm

Symbologies

All UPC/EAN/JAN, EAN128 Code, Code 39, Code 39 Full ASCII Code32 / Italian Pharmacy, Code 128, CODABAR/NW7 Interleave 25, Industrial 25, Matrix 25, MSI/PLESSEY, Telepen Code 93, Code 11, China Postage, Code 26, LCD25, GS1 DataBar.

Operation modes

Handheld / Presentation Mode and more.

Power Source

Operating voltage	DC 5V ± 5%
Consumption	Operation mode: <150mA
	Standby mode: <60mA

Enclosure

Scanner dimension	72mm x 70.3mm x 164 mm
Scanner weight	173.5g
Switch life	1 million times

Environmental

Operating temperature	0°C to 50°C
Storage temperature	-20°C to 70°C
Humidity	20%-95% non-condensing
Drop resistance	1.5 m
IP rate	IP42

Connectivity

KBW / RS232 / USB

Accessories

Hand-free stand (optional)
Interface cables

Regulatory approvals

CE, FCC, BSMI, VCCI



Unitech Europe

Tilburg, The Netherlands

• Tel.: +31 (0)13 460 9292

• Email: Info@eu.ute.com

• Website: <http://www.eu.ute.com>



unitech
because we care

Unitech America

Unitech Asia Pacific

Unitech China

Unitech Europe

Unitech Japan

Unitech Taiwan