


N 70
B57CR23N0B
SINGLE OVEN



A⁺



Included accessories

2 x combination grid, 1 x universal pan

Optional accessories

Z11SZ80X0 SeamlessCombination 60 + 29cm
Z11SZ90X0 SeamlessCombination 60 + 45cm
Z18C60X0 Cookbook

Built-in oven with SLIDE&HIDE[®] - unrestricted access to the oven interior

- ✓ Slide&Hide[®] - unrestricted access in the oven interior and easy handling due to rotating handle
- ✓ CircoTherm[®] - the unique hot air-system for simultaneous baking and roasting on up to 3 levels
- ✓ Self-cleaning Pyrolytic interior
- ✓ Dual cleaning options:
- ✓ Pyrolytic following heavy use - just let the oven interior clean itself.
- ✓ EasyClean[®] - the quick and easy option for day to day maintenance.
- ✓ Shift Control - fast navigation through menus and simple operation with the TFT display.
- ✓ TFT display - the high-resolution display takes you straight to the programme of your choice.

Features

Technical Data

Color / Material Front : Stainless steel
Construction type : Built-in
Integrated Cleaning system : Hydrolytic, Pyrolytic
Required niche size for installation (HxWxD) : 585-595 x 560-568 x 550
Dimensions of the product (mm) : 595 x 596 x 548
Dimensions of the packed product (HxWxD) (mm) : 675 x 690 x 660
Control Panel Material : Stainless steel
Door Material : Glass
Net weight (kg) : 40.5
Usable volume of cavity (l) : 71
Cooking method : , Bottom heat, Bread Baking Setting, Conventional heat, Dough proving setting, Full width grill, Half width grill, Hot Air, Hot Air-Eco, Hot air grilling, low temperature cooking, Pizza setting
First cavity material : Enamelled
Temperature control : electronic
Number of interior lights : 1
Approval certificates : CE, VDE
Length of electrical supply cord (cm) : 120
EAN code : 4242004192947
Number of cavities (2010/30/EC) : 1
Energy efficiency class (2010/30/EC) : A+
Energy consumption per cycle conventional (2010/30/EC) : 0.87
Energy consumption per cycle forced air convection (2010/30/EC) : 0.69
Energy efficiency index (2010/30/EC) : 81.2
Electrical connection rating (W) : 2990
Current (A) : 13
Voltage (V) : 220-240
Frequency (Hz) : 50; 60
Plug type : no plug



N 70
B57CR23N0B
SINGLE OVEN

Features

Design

- 2.5" TFT colour display
- Illuminated Shift Control
- Cavity inner surface: Enamel anthracite
- Slide&Hide® with fixed handle, SoftOpen
- Slide&Hide® with rotating handle

Features

- Control panel lock
- Automatic safety switch off
- Residual heat indicator
- Start button
- Door contact switch
- Temperature proposal
- Actual temperature display
- Heating up indicator
- Sabbath setting
- Interior halogen light
- Quadruple glazed door

Cleaning

- Pyrolytic cleaning
- EasyClean
- Full glass inner door

Programmes/functions

- 12 heating methods: CircoTherm®, CircoTherm® Gentle, Top/bottom heat, Conventional heat Gentle, Hot air grilling, Full surface grill, Centre surface grill, CircoTherm® intensive, Bread baking, Bottom heat, Low temperature cooking, Dough proving
- Rapid heat
- Cooling fan

Accessories

- 1 level telescopic shelf, full extension, Stop function
- 2 x combination grid, 1 x universal pan

Performance/technical information

- Energy efficiency rating (acc. EU Nr. 65/2014): A+
- Energy consumption per cycle in conventional mode: 0.87 kWh
- Energy consumption per cycle in fan-forced convection mode: 0.69 kWh
- Number of cavities: Main cavity
- Heat source: electrical
- Cavity volume: 71 litre
- Total connected load electric: 2.99 KW
- Temperature range 40 °C - 275 °C
- Length of mains cable: 120 cm
- Nominal voltage: 220 - 240 V
- Appliance dimension (hxwxd): 595 mm x 596 mm x 548 mm
- Niche dimension (hxwxd): 585 mm - 595 mm x 560 mm - 568 mm x 550 mm
- Please refer to the dimensions provided in the installation manual