

LG MONITORS

34UM88C

34" 21:9 UltraWide® QHD IPS Monitor

34"

* Class size: See below for details.

21:9 QHD IPS
sRGB over 99% / Color Calibrated
Screen Split 2.0 (PIP Mode) / Dual Link-up / Dual Controller
USB QuickCharge
Game Mode/ Black Stabilizer/ Dynamic Action Sync
On-Screen Control / Dark Room Mode / My Display Presets
Height / Tilt Adjustable Stand


PANEL	
Screen Size	34"
Panel Type	IPS
Color Gamut (CIE 1931)	sRGB over 99%
Color Depth (Number of Colors)	10bits (8bit+FRC), 1,07B
Pixel Pitch (mm)	0.2325 mm x 0.2325 mm
Response Time	5ms GTG
Refresh Rate	75Hz
Aspect Ratio	21:9
Resolution	3440 x 1440
Brightness	300 cd/m ²
Contrast Ratio	5M:1
Viewing Angle	178 / 178
Surface Treatment	Hard coating (3H), Anti-glare
INPUT/OUTPUT	
HDMI (ver 2.0)	2
DisplayPort (ver 1.2)	1
USB Up-Stream (ver 3.0)	1
USB Down-Stream (ver 3.0)	2 (Port 1 Supports Quick Charge)
POWER	
Type	Adapter
Input	100 ~ 240V
Normal On (EPA 6.0)	56.73W
SPECIAL FEATURES	
Picture Mode	Yes
Ratio	Wide, Original, Cinema 1, Cinema 2, 1:1
PIP	in Screen Split
PBP	Yes
DDC/CI	Yes
HDCP	Yes
Key Lock	Yes
Response Time Control	Yes
Freesync	Yes (DP 48-75Hz)
Game Mode	Yes
DAS Mode	Yes
Black Stabilizer	Yes
Flicker Safe	Yes
Smart Energy saving	Yes
Automatic standby	Yes
Reader Mode	Yes (included in Picture Mode)
Six Axis Control	Yes

Color Calibrated	Yes
H/W Calibration (True Color Finder)	Yes
Dual controller	Yes
Screen Split 2.0 (in OSC)	Yes
My Display Preset (in OSC)	Yes
On-Screen Control (OSC)	Yes
Dual EDID (H/W)	Yes
Tilt (Angle)	-5-20 Degree
Height (Range)	120mm
Audio Output	MaxxAudio 7Wx2
DIMENSIONS/WEIGHT	
Without Stand (WxHxD)	32.7" x 15" x 1.9"
With Stand (WxHxD)	(Down) 32.7" x 16.9" x 9.4" (Up) 32.7" x 21.6" x 9.4"
Shipping Dimensions (WxHxD)	38.5" x 20.6" x 8.2"
With Stand Weight	18.5 lbs
Shipping Weight	25 lbs
CABINET / ACCESSORIES	
VESA size (mm)	100 x 100
Power Cord	Yes
HDMI	Yes
DisplayPort	Yes
Cable holder	Yes
STANDARD	
UL (cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes
CCC (for China)	Yes
BSMI (for Taiwan)	Yes
EPA 6.0	Yes
ErP	Yes
EPEAT Gold	Yes
Windows	Yes
DisplayPort	Yes
LIMITED WARRANTY / UPC	
Limited Warranty	1 Year Parts and Labor
UPC	719192199828
Country of Origin	China