

# Cybernet Rugged X10

## Industrial Windows Tablet



### Rugged All Day Performance

The Rugged X10 is powered by two hot swap batteries meaning you never need to plug the unit in to charge. Simply swap out depleted batteries with fresh ones on the fly for all-day operability. An optional battery charging station can charge up to 6 batteries at a time.

### Industrial Grade Certified



#### Drop Tested

The Rugged X10 has been drop tested to meet MIL-STD-810G standards for surviving drops of up to 5 feet, making this ideal for the field or manufacturing floor.



#### IP65 Rated

This unit features an IP65 rated sealed front bezel. This protects the unit from both dust ingress and water ingress, protecting internal components.



#### Rated for Extreme Temperatures

The Rugged X10 is rated for extreme temperatures and can operate in conditions ranging from 0°C (32°F) to 40°C (104°F).

## Extreme Integration



- An optional 2D barcode scanner with a push button trigger built into the handle can be used to track assets and manage your warehouse.
- Optional integrated smart card, biometric, and RFID readers provide countless use case applications.
- Built-In 4G/3G connectivity allows you to stay connected in the field - no matter how remote.

## Engineered for Versatility

Expand the functionality of the Rugged X10 with an array of accessories. Two different mounting docks allow for a variety options. Connect to a monitor and keyboard to convert to a desktop option and use the additional ports to connect to legacy devices.



## Built with Customization & Compatibility in Mind

- Windows 7, 8, and 10
- Intel Core i5/i7 Processor with vPro
- Optional 4G/3G LTE Mobile Broadband
- 128GB Storage (Up To 256GB)
- 1 x USB 2.0, DC-In Jack, and Audio Jack
- Dual Lithium-Ion Hot Swap Batteries
- 1 x 8GB DDR3L SO-DIMM (Up to 16GB)
- 2 MP Front Webcam, 5MP Rear Webcam
- Desktop or VESA Docking Station Adds:
- 2 x USB 2.0, 1 x HDMI, 1 x RS232/422/485t, 1 x 1Gb LAN