



Intensifier IP® Full HD 1080p Vandal Resistant Corner Mount IP Camera

O2i607CM 2.9mm fixed lens, stainless steel housing

Features

- See color in low light without IR LEDs
- Supports up to Full HD resolution @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- No problems caused by objects that reflect or absorb IR light sources
- Presets: Outdoor, Indoor, Elevator, Lobby, Hallway & Low Light
- Attached cable (16 ft.) connects camera unit to main unit for flexible placement
- Wide dynamic range (WDR) operation
- Perfect for use in elevators
- Supports H.264 and MJPEG codecs
- 2-way audio communication
- Micro SD card slot (card not included)
- Sensor input and relay output
- Conformant with ONVIF Profile S
- 2 year warranty



Camera Specifications

Image Sensor.....Progressive scan 1/3" CMOS, 2MP
 Maximum Resolution1920 x 1080
 Minimum IlluminationF1.2, Color: 0.001 lux (Max Intensify)
 White Balance.....ATW, Manual, Push
 Intensify.....Selectable / Off
 Exposure ControlYes
 De-FogYes
 Backlight.....WDR, BLC
 DNR.....3D (0-20)

Video Specifications

Main Resolution1920x1080 @ 30fps
 Compression.....H.264 (HP/MP/BP), MJPEG
 Bitrate ControlVBR, CBR
 Multiple Streaming5 profiles

Audio Specifications

Mono Input64Kbps G.711 / 32Kbps G.726
 Mono Output64Kbps G.711

External Terminal Specifications

Ethernet.....10/100 Mbps
 Alarm.....1 sensor input, 1 relay output
 Audio1 mic in, 1 line out
 PowerDC jack
 Storage.....Micro SD slot

Network Specifications

ProtocolsIPv4, TCP, UDP, RTP, RTSP, HTTP, HTTPS,
 SMTP, FTP, DHCP, UPnP, DNS
 DDNS support.....Speco DDNS (free of charge)

Network Specifications (continued)

SecurityUser ID & Password protection, IP address filtering,
 digest authentication, user access log
 User Access8 simultaneous users at D1 resolution
 Number of users may vary depending on resolution

System Specifications

PoE.....Standard (IEEE 802.3af)
 Analytics.....Motion detection (3 regions), audio detection
 Alarm Triggers.....Analytics & sensor input
 Alarm Events.....FTP video file upload, email image upload,
 micro SD card recording, relay out
 Video Buffer.....Configurable pre-record & post-record
 Image SettingsPrivacy mask

Client Specifications

Web Browser Support.....Windows (Internet Explorer 8 and up)
 PC Application.....SecureGuard®

Operating & Unit Specifications

Power SupplyPoE, 12VDC (power supply not included)
 Power Consumption.....6W
 Operating Temperature...14° F – 122° F
 Operating Humidity8% - 80% RH
 Unit Dimensions.....5.1" (W) x 3.3" (H)
 Unit Weight.....1.5 lbs.
 CertificationsFCC, RoHS
 Included in Package.....Unit, CD (manual, software), mounting screws

Optional Accessories



O2MTOH
Outdoor Housing
for Encoder Box



POEINJ
12.95W
PoE Injector



PSW5
12VDC
Power Supply

*Visit www.specotech.com for latest ONVIF support. ONVIF is a trademark of Onvif, Inc. Apple and the Apple logo are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Android, Google Play and the Google Play logo are trademarks of Google Inc. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 4/27/16