

Color laser multifunction product



Lexmark X950 Series

Powerful color performance for your workgroup.



Color



10-inch
touch screen



Solutions



Duplex
printing



Up to 55
ppm



Network



12.6" x 19"



Copy



Scan



Fax



Outstanding color output

Make a lasting impression on your customers and do more printing in-house with vibrant, professional-quality output on a wide variety of media. With the advanced technology of the Lexmark X950 Series, you'll get high-performance tabloid multifunction capability that produces consistent color from the first page to the last.

- ▶ 1200 x 1200 print resolution for rich vibrant colors and crisp black text.
- ▶ Match brand sensitive corporate colors on marketing collateral and within Microsoft Office with Lexmark Named Color Replacement and PANTONE® calibration
- ▶ Lexmark Color Care Technology to manage color use and control costs.
- ▶ Create professional collateral materials ranging from saddle stitch booklets to folded brochures on media up to 12.6 x 48 inches.

Productive and intuitive

The Lexmark X950 Series combines high-performance printing, copying, scanning and faxing with time-saving workflow applications designed to boost your productivity.

- ▶ Print and copy at speeds up to 55 ppm black and 50 ppm color, and scan at speeds up to 70 images per minute; time to first copy as quick as 5.8 seconds.
- ▶ Extra large, easy to navigate 10-inch color touch screen provides audible and tactile feedback to make completing tasks intuitive.
- ▶ Preloaded applications help you drive greater efficiency in your workflow.
- ▶ Scan to multiple destinations, including scan to e-mail, scan to FTP, scan to fax, scan to network, scan to USB drive, and more.

Built for business

The Lexmark X950 Series features a robust print engine designed to handle the most demanding workloads with the advanced features and flexibility you need to run your business.

- ▶ Robust connectivity makes it easy to integrate into almost any network environment.
- ▶ Simplify device monitoring and administration through the embedded web server, Lexmark Universal Print Driver, and Lexmark Markvision Enterprise.
- ▶ High-capacity hard disk, 1.2 GHz processor, and up to 2GB RAM.
- ▶ Inner Tray 2 is standard, allowing you to separate print, copy or fax output into two bins.
- ▶ Choose from multiple input options to expand capacity up to 5,140 sheets.
- ▶ Easy-to-replace aftermarket cartridges provide yields of up to 32,000¹ pages black and up to 22,000¹ pages color

The right touch

The Lexmark e-Task color touch screen is a key access point to your MFP. The extra large customizable 10-inch interface gives you the ability to preview thumbnails of documents prior to printing, as well as to change print jobs at the device. You can even view, select and print specific pages within a document directly from the touch screen. Easy-to-use, intuitive navigation provides fast access to the functions, shortcuts and workflows you use most, and through the MyMFP feature, you can tailor your device with personal settings. New interactive sensory features provide both tactile and audible feedback, helping to guide you through each operation, confirming a touch has registered and indicating an action is transpiring.

Preloaded solutions* on the X950 series:



Forms and Favorites

Eliminate waste and inefficiencies associated with preprinted forms. Store frequently printed forms, marketing materials or other documents online, then print them on demand.



Scan to Network

Scan a hardcopy document and route the image to one of 30 predefined personal or public shared network folders.



Change Language**

Easily switch the language displayed on the touch screen—18 languages supported.

Examples of solutions available through Lexmark authorized partners and dealers, or through a Lexmark Professional Services engagement:



Scan to Network Premium

This enhanced version of Scan to Network offers advanced functionality to preview, modify, enhance and index scanned documents before routing them to a shared network folder.



Showroom

Display a customizable, scrolling slideshow on the color touch screen to promote your business or products, or to communicate important messages to your customers or employees.



Card Copy

Save time and effort in copying identification cards, licenses and insurance cards by automatically scanning, enlarging and printing both sides of a two-sided card onto one side of a sheet of paper.

* Additional solutions are available

** Opt-in to Change Language during installation



Consistent color every time

Produce professional documents confidently in-house knowing that the named colors of your company's brand and logo will print accurately and consistently every time. Included standard with your device, users can match brand sensitive corporate colors on marketing collateral and within Microsoft Office with Lexmark Named Color Replacement and PANTONE® calibration.

Protecting your information

From the data traveling through your network to the pages being printed, multilayered security features and built-in capabilities help you protect your devices, documents, data and network.

- ▶ Supports a variety of user authentication and authorization controls.
- ▶ Card reader option allows users to authenticate with proximity or swipe cards.
- ▶ Advanced hard disk encryption protects sensitive data on the printer's disk drive.
- ▶ Automatic, scheduled or manual disk wiping removes latent data.
- ▶ IPSec, SNMPv3 and 802.1x network security are supported.
- ▶ Security-audit logging tracks and identifies security risks.

Easy device management

Manage your output environment effectively with Lexmark Markvision Enterprise. This free browser-based software gives you complete visibility into your entire fleet of network printers and MFPs regardless of manufacturer. Markvision Enterprise makes it easy for administrators to configure, track, view, troubleshoot and proactively manage devices throughout their lifecycle, from the moment you connect them to the network until the day you retire them.



Intuitive color touch screen

The extra large 10-inch color touch screen allows you to operate your MFP with ease through intuitive navigation and easy access to workflow solutions and shortcuts.



Direct USB

The front USB port allows for convenient walk-up printing and is compatible with many printable image file formats.



Flexible input capacity

Choose the configuration that best fits your needs, up to a maximum of 5,140 sheets.




Exceptional media handling

Ultra-reliable paper feeding lets you load up to six different types of media, including sizes up to 12.6 x 48 inches and weights up to 300 gsm.



Advanced finishing options


Easily create professional output in-house with flexible finishing options, including multi-position stapling, hole punch, expanded output stacking, and booklet capability.



Lexmark solutions

Reduce unnecessary printing and simplify work processes through solutions applications preloaded on your device. Choose additional Lexmark solutions to fit your unique workflow needs.

*Average continuous black or composite CMY declared cartridge yield in accordance with ISO/IEC 19798.



X950 Series

Part #	Models
22Z0019	Lexmark X950de

1021231	Parallel Cable (10-foot)
14F0100	RS-232C Serial Interface Card

Part #	Laser toner/print cartridge
X950X2KG	X95x Black Extra High Yield Toner Cartridge
X950X2CG	X95x Cyan Extra High Yield Toner Cartridge
X950X2MG	X95x Magenta Extra High Yield Toner Cartridge
X950X2YG	X95x Yellow Extra High Yield Toner Cartridge
C950X71G	C950, X95x Photoconductor Unit 1-pack
C950X73G	C950, X95x Photoconductor Unit 3-pack
C950X76G	C950, X95x Waste Toner Bottle
25A0013	Staple Cartridges (3 pack)
21Z0357	Booklet Saddle Staple Cartridges (4 pack)

Part #	Extended warranties
2354235	X950 2-Years Total Onsite Service, Next Business Day
2354236	X950 3-Years Total Onsite Service, Next Business Day
2354237	X950 4-Years Total Onsite Service, Next Business Day
2354238	X950 5-Years Total Onsite Service, Next Business Day
2354239	X950 1-Year Onsite Service Renewal, Next Business Day


Part #	Paper handling
22Z0014	C950, X95x 2520-sheet tandem tray module
22Z0013	C950, X95x 3x520-sheet drawer stand
22Z0012	C950, X95x 520-sheet drawer stand
22Z0016	C950, X95x 3500-sheet finisher (3-hole)
22Z0017	C950, X95x Booklet finisher (3-hole)
22Z0015	C950, X95x 2000-sheet high capacity feeder

Part #	User replaceable parts
40X7550	C950, X95x Fuser Maintenance Kit, 320K, 110-120V
40X7540	C950, X95x 160K Maintenance Kit

Part #	Memory options
1025041	256MB DDR2-DRAM
1025042	512MB DDR2-DRAM
1025043	1024MB DDR2-DRAM
14F0245	256MB Flash Card
27X0014	160+ GB Hard Disk
30G0287	Arabic Font Card
30G0828	Japanese Font Card
30G0825	Korean Font Card
30G0826	Simplified Chinese Font Card
30G0827	Traditional Chinese Font Card

Part #	Application solutions
22Z0186	X950, X952, X954 Card for IPDS
22Z0187	X950, X952, X954 Card for PRESCRIBE Emulation
22Z0185	X950, X952, X954 Forms and Bar Code Card
57X9000	Lexmark PrintCryption Card

Part #	Connectivity
27X0025	MarkNet N8250 802.11b/g/n Wireless Print Server
14F0042	MarkNet N8130 Fiber Ethernet 100BaseFX, 10BaseFL Print Server
1021294	USB Cable (2-meter)
14F0000	Parallel 1284-B Interface Card



Color laser multifunction product



Product specifications	Lexmark X950de	Lexmark X952dte	Lexmark X954dhe
Printing			
Print technology	Color LED		
Display	Lexmark e-Task 10-inch (25.9 cm) color touch screen		
Print speed: Up to ⁴	Black: 45 ppm / Color: 40 ppm / (Black) Duplex: 45 spm	Black: 50 ppm / Color: 45 ppm / (Black) Duplex: 50 spm	Black: 55 ppm / Color: 50 ppm / (Black) Duplex: 55 spm
Time to first page: As fast as	Black: 5.5 seconds / Color: 7.7 seconds	Black: 5.2 seconds / Color: 7.7 seconds	Black: 5 seconds / Color: 7.2 seconds
Print resolution	1200 x 1200 dpi, 2400 Color Quality (2400 x 600 dpi)		
Memory	Standard: 1024 MB / Maximum: 2048 MB		Standard: 2048 MB / Maximum: 2048 MB
Hard disk	Included in configuration		
Print noise level, operating / idle	52 dBA / 24 dBA	52 dBA / 24 dBA	53 dBA / 24 dBA
Recommended monthly page volume ²	5,000 - 33,000 pages		
Maximum monthly duty cycle: Up to ³	200,000 pages per month	225,000 pages per month	250,000 pages per month
Supplies			
Supplies yield (*Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798.)	22,000*-page color (CMY) Toner Cartridges, 32,000*-page Black Toner Cartridges		
Paper handling			
Paper handling standard	520-sheet input tray, 100-sheet multipurpose feeder, 500-sheet output bin, integrated duplex	3 x 520-sheet drawer stand, 520-sheet input tray, 500-sheet output bin, integrated duplex, 100-sheet multipurpose feeder	2,520-sheet tandem tray module, 520-sheet input tray, 500-sheet output bin, integrated duplex, 100-sheet multipurpose feeder
Paper handling optional	520-sheet drawer stand, 2,520-sheet tandem tray module, 3 x 520-sheet drawer stand, 2,000-sheet high-capacity feeder, banner media tray, 3,500-sheet finisher, booklet finisher	Booklet finisher, 2,000-sheet high-capacity feeder, banner media tray, 3,500-sheet finisher	
Paper input capacity, standard: Up to	620 pages 20 lb or 75 gsm bond	2180 pages 20 lb or 75 gsm bond	3140 pages 20 lb or 75 gsm bond
Paper input capacity, maximum: Up to	5140 pages 20 lb or 75 gsm bond	4180 pages 20 lb or 75 gsm bond	5140 pages 20 lb or 75 gsm bond
Paper output capacity, standard: Up to	500 pages 20 lb or 75 gsm bond		
Paper output capacity, standard: Up to	3750 pages 20 lb or 75 gsm bond		
Media types supported	Refer to the Card Stock & Label Guide, Glossy Paper, Card Stock, Envelopes, Labels, Transparencies, Plain Paper		
General			
Function	Color Network Scanning, Color Scanning, Color Printing, Color Faxing, Color Copying		
Limited warranty	1-Year Onsite Service, Next Business Day		
Product certifications	www.lexmark.com		
Specified operating environment	Temperature: 10 to 32°C (50 to 90°F), Humidity: 15 to 85% Relative Humidity, Altitude: 0 - 2500 Meters (8,200 Feet)		
Size (in. - H x W x D) / weight (lb.)	30.01 x 25.20 x 43.63 in. / 255.8 lb.	44.38 x 25.20 x 26.97 in. / 332.2 lb.	44.38 x 25.20 x 26.97 in. / 351.8 lb.

¹Yield at approximately 5% print coverage. ²Recommended monthly page volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³Maximum monthly duty cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴Print and copy speeds measured in accordance with ISO/IEC 24734, excludes first set of text documents. For more information see: www.lexmark.com/ISOspeeds.

© 2015 Lexmark and the Lexmark logo are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. All other trademarks are the property of their respective owners. ENERGY STAR® is a U.S. registered mark.

AirPrint and the AirPrint logo are trademarks of Apple Inc.