

WorkForce WF-2750DWF



DATASHEET



Business-quality printing from this compact and affordable 4-in-1 with Wi-Fi, Wi-Fi Direct® and double-sided printing

Small business and home office users should look no further than this compact 4-in-1. The WF-2750DWF boasts double-sided, business-quality printing and individual inks for cost savings. It also features Wi-Fi and Wi-Fi Direct® and is compatible with Epson Connect¹ to ensure quick and easy mobile printing.

Business quality

This 4-in-1 printer uses a PrecisionCore printhead to ensure top quality, laser-like performance. Fast print speeds and a 30-page automatic document feeder for multi-page, 1200dpi scanning, copying and faxing offer the ultimate in convenience. Wi-Fi and Wi-Fi Direct® connectivity ensure the flexibility every small business needs.

Low running costs

The WF-2750DWF uses Epson's 16 series Pen and Crossword inks, available in a choice of standard or XL cartridges sizes to suit your specific printing needs. XL inks can help you to reduce your printing costs by up to 25%². The use of individual ink cartridges means only the colour used will need to be replaced, further reducing costs.

Mobile printing


Epson Connect compatibility offers useful features like scan-to-cloud, email print and the Epson iPrint app¹. The WF-2750DWF is also compatible with Apple AirPrint³ and Google Cloud print, letting you print seamlessly from smartphones and tablets.

Easy to use

Automatic Wi-Fi set-up⁴ helps make connection a breeze, while the 150-sheet front-loading paper cassette makes refilling easy. A 5.6cm LCD screen and a user-friendly menu makes navigating the WF-2750DWF simple and quick.

KEY FEATURES

- **Business-quality duplex printing**
Laser-like results
- **4-in-1**
Scan, copy, print and fax
- **Wi-Fi & Wi-Fi Direct**
Print wirelessly wherever you are
- **Save money with individual inks**
Only replace the colour used
- **Easy to use**
150 page front-loading paper tray



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	PrecisionCore™ Print Head
Minimum Droplet Size	3.3 pl, With Variable-Sized Droplet Technology
Ink Technology	DURABrite™ Ultra

PRINT

Printing Speed ISO/IEC 24734	13 Pages/min Monochrome, 7.3 Pages/min Colour
Maximum Printing Speed	20 Pages/min Colour (plain paper), 33 Pages/min Monochrome (plain paper)
Colours	Black, Cyan, Yellow, Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Scanning Resolution	1,200 dpi x 2,400 dpi (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

FAX

Fax speed dials (max)	60 names and numbers
Page memory	Up to 100 pages (ITU-T No.1 chart)
Fax Functions	PC Fax, Memory Reception, Auto Redial, Speed Dial

PAPER / MEDIA HANDLING

Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, Letter Legal, 10 x 15 cm, 13 x 18 cm, 16:9, User defined
Automatic Document Feeder	30 Pages
Duplex	Yes
Paper Tray Capacity	150 Sheets Standard
Number of paper trays	1

CONNECTIVITY

Interfaces	Wi-Fi Direct, Wireless LAN IEEE 802.11b/g/n, Hi-Speed USB - compatible with USB 2.0 specification
Mobile and Cloud printing services	Epson Connect (iPrint, Email Print, Remote Print Driver, Scan-to-Cloud), Apple AirPrint, Google Cloud Print

GENERAL

Product dimensions	425 x 360 x 230 mm (Width x Depth x Height)
Product weight	6.6 kg
Compatible Operating Systems	Mac OS X 10.6.8 or later, Windows 10, Windows 7, Windows 8, Windows 8.1, Windows Server 2003 (32/64bit), Windows Server 2008 (32/64bit), Windows Server 2008 R2, Windows Server 2012 (64bit), Windows Server 2012 R2, Windows Vista, Windows XP, Windows server 2003 R2, XP Professional x64 Edition

LOGISTICS INFORMATION

SKU	C11CF76401
EAN code	8715946616452
Dimensions Single Carton	490 x 300 x 433 mm
Carton Weight	8.49 Kg
Country of Origin	Indonesia
Pallet Size Euro	26 Units
Pallet Size Block	36 Units

WorkForce WF-2750DWF

WHAT'S IN THE BOX

- Main unit
- Individual Ink Cartridges
- Driver and utilities (CD)
- Warranty document
- User manual (CD)
- Software (CD)
- Quick Start Guide
- Power cable

INK CARTRIDGE COMPATIBILITY

● 16	
● 16	
● 16	
● 16	
● 16	
● 16XL	
● 16XL	
● 16XL	
● 16XL	
● 16XL	

INK YIELD DATA

	Pen and crossword 16	Pen and crossword 16XL
●	175 pages*	500 pages*
● ● ●	165 pages*	450 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>



For more information please contact:

Telephone: 01952 607111 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740
+ Local call rate.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

1. Epson iPrint requires a wireless connection and the Epson printing app. Email print and scan-to-cloud require an internet connection. For more information, supported languages and devices, please visit www.epsonconnect.eu
2. Comparison based on the cost per page for 16 vs. 16XL inks. For more information visit www.epson.eu/pageyield
3. AirPrint-enabled printers work with iPad (all models), iPhone (3GS or later), and iPod touch (3rd generation or later) running the latest version of iOS.
4. Automatic set-up compatible with Windows 10, Windows 8, Windows 7, Windows Vista and Mac OS

EPSON®