

## AXIS T91B50 Telescopic Ceiling Mount

Expandable ceiling mount for PTZ and fixed domes

AXIS T91B50 Telescopic Ceiling Mount is ideal where a PTZ /fixed dome camera needs to be installed in a high ceiling. The telescopic functionality allows the installer to adjust the length in an easy and secure way (up to 2 m/79 in). If a longer length is needed, two extension pipes are available, 30 cm (12 in) and 100 cm (39 in). The mount is designed to swing and not break if hit by forklifts or tall vehicles. It can also be installed in sloped ceilings thanks to the ball joint, which ensures that the camera is still hanging straight.

- > **For outdoors and indoors**
- > **Robust and safe installation**
- > **Support for Axis PTZ domes and fixed domes with 1.5" NPS thread**
- > **Flexible length, up to 5 m (197 in) with extension pipes**
- > **Swivel action with  $\alpha \pm 45^\circ$  pivot angle**



# AXIS T91B50 Telescopic Ceiling Mount

| General  |   |
|--|---|
| <b>Supported products</b>  | AXIS P55/P56/Q60/Q61 Series (requires AXIS T94A01D Pendant Kit)<br>AXIS M50 Series (requires AXIS T91A05 Camera Holder 1.5" NPS)<br>AXIS P33 Series (requires AXIS P33 Pendant Kit)<br>AXIS P32/Q35 Series (requires AXIS T94K01D/T94M01D Pendant Kit)<br>AXIS M3004-V/M3005-V (requires AXIS T94B01D Pendant Kit)<br>AXIS M3006-V/M3007-P/ M3007-PV (requires AXIS T94F01D Pendant Kit)<br>AXIS M3024-LVE/M3025-VE/M3026-VE/M3027-PVE/M3037-PVE (requires AXIS T94F02D Pendant Kit)<br>AXIS P3707-PE (requires AXIS T94M02D Pendant Kit)<br>AXIS Q3709-PVE (requires AXIS T94A01D Pendant Kit)<br>Axis fixed cameras (requires AXIS T91A05 Camera Holder 1.5" NPS) |
| <b>Casing</b>  | Powder coated aluminum NEMA 4X-rated*, IK10 impact-resistant<br>*Corrosion protection   |
| <b>Environment</b>   | Indoor<br>Outdoor   |
| <b>Maximum load</b>  | 10 kg (22 lb)   |
| <b>Pivot angle</b>   | ±45°  |
| <b>Cable routing</b>   | Side: Cable conduit hole 3/4"<br>Back: Cable conduit hole 3/4"  |
| <b>Approvals</b>   | IEC/EN/UL 60950-1<br>IEC/EN/UL 60950-22<br>EN 50581<br>IEC/EN 62262 IK10<br>NEMA 250 Type 4X*<br>*Corrosion protection  |
| <b>Dimensions</b>  | Minimum length: 1151 mm (45 in)<br>Maximum length: 2136 mm (84 in)  |
| <b>Weight</b>  | 4.1 kg (9 lb)   |
| <b>Included accessories</b>  | Installation Guide  |
| <b>Optional accessories</b>  | AXIS T91B52 Extension Pipe 30 cm (12 in)<br>AXIS T91B52 Extension Pipe 100 cm (40 in)<br>For more accessories, see <a href="http://www.axis.com">www.axis.com</a>   |
| <b>Warranty</b>  | Axis 3-year warranty, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>  |
| <b>Environmental responsibility:</b><br><a href="http://www.axis.com/environmental-responsibility">www.axis.com/environmental-responsibility</a> |   |