


Weather Resistant Long Range HD-TVI License Plate Capture Bullet Camera

HLPR67T 5-50mm motorized auto iris varifocal lens (10x auto focus/zoom), white housing

Note: Because of the special nature of this camera, during the day the scene will be monochrome. All license plates will be highlighted. Can be changed to color if desired in the OSD.

Features

- High-contrast imaging performance that delivers sharp, clear license-plate captures
- Full HD 1080p over coax (HD-TVI)
- 15 super high powered IR LEDs
- Captures license plates up to 40mph
- IR Range:165 ft. (depending on scene reflection)
- True Wide Dynamic Range operation (WDR)
- Additional 960H analog output
- Supports full UTC control over coax for Zoom/Focus and camera's OSD
- Weather resistant operation
- IP66 compliant
- 5 year warranty



Specifications

Image Sensor	1/3" Panasonic CMOS Sensor
Resolution.....	1080p
Minimum Illumination.....	0 lux (IR LEDs on)
Total Pixels	1956 (H) x 1266 (V)
Type.....	Monochrome
Number of IR LEDs	15 super high powered LEDs
IR Range	165 ft. (depending on scene reflection)
TV System.....	NTSC
S/N Ratio	More than 50db
Video Output.....	HD-TVI
Scanning System.....	Progressive scan
Power Supply	12VDC / 24VAC dual voltage (power supply not included)
Power Consumption	260mA (IR on: 560mA)
Operating Temperature.....	14° F – 122° F
Dimensions.....	4.01" (Dia.) x 10.82" (L)
Weight	3.5 lbs.



Optional Accessories



INTJBSW
Square
Junction Box



INTCMW
Corner/Pole
Adaptor



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply