



USA VISION SYSTEMS

Professional Series 4U Rackmount VMS Server

CPU		Intel 8th Generation i5 Coffee Lake
Memory (RAM)		Standard 16 GB DDR4 / Optional 32 GB DDR4
Hot Swap Bay		2/ 4/ 8
Video	Codec	MPEG4, MJPEG, H.265, H.264
	Input	32 or 64
Video Resolution		Panel Resolution up to 4K
Backup Type		DVD±R, DVD±RW, CD-R/RW
Recovery Option		Hidden Partition System Restore
Alarm Inputs	Sensor Input	4*
	Alarm Output	4*
Connector	Ethernet	2 RJ-45, 10/100/1000 Mbps
	VGA Output	DVI-D, DP, and HDMI
	USB 2.0	2 Rear
	USB 3.1	2 Front, 4 Rear
Remote Access		TCP/IP, LAN, WAN, Internet, ISDN
Operating Temperature		0 to 45 °C (32 to 133 °F)
Humidity		0 to 80% RH (non condensing)
Dimensions (W x D x H)		19 x 24 x 7 inch
Raid (optional)		0, 1, 5, 6
Power Supply		520W
Optional Products		GV-IO 12-In Card / GV-IO 12-Out Card / GV-IO Box 4 / GV-IO Box 8 / GV-IO Box 16 / GV-Data Capture Box Series / GV-Hub Box / GV-COM Box / GV-DOM / GV-Joystick / GV-Remote / GV - Keyboard
Languages		English/ Spanish