

22" (21.5" viewable) Dual Monitor Pack with DisplayPort Technology



Full HD 1080p and SuperClear® MVA Panel Technology

VA2252Sm_H2



If you're looking for high-performance monitors with easy deployment and mounting capabilities, look no further than the ViewSonic® VA2252Sm_H2. Sold as a dual pack of monitors without monitor stands, the VA2252Sm_H2 requires less packaging for a reduced environmental footprint, while still providing VESA compatible mounting for easy dual-screen installation. Designed with SuperClear MVA panel technology and a matte-finish uniform bezel, these 22" (21.5" viewable) monitors deliver an incredible front-of-screen experience at almost any viewing angle. And we didn't stop there, future-proof DisplayPort, as well as DVI and VGA inputs, provide productivity-boosting connectivity to PC systems, laptops, and other work devices. Our exclusive ViewMode™ feature lets you select the optimal screen setting for different applications, while Flicker-free and Blue Light filter technology minimizes eye fatigue so you can work for extended periods of time. With dual speakers on each monitor, you have the ultimate multimedia experience.

Key Features:

- Two monitors in a single package
- Full HD 1080p resolution
- Stunning color performance & wide-angle viewing
- Flexible connectivity options
- Superior color rendering & intuitive settings

Designed for:

Business


22" (21.5" viewable) Dual Monitor Pack with DisplayPort Technology



VA2252Sm_H2



Menu Controls



Internal Speaker

VESA® Compatible Wall Mount (100 x 100mm)

Internal Speaker

Kensington® Lock Slot

AC In

Audio In
Headphone
VGA
DVI-D
DisplayPort

Specifications

LCD PANEL	Type	Color a-Si TFT Active Matrix LCD
	Display Area	18.7" horizontal x 10.5" vertical; 21.5" diagonal
	Optimum Resolution	1920x1080
	Brightness	250 cd/m ² (typ.)
	Contrast Ratio	3,000:1 (typ.)
	Viewing Angles	178° horizontal, 178° vertical
	Colors	16.7M (6bit + Hi-FRC)
	Response Time	6.5ms (GTG)
	Backlight	White-light LED
	Backlight Life	40,000 hours (min.)
Panel Surface	Anti-glare, hard-coating (3H)	
VIDEO INPUT	Digital	VGA, DVI-D, DisplayPort
	Frequency	Fh: 24~82kHz, Fv: 50~75Hz
	Sync	Separate Sync
AUDIO OUTPUT	Speakers	1.5-watt (x2)
COMPATIBILITY	PC	Up to 1920x1080 non-interlaced
	Mac®	Up to 1920x1080
CONNECTOR	Video In	VGA, DVI-D, DisplayPort
	Audio In	3.5mm mini jack
	Headphone	3.5mm mini jack
	Power	3-pin plug (CEE22)
	Front Panel Buttons	Power, 1, Up, Down, 2
CONTROLS	OSD	Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Setup Menu, Memory Recall (See user guide for complete OSD functionality)

POWER	Voltage	AC 100~240V (universal), 50 / 60Hz
	Consumption	21W (typ.) / 28W (max.)
	Optimize	17W (typ.)
	Conserve	13W (typ.)
OPERATING CONDITIONS	Temperature	32~104° F (0~40° C)
	Humidity	10~90% (non-condensing)
DIMENSIONS (W x H x D)	Physical	22.2 x 12.2 x 2.0 in. / 563.9 x 309.8 x 50.8 mm
	Packaging	22.5 x 15.2 x 9.5 in. / 571 x 386 x 240 mm
WEIGHT	Net without Stand	6.8 lb. / 3.1 kg
	Gross	17.4 lb. / 7.9 kg
WALL MOUNT	VESA compatible	100 x 100mm
REGULATIONS		cUL, ENERGY STAR, FCC-B, EPEAT Silver, Mexico, Mexico Energy,
RECYCLE/DISPOSAL		Please dispose of in accordance with local, state, or federal laws
WARRANTY		Three-year limited warranty on parts, labor and backlight

Optional Accessories

Mini DisplayPort to DisplayPort Cable 6FT	CB-00010958
DVI-D to DVI-D Cable 6 Ft	CB-00008187
DisplayPort to DisplayPort Cable 30FT	CB-00010684
DisplayPort to DisplayPort Cable 6FT	CB-00010555
DisplayPort to DVI Adapter	LCD-CABLE-001
Desktop Display Wall Mount Kit	LCD-WMK-001

What's in the box?

VA2252Sm monitor (x2), Power cable, VGA cable, DisplayPort cable, Quick Start Guide



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by TUV NORD.