

HSM Pure 530

Small office shredder

Perfect for the workplace



- Made for everyday office use by 1 to 6 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Powerful motor allows for continuous operation
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Light barrier for automatic start/stop
- Mobile on castors
- Separate collecting bag for the sorted separation of the shredded material
- High quality wooden cabinet door
- Timeless machine design in trendy white
- Optional automatic external oiler for cross cut ensures long time cutting performance and quality
- Uses a 34 gallon capacity shred bag; Part #HSM1815



| HSM Part# | HSM2351 | HSM2353 |
|------------------------------------|-----------------------|-----------------------------|
| Cutting type | Strip cut | Cross cut |
| Cutting size | 1/4" | 3/16" x 11/8" |
| Security level DIN 32757-1 | 2 | 3 |
| Security level DIN 66399 | P-2 / O-2 / T-2 / E-2 | P-4 / O-3 / T-4 / E-3 / F-1 |
| Cutting capacity per run in sheets | 28 - 30 | 16 - 18 |
| Cutting Speed | 12.8 ft / min | 12.8 ft / min |
| Throat opening | 11.8" | 11.8" |
| Motor power (horsepower) | 0.67 hp | 0.67 hp |
| Voltage | 115 V / 60Hz | 115 V / 60Hz |
| Dimensions (H x W x D) | 28" x 19.5" x 14.25" | 28" x 19.5" x 14.25" |
| Weight | 60 lbs | 65 lbs |
| Shred-bin volume | 21 gal | 21 gal |
| Cutting capabilities | | |

All technical specifications are approximate values. Technical and design modifications reserved.