



HP PageWide Pro 477dn Multifunction Printer

Ultimate value and speed—HP PageWide Pro delivers the lowest total cost of ownership and fastest speeds in its class.^{1,2} Get quick two-sided scanning, plus best-in-class security features and energy efficiency.^{3,4}



Professional mode speed: Up to 40 ppm black; Up to 40 ppm color

Scan resolution: Up to 1200 x 1200 dpi hardware; Up to 1200 dpi optical

Copy resolution: Up to 600 dpi black (text and graphics); Up to 600 dpi color (text and graphics)

Standard connectivity: 2 Hi-Speed USB 2.0 Host; 1 Hi-Speed USB 2.0 Device; 1 Ethernet 10/100 Base-TX network; 2 RJ-11 modem port/phone line

Paper handling: 500-sheet input tray, 50-sheet multi-purpose tray; 300-sheet face-down output bin

Duty cycle (monthly): Up to 50,000 pages

Professional color, breakthrough total cost

- Results you expect and lasting value—breakthrough total cost of ownership, the lowest in its class.²
- Print professional-quality color on a variety of papers—perfect for office use.
- Print more pages and replace cartridges less often, using Original HP PageWide high-yield cartridges.⁷
- Spend less time and budget on scheduled maintenance with streamlined HP PageWide Technology.⁸

The fastest MFP in its class¹

- Wait less, do more with unmatched speeds¹—up to 55 ppm—and the fastest first-page printing in its class.⁵
- Get fast two-sided scanning directly to email and the cloud with this LDAP-enabled MFP.⁹
- Manage tasks from a 4.3-inch (10.9 cm) touchscreen. Print Microsoft® Word and PowerPoint® files from USB.⁶

Proven technology. Superior energy efficiency.⁴

- Minimize downtime with HP PageWide Technology that delivers reliable performance businesses demand.
- Conserve with HP PageWide Technology—designed to use less energy than any MFP in its class.⁴
- Get professional-quality color documents and the performance you expect with Original HP PageWide cartridges.

Best-in-class security and management features³

- Help protect your investment and extend capabilities as your needs grow, with a portfolio of solutions.¹⁰
- Help ensure the security of confidential information. Enter a PIN at the device to retrieve your print job.
- Regulate color use and reduce printing costs with HP Color Access Control.¹¹
- Help keep your printer secure—from boot up to shutdown—with secure boot and secure code integrity validation.



Mac



2-sided printing

¹ Comparison based on manufacturers' published specifications of fastest available color mode of all color business printers \$300–\$800 USD and MFPs \$400–\$1000 USD as of November 2015, excluding other HP PageWide products, and products with 1% or lower market share using market share as reported by IDC as of Q3 2015. HP PageWide speeds based on General Office mode and exclude first page. Learn more at <http://www.hp.com/go/printerspeeds> ² Total cost of ownership comparison based on 90,000 pages, manufacturers' published specifications for page yields and energy use, manufacturers' suggested retail prices for hardware and supplies, cost per page based on ISO yield with continuous printing in default mode with highest-available-capacity cartridges, long-life consumables of all color business printers \$300–\$800 USD and MFPs \$400–\$1,000 USD as of November 2015, excluding products with 1% or lower market share using market share as reported by IDC as of Q3 2015. Learn more at <http://www.hp.com/go/pagewideclaims> and <http://www.hp.com/go/learnaboutsupplies>. ³ Best-in-class security and fleet management claim based on comparison of built-in features of all color business printers \$300–\$800 USD and MFPs \$400–\$1000 USD as of November 2015, excluding products with 1% or lower market share using market share as reported by IDC as of Q3 2015. Learn more at <http://www.hp.com/go/printersecurityclaims> ⁴ Energy claim based on TEC data reported on energystar.gov. Data normalized to determine energy efficiency of majority of in-class business printers \$300–\$800 USD and MFPs \$400–\$1000 USD as of November 2015; market share as reported by IDC as of Q3 2015. Actual results may vary. Learn more at <http://www.hp.com/go/pagewideclaims> ⁵ Comparison based on manufacturers' published specifications of first page out from ready and sleep mode of all color business printers \$300–\$800 USD and MFPs \$400–\$1000 USD as of November 2015, excluding other HP PageWide products, and products with 1% or lower market share using market share as reported by IDC as of Q3 2015. Subject to device settings. Actual results may vary. Learn more at <http://www.hp.com/go/printerspeeds> ⁶ Feature works with Microsoft® Word and PowerPoint® 2003 and later. Only Latin language fonts are supported. ⁷ HP 970X High Yield Original PageWide cartridges are not included in printer purchase; purchase separately. Comparison based on ISO 24711 cartridge yields for HP 970 series High Yield Original PageWide Cartridges compared with HP 970 series Original PageWide Cartridges. High-yield cartridges are compatible only with HP PageWide Pro 400 and 500 series MFPs and printers. Learn more at <http://www.hp.com/go/learnaboutsupplies>. ⁸ Less scheduled maintenance based on 150,000 pages printed, and published comparisons of majority of in-class color laser printers \$300–\$800 USD and MFPs \$400–\$1000 USD as of November 2015; market share as reported by IDC as of Q3 2015. Learn more at <http://www.hp.com/go/pagewideclaims> ⁹ Requires an Internet connection to the printer. Services may require registration. App availability varies by country, language, and agreements. For details, see hpconnected.com ¹⁰ Additional workflow solutions available through HP's software and third-party partner program. For solution details, visit <http://www.hp.com/go/gsc> ¹¹ HP Color Access Control available only on HP PageWide Pro devices with a 4.3-inch touchscreen. Learn more at <http://www.hp.com/go/pagewidebusiness>

HP PageWide Pro 477dn Multifunction Printer Specifications Table

Functions / Multitasking supported	Print, copy, scan, fax / Yes	Media Sizes Custom	Tray 1: 3 x 5 in to 8.5 x 14 in; Tray 2: 4.0 x 8.3 in to 8.5 x 11.7 in; Optional Tray 3: 4.0 x 8.3 in to 8.5 x 14 in
Print Speed^{5,6}	Professional Mode (black): Up to 40 ppm; Professional Mode (color): Up to 40 ppm; First Page Out Color: As fast as 6.5 sec; First Page Out Color: As fast as 7 sec; General Office Mode (black): Up to 55 ppm; General Office Mode (color): Up to 55 ppm	Paper Handling	500-sheet input tray, 50-sheet multi-purpose tray, 300-sheet face-down output bin; Duplex Options: Automatic (standard); Auto Document Feeder Capacity: Standard, 50 sheets; Envelope Feeder: No; Standard Paper Trays: 2; Input Capacities: Up to 500 sheets standard; Up to 37 envelopes; Up to 100 cards; Up to 2.25 sheets labels; Output Capacities: Up to 300 sheets standard; Up to 35 envelopes; Up to 100 cards; Up to 100 sheets labels; Up to 250 sheets legal
Print Resolution	Black (best): Up to 1200 x 1200 optimized dpi from 600 x 600 input dpi (on Unspecified, Plain, HP Premium Presentation Matte, and HP Brochure Matte); Color (best): Up to 2400 x 1200 optimized dpi from 600 x 600 input dpi (on HP Advanced Photo Papers)	What's in the box	D3Q19A HP PageWide Pro 477dn Multifunction Printer; HP 972A Setup Black PageWide Cartridge (–3000 pages); HP 972A Setup Cyan PageWide Cartridge; HP 972A Setup Magenta PageWide Cartridge; HP 972A Setup Yellow PageWide Cartridge (CMY composite –1500 pages); power cord; phone cord; installation guide; CD-ROMs (for software, Windows and Mac printer drivers, and User's Guide).
Printer Drivers Included	Windows PCL 6 Discrete; Mac PS; Windows HP UPD (PCL 6, PS); Linux; UNIX; SAP	Replacement Cartridges	HP 972A Black Original PageWide Cartridge (–3500 pages); HP 972A Cyan Original PageWide Cartridge; HP 972A Magenta Original PageWide Cartridge; HP 972A Yellow Original PageWide Cartridge (CMY composite –3000 pages); HP 972X High Yield Black Original PageWide Cartridge (–10,000 pages); HP 972X High Yield Cyan Original PageWide Cartridge; HP 972X High Yield Magenta Original PageWide Cartridge; HP 972X High Yield Yellow Original PageWide Cartridge (CMY composite –7000 pages)
Print Cartridges Number	4 (1 each black, cyan, magenta, yellow)	Product Dimensions	W x D x H: 20.9 x 16.0 x 18.4 in; Maximum: 31.6 x 27.3 x 18.4 in
Borderless Printing	No	Product Weight¹	48.83 lb
Standard Print languages	HP PCLXL (PCL6), native PDF, HP Postscript Level 3 emulation	Warranty Features	One-year, on-site warranty, service and support; one-year technical phone support, chat, and e-mail
Printer Smart Software Features	HP ePrint, HP Mobile Apps, Google Cloud Print v2, HP EasyColor, print preview, automatic two-sided printing, print multiple pages per sheet (2, 4, 6, 9, 16), collation, booklet printing, cover pages, tray selection, scaling, Portrait/Landscape orientation, High Quality Grayscale and Black Ink Only, General Office/Professional/Presentation/Maximum dpi print modes, front USB port, copy/scan/fax; Control Panel Shortcuts; HP UPD PIN printing; HP Color Access Control; Optional: HP and third party extensibility solutions.	Control Panel	4.3" CGD (color graphics), IR touchscreen
Printer Management	HP Web Jetadmin; Embedded Web Server; HP UPD Printer Administrator Resource Kit; HP Utility (Mac), HP JetAdvantage Security Manager optional	Display Description	4.3" CGD (color graphics), IR touchscreen
Scan Type / Technology	Flatbed, ADF / Contact Image Sensor (CIS)	Software Included	Windows Installer and discrete PCL 6 driver; Mac Installer and PS driver; HP Participation Study; IRIS OCR
Scan Resolution	Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi	Compatible Operating Systems	Windows 10, Windows 8, Windows 7, Mac OS X v10.6, Mac OS X Lion, Mac OS X Mountain Lion, Linux (hplip.net)
Scan File Format	Scan File Type supported by Software: Bitmap (.bmp), JPEG (.jpg), PDF (.pdf), PNG (.png), Rich Text (.rtf), Searchable PDF (.pdf), Text (.txt), TIFF (.tif)	Compatible Network Operating Systems	Windows 8, Windows 7, Windows 10, Mac OS X v10.6, Mac OS X Lion, Mac OS X Mountain Lion, Windows 2003 Server (Standard Edition, Enterprise Edition, 32bit & 64-bit), Windows 2003 Server R2 (Standard Edition, Enterprise Edition, 32bit & 64-bit), Windows Small Business Server 2003 (32bit & 64-bit), Windows 2008 Server (Standard Edition, Enterprise Edition, 32bit & 64-bit), Windows Small Business Server 2008 (64-bit), Windows 2008 Server R2 (Standard Edition, Enterprise Edition, 64-bit), Windows Small Business Server 2011, Windows Server 2012, Windows Cluster (Windows Server 2008 R2), Windows Terminal Services (Windows Server 2008 R2), Windows 2003 Server Terminal Services with Citrix Metaframe XP with Feature Release 3, Windows Server 2003 Terminal Services with Citrix Presentation Server 4.0/4.5, Windows Server 2008 Terminal Services, Windows Server 2008 Terminal Services with Citrix XenApp, Citrix (Print): Xen Server 5.6, Xen Desktop 5.5, Citrix XenApps 6.0, Citrix XenApp 6.5, Novell Netware 6/6.5/Open Enterprise Server 6.5 (Novell Print support only), Linux (For more information, see hplip.net), SAP (For more information, see http://www.hp.com/go/sap/drivers), UNIX (For more information, see http://www.hp.com/go/unixmodelscripts)
Scan Input Modes	Front panel applications: Copy, Scan to E-mail with LDAP e-mail address lookup, Scan to Network Folder, Scan to USB, Scan to Sharepoint, Scan to Computer with SW. Client applications: EWS, HP Scan App, Compatible with HP Capture and Route	Minimum System Requirements	PC: Windows® 10, 8.1, 8, 7: 32-bit or 64-bit, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer. Windows Vista®: (32-bit only), 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer 8. Windows® XP SP3 or higher (32-bit only): any Intel® Pentium® II, Celeron® or 233 MHz compatible processor, 850 MB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer 8; MAC: Apple® OS X Yosemite, OS X Mavericks, OS X Mountain Lion; 1 GB HD; Internet required; USB
Scan Size	ADF: 8.5 x 14 in Maximum; Flatbed: 8.5 x 14 in	Power²	Power Supply Type: Internal (Built-in) Universal Power Supply; Power Requirements: Input voltage: 100 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3 Hz); Power Consumption: 100 watts (Maximum), 70 watts average (Printing), 10 watts (Ready), 4.8 watts (Sleep), 1.0 watt (Auto-Off), 0.2 watts (Manual-Off)
Scan Speed	Up to 25 ipm (mono & color)	Acoustics	Acoustic Power Emissions: 6.9 dB(A); Acoustic Pressure Emissions: 56 dB(A) (mono/color printing), 54 dB(A) (ADF mono copying), 54 dB(A) (ADF color copying), 45 dB(A) (ADF color scanning), 45 dB(A) (ADF mono scanning), Inaudible (idle)
Scanner Advanced Features	Image adjustments; Output quality setting; Selectable scan resolution 75 to 1200 dpi; Job notification; Scan and save to destinations: network folder, Computer, Sharepoint, USB flash drive, e-mail; OCR	Operating Environment	Recommended Operating Temperature: 59 to 86°F; Storage Temperature Range: -40 to 140°F; Non-Operating Humidity Range: 5 to 90% RH; Operating Humidity Range: 20 to 80% RH
Bit depth / Grayscale levels	24-bit (color); 8-bit (gray) / 256	Security Management	SSL/TLS (HTTPS), LDAP authentication; optional HP and 3rd party authentication solutions (e.g. badge readers) IPP over TLS; WPA2-Enterprise wired; firewall, certificates configuration; Control panel lock; Password protect EWS; Unused protocol and service disablement; Syslog; Signed firmware; Administrator settings; native authentication and authorization access control, native color access control; configurable authentication time out; UPD PIN printing; Mopy mode via UPD PIN printing; compatible with optional HP JetAdvantage Security Manager
Digital Sending Standard Features	Scan-to E-mail with LDAP email address lookup; Scan-to Network Folder; Scan-to USB; Scan-to Sharepoint; Scan-to Computer with SW; Fax Archive-to Network Folder; Fax Archive to E-mail; Fax-to Computer; Enable/Disable Fax; Enable/Disable color Fax, Color Access Control; Native Authorization & authentication;	Accessories	HP Officejet Pro Series 500-sheet Paper Tray (D3Q23A); HP PageWide Pro 2x500-sheet Paper Tray and Stand (P0V04A)
Copy Speed³	Black (ISO): Up to 40 cpm; Color (ISO): Up to 40 cpm; Black (Draft): Up to 55 cpm; Color (Draft): Up to 55 cpm	HP Service and Support Options	UBZ76E - HP 2 year Next Business Day PageWide Pro X477 Hardware Support; UBZ77E - HP 3 year Next Business Day PageWide Pro X477 Hardware Support; UBZ78E - HP 4 year Next Business Day PageWide Pro X477 Hardware Support; UBZ79E - HP 5 year Next Business Day PageWide Pro X477 Hardware Support; UBZ76E - HP 3 year Next Business Day Exchange PageWide Pro X477 Service; UBZ80E - HP Network Installation OfficeJet/PageWide Pro X47x-X57x Service
Copy Resolution	Black (text and graphics): Up to 600 dpi; Up to 600 dpi; Color (text and graphics): Up to 600 dpi		
Maximum Number Of Copies	Up to 99 copies		
Copier Resize	25 to 400%		
Copier Settings	ID Copy; Resize; Quality; Lighter/Darker; Two-sided copying; Tray Selection; Collate; Binding Margining; Copy Preview with Crop and resize; Enhancements; Enable/Disable copy; Enable/Disable color color; Color Access Control; Native Authorization & authentication; Set as New Defaults		
Fax Speed	Up to: 33.6 kbps; Letter: 4 sec per page		
Fax Resolution	Black (best): 300 x 300 dpi; Color (best): 200 x 200 dpi; Black (standard): 203 x 98 dpi; Color (standard): 200 x 200 dpi		
Fax Smart Software Features	Digital Fax - Fax to Computer is available with Windows and Macintosh, visit http://www.hp.com/support to download the latest software.		
Fax Features⁴	Fax Memory: Up to 100 pages (black and white); Up to 8 pages (color); Auto Fax Reduction Supported: Yes; Auto-Retrieving: Yes; Fax Delayed Sending: Yes; Distinctive Ring Detection Supported: Yes; Fax Forwarding Supported: Yes; Fax Phone TAM Interface Supported: Yes; Fax Polling Supported: Yes; Fax Telephone Mode Supported: No; Junk Barrier Supported: Yes, requires Caller ID; Maximum Speed Dialing Numbers: Up to 199 numbers; PC Interface Supported: Yes; HP Software support provided; Telephone Handset Supported: Yes		
Standard Connectivity	2 Hi-Speed USB 2.0 Host; 1 Hi-Speed USB 2.0 Device; 1 Ethernet 10/100 Base-TX network; 2 RJ-11 modem port/phone line		
Network Capabilities	Standard (built-in Ethernet)		
Wireless Capability	No		
Mobile Printing Capability¹²	HP ePrint, HP Mobile Apps, Android Plug-in, Windows 8/10, Windows 10 Mobile, Chromebook		
Memory	Standard: 768 MB; Maximum: 768 MB		
Duty Cycle⁷	Monthly, letter: Up to 50,000 pages		
Recommended Monthly Page Volume⁸	750 to 4500		
Media Types Supported	Plain paper (light, intermediate, mid-weight, heavy, extra heavy, prepunched, recycled, bond, other inkjet plain paper), photo (glossy, gloss, soft gloss, satin, matte, other inkjet photo), envelopes, labels, cards, specialty papers (glossy brochure, matte brochure, tri-fold brochure, Hagaki, greeting cards, other inkjet specialty paper)		
Media Weight Supported¹⁰	Tray 1: 16 to 32 lb (plain paper); 33 to 80 lb (photo); 20 to 24 lb (envelope); 32 to 48 lb (brochure); 90 to 110 lb (card); Tray 2: 16 to 32 lb (plain paper); 33 to 66 lb (photo); 20 to 24 lb (envelope); 32 to 48 lb (brochure); 90 to 110 lb (card); Tray 3: 16 to 32 lb (plain paper); 33 to 66 lb (photo); 32 to 48 lb (brochure); 90 to 110 lb (card)		
Media Sizes Supported	Tray 1: Letter, oficio, legal, statement, executive, 3 x 5 in, 4 x 6 in, 5 x 7 in, 5 x 8 in, envelopes (No. 10, Monarch); Tray 2: Letter, statement, executive, envelopes (No. 10); Tray 3: Letter, oficio, legal, statement, executive		

¹ With ink installed, no media in trays. ² Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Power consumption in Sleep mode depends on customer network switch capability, user configuration and network activity. ³ Speed specifications have been updated to reflect current industry testing methods. ⁴ Based on standard ITU-T test image #1 at standard resolution. More complicated pages or higher resolution will take longer and use more memory. ⁵ ISO speeds measured using ISO/IEC 24734. Excludes first page or first set of ISO test pages. For details see <http://www.hp.com/go/printerclaims>. ⁶ No heating or fusing warm up time required. ⁷ Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups. ⁸ HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement intervals and device life over an extended warranty period. ⁹ HP SureSupply alerts you when you should replace a print cartridge and helps you purchase locally or via the Internet. For more information, visit <http://www.hp.com/learn/suresupply>. Only available with original HP supplies; Internet access required. ¹⁰ All HP media listed as compatible with the printer in the HP DesignJet Printing Supplies Compatibility Guide, regardless of weight, may be used. ¹² Remote printing requires an Internet connection to an HP web-connected printer. App or software and HP ePrint account registration may also be required. See <http://www.hp.com/go/mobileprinting> for more details.

© Copyright 2016 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ENERGY STAR and the ENERGY STAR logo are registered U.S. marks. Windows is a registered trademark of Microsoft Corporation. AirPrint, iPad, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.

