

## Serie | 4 Washing Machines

### WAN28000GB

#### Automatic washing machine



**A+++**

#### Automatic washing machine with EcoSilence Drive™: quiet operation and durability that you can rely on.

- **EcoSilence Drive™:** extremely energy-efficient and quiet in operation with a 10-year warranty.
- **VarioPerfect™:** takes 65% less time or uses 50% less energy – delivers total flexibility.
- **Noise Level 54dB/75dB:** quiet washing and spinning.
- Easy operation with LED-Display and convenient control dial.
- **ActiveWater™:** saves water and costs thanks to a 2-step automatic load adjustment system.

#### Technical Data



Construction type :	Free-standing
Height of removable worktop (mm) :	850
Dimensions of the product (mm) :	848 x 598 x 550
Net weight (kg) :	67.0
Connection rating (W) :	2300
Current (A) :	10
Voltage (V) :	220-240
Frequency (Hz) :	50
Approval certificates :	CE, VDE
Length of electrical supply cord (cm) :	210
Washing performance class :	A
Door hinge :	Left
Wheels :	No
EAN code :	4242002938271
Capacity cotton (kg) - NEW (2010/30/EC) :	7.0
Energy efficiency class (2010/30/EC) :	A+++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) :	157
Power consumption in off-mode (W) - NEW (2010/30/EC) :	0.12
Power consumption in left-on mode - NEW (2010/30/EC) :	0.50
Water consumption annual (l/annum) - NEW (2010/30/EC) :	9020
Spin drying performance class :	B
Maximum spin speed (rpm) - NEW (2010/30/EC) :	1390
Average washing time cotton 40C (partial load) - NEW (2010/30/EC) :	200
Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC) :	200
Average washing time cotton 60C (partial load) - NEW (2010/30/EC) :	200
Noise level washing (dB(A) re 1 pW) :	54
Noise level spinning (dB(A) re 1 pW) :	75
Installation type :	Free-standing



4 242002 938271

#### Optional accessories

WMZ2200 : Floor securing component

WMZ2380 : Extension for cold water inlet /Aquastop

## Serie | 4 Washing Machines

### WAN28000GB

#### Automatic washing machine

#### Automatic washing machine with EcoSilence Drive™: quiet operation and durability that you can rely on.

##### Performance

- Energy Efficiency Class: A+++
- Capacity: 7 kg
- Maximum spin speed: 1400 rpm
- B spin class
- Energy consumption :157 kWh per year, based on 220 standard washing cycles
- -10% more economical (157kWh/year) than the standard value (174 kWh/year) of energy efficiency class A+++ in category 7 kg according to the EU-order 1061/2010
- Energy consumption: standard 60 °C cotton programme 0.84 kWh full load and 0.68 kWh partial load and 40 °C cotton programme 0.51 kWh partial load
- Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.
- Water consumption 9020 litres per year, based on 220 standard washing cycles
- Programme time:60 °C cotton programme 200 min at full load 200 min at partial load and 40 °C cotton programme 200 min partial load
- Weighted power consumption off-mode / left-on mode: 0.12 W / 0.5 W
- Duration of the left-on mode: NO\_FEATURE
- Drum volume: 55 litres
- Noise level washing : 54dB (A) re 1pW: Noise level spinning:75dB (A) re 1 pW

##### Programmes/functions

- Fully electronic control dial for all wash and special programmes
- Touch control buttons: Start delay, start/pause with reload function, SpeedPerfect, EcoPerfect, Spin speed reduction
- Special programmes: Aqua Plus, Jeans, Mixed Load, Handwash/Wool, Delicates 30°C

##### Key features


- VarioPerfect: speed or energy efficiency with perfect wash performance every time
- EcoSilence drive with 10 year warranty
- AntiVibration Design - for more stability and quietness

##### Additional features


- Large display for programme progress indication, spin speed, remaining time, 24 hour end time delay and load recommendation.
- 3D AquaSpa wash system with cascade for faster water penetration
- Safeguard monitoring system adjusts load distribution and programme settings to protect clothes
- Reload facility
- Automatic load adjustment system
- Multiple Water Protection
- Foam detection system
- Divider for Liquid Detergent
- Child lock
- Metal door catch
- Buzzer to indicate the end of cycle

##### Technical Information

- Slide-under installation
- Dimensions (H X W X D): 84.8 x 59.8 x 55 cm
- Large white door with 180° opening and 30 cm porthole

**Serie | 4 Washing Machines****WAN28000GB****Automatic washing machine**

measurements in mm



measurements in mm