



TOUGHBOOK 54

- Windows 10 Pro
- 14" HD (768p) and FHD (1080p) Displays
- Available Daylight-readable 1000 Nit Gloved Multi Touch Display
- Desktop Class Performance with Available Discrete Graphics and Dual Fans
- The World's Lightest 14" Semi-rugged Laptop—2 lbs. Lighter than the Competition
- MIL-STD-810G and IP51 Certified Magnesium Alloy Design with Built-in Handle
- Available 2nd Drive, Hot-swappable 2nd Battery, 2nd LAN, Serial, DVD, Antenna Pass-through, SmartCard Readers and More

ONE OF THE WORLD'S LIGHTEST AND THINNEST SEMI-RUGGED LAPTOP IN ITS CLASS.

The new Toughbook 54 laptop from Panasonic uses the latest advances to create a laptop 2 lbs. lighter and 0.5" thinner than the competition. It features a spill-resistant, full magnesium alloy design, hard drive heater, backlit keyboard and is available in various models to suit every need. The Toughbook 54 has a wide range of integrated options, such as dedicated GPS, 4G LTE mobile broadband with satellite GPS, antenna pass-through, and insertable and contactless SmartCard readers. It is the only semi-rugged laptop that offers an optional 2nd battery allowing hot-swap battery replacement without the need to shut down or hibernate. It is also the only laptop in its class to offer dual hard drives, another feature that makes the Toughbook 54 one of the most versatile and advanced semi-rugged notebooks on the market.

IP51

**3-FOOT
DROP RATING**

**MIL-STD-
810G**

TOUGHBOOK 54

Panasonic recommends Windows 10 Pro.

SOFTWARE

- Windows 10 Pro
- Panasonic Utilities (including Dashboard), Recovery Partition

DURABILITY

- MIL-STD-810G certified (3' drop, shock, vibration, sand, dust, altitude, high/low temperature, temperature shock, humidity)
- IP51 certified
- Spill-resistant keyboard
- Magnesium alloy case with handle
- Hard drive heater
- Shock-mounted flex-connect hard drive with quick-release
- Pre-installed replaceable screen film (Gloved Multi Touch model)

CPU

- Intel® Core™ i5-6300U vPro™ Processor
- 2.4GHz with Turbo Boost up to 3.0GHz
- 3MB cache

STORAGE & MEMORY

- Memory [RAM]
 - 4GB, 8GB or SDRAM [DDR3L-1600MHz]
- Primary Hard Drive (quick-release)
 - 500GB HDD 7200rpm³
 - Optional 128GB SSD, 256GB SSD, 1TB 7200rpm HDD^{2,3}
 - Hard drive heater
 - Shock-mounted with flex-connect
- Optional Second Drive (onboard)
 - 256GB SSD^{2,3}
 - Hard drive heater
 - Trained technician removable

DISPLAY

- Display Size and Resolution
 - Gloved Multi Touch model: 14.0" FHD 1920 x 1080 (1000 nit)
 - Non Touch model: 14.0" HD 1366 x 768
- IPS with direct bonding on FHD displays
- Anti-reflective and anti-glare screen treatments
- Graphics
 - Intel® HD Graphics 520
- Dual monitor support through HDMI and/or optional VGA
- Concealed mode (configurable)
- Optional AMD Firepro™ M5100 available on Touch Model

AUDIO

- Intel® high-definition audio compliant
- Integrated speakers
- Keyboard volume and mute controls

KEYBOARD & INPUT

- Touch, gestures and optional stylus pen (Gloved Multi Touch model)
- 2 user-definable keys [A1/A2]
- Dashboard
- 87-key with dedicated Windows® key
- Emissive backlit keyboard
- Electrostatic touchpad with multi touch support

DVD DRIVE

- Optional DVD Super MULTI Drive⁴

CAMERAS

- Optional 1080P webcam with mic and camera on/off indicator⁴

EXPANSION SLOTS

- Optional PC card Type II^{1,4}
- SD card (SDXC UHS-II)

INTERFACE

Docking Connector	24-pin
HDMI	Type A
Optional VGA	D-sub 15-pin
Headphones/Mic	Mini-jack stereo
Optional Serial (True)	D-sub 9-pin
USB 3.0 (x 3)	Type A
Optional USB 2.0 (x 1)	Type A ⁵
Optional Rugged Fischer® USB (Core Series)	5-pin ^{1,5}
10/100/1000 Ethernet	RJ-45
Optional 10/100/1000 2nd LAN (Ethernet)	RJ-45 ^{1,5}

WIRELESS

- Optional integrated 4G LTE multi carrier mobile broadband with satellite GPS
- Optional dedicated GPS (u-blox NEO M8N)⁶
- Optional dual high-gain antenna pass-through
- Optional contactless SmartCard/NFC reader^{7,8}
- Intel® Dual Band Wireless-AC 8260 802.11a/b/g/n/ac
- Intel® Wireless Display (WiDi)
- Bluetooth® v4.1 + EDR (Class 1) (Version 4.0 for Windows 7)
- Security
 - Authentication: LEAP, WPA, 802.1x, EAP-TLS, EAP-FAST, PEAP
 - Encryption: CKIP, TKIP, 128-bit and 64-bit WEP, Hardware AES
- Slide on/off switch

POWER

- Li-Ion battery pack:
 - Long life battery (standard on other models): 11.1V, typical 4200mAh, min. 4080mAh
 - Media bay 2nd battery⁴: 11.1V, typical 2960mAh, min. 2860mAh
- Battery operation:
 - 11 hours (18 hours with opt. 2nd battery)
- Hot-swap with optional media bay 2nd battery
- Battery charging time⁷: 2.5 hours (each battery)
- AC Adapter: AC 100V-240V 50/60Hz, auto sensing/switching worldwide power supply
- Battery status and battery hot-swap LED indicators

POWER MANAGEMENT

- Suspend/Resume Function, Hibernation, Standby, ACPI BIOS

SECURITY FEATURES

- >Password Security: Supervisor, User, Hard Disk Lock
- Kensington cable lock slot
- Trusted platform module (TPM) security chip v.1.2
- Computrace® theft protection agent in BIOS⁹
- Optional fingerprint reader⁴
- Optional insertable SmartCard reader (bottom)
- Optional 13.56MHz contactless SmartCard/NFC reader^{1,6}
 - ISO 14443 A/B compliant

WARRANTY

- 3-year limited warranty, parts and labor

DIMENSIONS & WEIGHT

- 10.7" (L) x 13.6" (W) x 1.2" (H)
- 4.4 lbs. (Non Touch model)
- 4.6 lbs. (Gloved Multi Touch models)

INTEGRATED OPTIONS¹⁰

- 4G LTE multi carrier mobile broadband with satellite GPS
- Dual antenna pass-through⁴
- Dedicated GPS (u-blox) or 2nd LAN or 4th USB (2.0) or rugged Fischer USB¹
- PC Card⁴ or DVD drive or media bay 2nd battery
- Contactless SmartCard/NFC or fingerprint readers⁴
- Insertable SmartCard reader (bottom)
- Serial
- VGA
- 1080p webcam and mic
- Primary hard drive (quick-release):
 - 128GB SSD, 256GB SSD and 1TB 7200rpm HDD with heaters
- 2nd hard drive (onboard)⁴:
 - 256GB SSD with heaters

SELECT ACCESSORIES¹⁰

AC Adapter (3-prong)	CF-AA5713AM
Long Life Battery Pack	CF-VZSU0PW
Media Bay 2nd Battery Pack ⁴	CF-VZSU0KW
Battery Charger	CF-VCTB2BW
LIND Car Adapter 120W	CF-LNDDC120
Memory Card 4GB	CF-WMBA1304G
Memory Card 8GB	CF-WMBA1308G
Desktop Dock	CF-VEB541U
Gloved Multi Touch Stylus	FZ-VMPM11U
14.0" Gloved Multi Touch LCD Protective Film	CF-VPF29U

Please consult your reseller or Panasonic representative before purchasing.

¹ Delayed availability on select options (2nd LAN, rugged Fischer USB, Contactless SmartCard/NFC and PC Card).

² Total usable memory will be less depending upon actual system configuration.

³ 1GB = 1,000,000,000 bytes.

⁴ DVD, PC Card and Media Bay 2nd Battery are mutually exclusive.

⁵ Dedicated GPS (u-blox), 4th USB (2.0), rugged Fischer USB and 2nd LAN are mutually exclusive.

⁶ Contactless SmartCard/NFC and fingerprint readers are mutually exclusive.

⁷ Approximate time. Battery performance features such as charge time and life span can vary according to the conditions under which the computer and battery are used. Battery operation and recharge times will vary based on many factors, including screen brightness, applications, features, power management, battery conditioning and other customer preferences. Battery testing results from MobileMark 2007.

⁸ Requires software and activation to enable theft protection.

⁹ 1.5" height on models with the following integrated options: insertable SmartCard (bottom), 2nd LAN, 4th USB (2.0), rugged Fischer USB, VGA and Serial.

¹⁰ Accessories and Integrated Options may vary depending on your notebook configuration. Not all items are currently available. Visit Panasonic website for more accessories and details.



1.866.413.3099

business.panasonic.ca

Panasonic is constantly enhancing product specifications and accessories. Specifications subject to change without notice. Trademarks are property of their respective owners.
©2016 Panasonic Corporation of North America. All rights reserved. Toughbook 54_MK2 Spec Sheet_06/16

TOUGHBOOK