

# ThinkCentre M600 Tiny 10G9001GUS

Region	Toolless Chassis Screw	
US	None	
Machine Type	Keyboard / Mouse	
10G9	USB / USB	
TopSeller	VESA Mount	
TopSeller	None	
Case 1L/2L	Stand	
1L	Floor Stand	
Processor	Power Supply	
Pentium J3710 (4C, 1.6 / 2.64GHz, 2MB)	65W 88% Adapter	
vPro	Operating System	
No	Windows 10 Pro 64	
Graphics	Warranty	
Integrated Intel HD Graphics 405	1-year, Onsite	
Monitor Cable	Global	
None	No	
Memory	End of Support	
4GBx1	Aug 26, 2022	
Storage	Ann Date (mm/yy)	
128GB SSD	07/16	
External Optical / I/O Box	Note:	
None	Country Code "US" is for United States, "++" is for EMEA countries (e.g. AD - Saudi, Arabia, AT - Austria, BM - Bulgaria, etc.), "xx" is for EAST countries (e.g. BM - Bulgaria, CX - Hungary, CY - Cyprus, etc.), and "***" is for MEA countries (e.g. AD - Saudi, Arabia, ED - Egypt, EQ - Sweden, etc.). Please be aware that the EMEA/ EAST/MEA models listed above might not be available in all countries	
WLAN + Bluetooth		
Intel 3165 ac, 1x1 + BT4.0		
Optional Rear Ports		
None		
Chassis Intrusion Switch		
Chassis Intrusion Switch		
Kensington Cable Lock		
None		
Speaker		
1Wx1		
Adapter Cage		
None		



This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<http://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.  
© Lenovo, 2018. All rights reserved.



# ThinkCentre M600 Tiny Platform Specifications

Product Specifications Reference (PSREF)

Processor	Intel® Celeron® Processor N3000 Series or Intel Pentium® Processor N3000 Series						Keyboard Mouse	<p>Some: Preferred Pro USB Keyboard (USB connector), Lenovo logo</p> <p>Some: Lenovo USB Fingerprint Keyboard (USB connector)</p> <p>Some: Ultrathin Plus Wireless Keyboard (2.4GHz via USB receiver), black</p> <p>Some: Enhanced Optical USB Mouse, black, Lenovo logo</p> <p>Some: Ultrathin Plus Wireless Mouse (2.4GHz via USB receiver), black</p>				
	Processor	Cores / Threads	Frequency (Base/Max)	Cache	Memory Types	Integrated Graphics		M600 Tiny only (1L)	Dimensions (WxDxH)	Max weight (lb / kg)		
	Celeron N3050	2 / 2	1.6 / 2.16 GHz	2MB	DDR3L-1600	Intel HD						
	Celeron J3060	2 / 2	1.6 / 2.48 GHz	2MB	DDR3L-1600	Intel HD 400						
	Pentium N3700	4 / 4	1.6 / 2.4 GHz	2MB	DDR3L-1600	Intel HD						
	Pentium J3710	4 / 4	1.6 / 2.64 GHz	2MB	DDR3L-1600	Intel HD 405						
Chipset	Intel Architecture (IA) SoC that integrates Intel processor core, graphics, memory controller, and I/O interfaces into a single system-on-chip solution						Mechanical	<ul style="list-style-type: none"> <li>• Tiny (1L), black color, metal case</li> </ul>				
Graphics	Intel HD Graphics in processor, uses main memory, DirectX® 11.1, twoDisplayPort™, one optional 3rd DP (not support DP to HDMI dongle) or VGA, supports triple independent display; Maximum resolution: 3840x2160(DP)@30Hz; 1920x1200(optional VGA)@60Hz; 1920x1080(DP to VGA dongle)@60Hz; 1920x1080(DP to DVI dongle)@60Hz; 3840x2160(DP to HDMI dongle)@30Hz							M600 Tiny (1L)	7.05" X 7.20" X 1.36" 179mm X 182.9mm X 34.5mm	2.9 lb (1.3 kg)		
Monitor cable	Optional DP to VGA, DP to DVI-D (single link), or DP to HDMI 1.4 dongle							M600 Tiny (1L) with VESA mount & ODD box	7.42" X 7.30" X 2.48" 188.4mm X 185.38mm X 63mm	4.12 lb (1.87 kg)		
Memory	8GB max / DDR3 Low Voltage, DDR3L-1600, non-parity, one 204-pin SO-DIMM socket							M600 Tiny (1L) with VESA mount & I/O box	7.42" X 7.30" X 2.62" 188.4mm X 185.38mm X 66.6mm	3.53 lb (1.6 kg)		
Storage	<p>Some: hard disk, 5400 or 7200 rpm, SATA 6.0Gb/s, 2.5" Wide</p> <p>Some: 500GB (5400 rpm) Solid State Hybrid Drive (SSHD) / with 8GB MLC NAND flash memory, SATA 6.0Gb/s, 2.5" wide</p>						VESA mount Floor Stand	Optional VESA mount bracket kit, supports VESA 75mm and 100mm				
Optical	<p>Some: Solid State Drive (SSD) / SATA 6.0Gb/s, 2.5" Wide</p> <p>Some: external ODD box with DVD-ROM, 9.5mm high, via USB</p> <p>Some: external ODD box with DVD±RW, 9.5mm high, via USB</p> <p>Some: external ODD box (for TIO) with DVD-ROM, 9.5mm high, via USB</p> <p>Some: external ODD box (for TIO) with DVD±RW, 9.5mm high, via USB</p>							Optional system floor stand for vertical orientation				
Onboard SATA Media reader	SATA 6.0Gb/s controller, one connectors on planar						Power supply	65 watts AC/DC adapter, autosensing, 88% PSU (not included for TIO models)				
	None							90 watts AC/DC adapter, autosensing, 88% PSU (only for models with I/O box)				
Front ports	Two USB 3.0 (one is Always On and fast charge), one microphone (stereo, 3.5mm), one headphone / microphone combo jack (stereo, 3.5mm)						Limited warranty <sup>3</sup>	1-year or 3-year, depot service / service upgrades available				
Rear ports	Two USB 2.0, two USB 3.0 (optional external optical box or I/O box occupies one or two specific USB on some models), ethernet (RJ-45), two DisplayPort, one optional port (VGA, 3rd DP, or serial on some models), one headphone							1-year or 3-year, limited onsite service / service upgrades available				
I/O box	Optional external I/O box, extends two USB 2.0, two USB 3.0, and one serial on rear, two USB 2.0 on front, via USB (occupy two specific USB 3.0 of M600 Tiny)						For Lenovo service upgrade options, please go to S-TC sheet	3-year, limited onsite service, OID (Onsite International Delivery) / service upgrades available				
Audio support	High Definition (HD) Audio, Realtek ALC223 / optional internal speaker (1 watt)							For Lenovo service upgrade options, please go to S-TC sheet				
WLAN <sup>13</sup>	<p>Some: 11ac wireless, M.2 Card, Realtek RTL8821AE (dual band), Wi-Fi + Bluetooth 4.0 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174 (dual band), Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 3165, Wi-Fi + Bluetooth 4.0 combo adapter, 1x1</p> <p>Some: 11ac wireless, M.2 Card, Intel Dual Band Wireless-AC 8260, Wi-Fi + Bluetooth 4.1 combo adapter, 2x2</p>						Preload	Windows® 7 Professional 64 preinstalled through downgrade rights in Windows 10 Pro 64-bit				
Bluetooth™ Ethernet Modem	<p>Some: Bluetooth 4.0 or 4.1 wireless, integrated in Wi-Fi + BT combo adapter</p> <p>One gigabit ethernet port, Realtek RTL8111GN, Wake on LAN®</p> <p>None</p>							Windows 7 Professional 64				
Manageability Security chip	None Trusted Platform Module, TCG 1.2-compliant						Environment	Windows 10 Pro 64-bit				
Security features	<ul style="list-style-type: none"> <li>• Security slot (in rear for optional Kensington® MicroSaver® cable)</li> <li>• Padlock loop</li> <li>• Smart USB protection, allows keyboard/ mouse only, blocks all storage devices</li> <li>• Power-on password</li> </ul>							<ul style="list-style-type: none"> <li>• Administrator password</li> <li>• Hard disk password</li> <li>• Boot sequence control</li> <li>• Boot without keyboard and mouse</li> <li>• Individual USB port disablement</li> <li>• Chassis intrusion switch</li> </ul>				
							Accessories	ENERGY STAR® 6.0*, EPEAT™ Gold rating* (*not for non-OS models); GREENGUARD®; RoHS-compliant; Cisco EnergyWise compatible; ErP Lot 3				
								For compatible accessories, please go to TC-AQP sheet				

See footnotes for more detailed information

©

Lenovo  
(M600 Tiny Spec) November 2017



# ThinkCentre M600 Tiny

Lenovo

