

HSM Pure 830

Powerful and mobile paper shredder

Designed for large departments



- Made for office use by 6 to 11 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Power motor allows for continuous operation
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Light barrier for automatic start/stop
- Mobile on castors
- Separate collecting bag for the sorted separation of the shredded material
- High quality wooden cabinet door
- Optional automatic external oiler for cross cut ensures long time cutting performance and quality
- Timeless machine design in trendy white
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM Part#	HSM2380	HSM2383
Cutting type	Strip cut	Cross cut
Cutting size	1/8"	3/16" x 11/8"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	47 - 49	39 - 41
Cutting Speed	21.65 ft / min	21.65 ft / min
Throat opening	12.9"	12.9"
Motor power (horsepower)	2.8 hp	2.8 hp
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	37.5" x 22.7" x 21.5"	37.5" x 22.7" x 21.5"
Weight	148 lbs	148 lbs
Shred-bin volume	39.6 gal	39.6 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.