RICOH
imagine. change.

B/W Printer

SP 5300DN
SP 5310DN

☑ Printer



SP 5300DN	SP 5310DN
50 ppm B/W	60 ppm B/W

A powerful yet durable addition to your workspace.

Both the SP 5300DN and SP 5310DN models are the types of fast, reliable, hardworking, everyday printers that will form the backbone of your company's document output. In fact, they're probably both best described as powerful, efficient and durable workhorses. And although they're both compact, these A4 Black and White Printers will quite simply get the job done. An added bonus is their durable design combined with their class-leading reliability – and their powerful controller and advanced processor means superfast output too.

- Small footprint
- Advanced controller and processor
- An almost maintenance free device
- Print speed options of 50 and 60 ppm
- ECO friendly with low power consumption



Working hard. Every day of the week.

All the power, with added control.

With a powerful Intel 1.46 Ghz processor and 2 GB memory, you can complete even the most complex of print jobs with the minimum of fuss. And because all this technology is working in the background, all you see is your productivity, speed and output increasing – which helps your business become even more efficient.



Just keeps on printing.

When your printers are always in use, you need to have a machine you can rely on. And that's why both these models are advanced enough to give you all the features you want, but robust enough to simply get every job done. They're also both designed to have almost no maintenance – allowing you to keep your business moving.



Packed full of features.

Thanks to their compact design, you don't have to worry about space, or set aside a specific area in the office. Their small footprint disguises just how much they can do – and these printers can be located almost anywhere. You can even print directly from your phone or tablet, or direct from mainframes using the IPDS option.

Low energy. Lower costs for your business.

GLOBAL puts the environment first and helps you do that too. So these printers offer the best combination of technological features, value for money and also help you reduce your energy costs.



SP 5300DN/SP 5310DN

MAIN SPECIFICATIONS

GENERAL

Configuration:	Desktop
Technology:	Laser
Warm-up time:	21/25.4 seconds
First output speed:	6/6 seconds
Print speed:	B/W: 50/60 pages per minute
CPU:	Intel Celeron-M: 1.46 GHz
Memory:	Standard: 2 GB Maximum: 2 GB
HDD (option):	320 GB
Dimensions (W x D x H):	420 x 410 x 345 mm
Weight:	18 kg
Power source:	220 - 240 V, 50/60 Hz

PRINTER

Printer language:	Standard: PCL5e, PCL6, Adobe® PostScript® 3™, PDF Option: XPS
Print resolution:	1,200 x 1,200 dpi
Interface:	Standard: USB2.0 Type A, Ethernet 10 base-T/100 base-TX/1000 base-T Option: Bi-directional IEEE 1284, Wireless LAN (IEEE 802.11a/b/g/n), USB Server for Second Network Interface
Network protocol:	TCP/IP (IP v4, IP v6)
Windows® environments:	Windows® 2000, Windows® Vista, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10, Windows® Server 2003, Windows® Server 2003R2, Windows® Server 2008, Windows® Server 2008R2, Windows® Server 2012, Windows® Server 2012R2
Mac OS environments:	Macintosh OS X v10.7 or later

PAPER HANDLING

Recommended paper size:	Standard paper tray(s): A4, A5, A6, B5, B6 Bypass tray: A4, A5, A6, B5, B6, Letter, Half Letter
Paper input capacity:	Maximum: 2,600 sheets
Paper output capacity:	Maximum: 500 sheets
Paper weight:	Paper tray(s): 64 - 120 g/m² Bypass tray: 60 - 220 g/m² Duplex: 64 - 120 g/m²
Media capability:	Plain paper, Middle thick paper, Thick paper, Recycled paper, Colour paper, Letterhead, Pre-printed paper, Thin paper, Special paper, Label paper, Envelopes, Bond, Transparencies

SECURITY

Authentication:	Windows® authentication, LDAP authentication, Basic authentication, User code authentication, 802.1.x wired authentication, Integration server authentication, SMTP authentication, POP before SMTP
Network security:	Disable/Enable ports and protocols, SSL support, SNMPv3 support

ECOLOGY

Power consumption:	Maximum: 1.4 kW Ready mode: 80.4/75.1 W Sleep mode: Less than 0.63/0.68 W TEC (Typical Electricity Consumption): 2.6/3.1 kWh

OPTIONS

1 x 500-sheet paper tray, Caster table, Low cabinet, High cabinet, Hard Disk Drive (320 GB), Bi-directional IEEE 1284, Wireless LAN (IEEE 802.11a/b/g/n), VM Card, IPDS unit, XPS direct print, Enhanced security HDD, USB Device Server, Extended USB board

CONSUMABLES

Toner capacity:	Black: 25,000 prints Declared yield value: Declared yield value in accordance with ISO/IEC 19752
Starter kit:	10,000 prints

For availability of models, options and software, please consult your local supplier.

RICOH @Remote

ISO9001 certified, ISO14001 certified, ISO27001 certified

All brand and/or product names are trademarks of their respective owners. Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure. The images in this brochure are not real photographs and slight differences in detail might appear.

Copyright © 2016 Ricoh Europe PLC. All rights reserved. This brochure, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of Ricoh Europe PLC.

RICOH
imagine. change.

www.ricoh-europe.com