

USB 2.0 to VGA Dual/Multi-Monitor External Video Graphics Card Adapter with Built-In USB Cable, 128 MB SDRAM, 1080p @ 60 Hz

MODEL NUMBER: U244-001-VGA



Connect a VGA monitor or projector to the USB 2.0 port of your computer or laptop. Use up to 6 adapters to connect up to 6 additional displays to a source. Ideal for multitasking, presentations and editing documents.

Description

The U244-001-VGA USB 2.0 to VGA External Video Graphics Card Adapter displays video on a VGA monitor or projector via your computer or laptop's USB 2.0 port. You can extend video from your primary display to another, duplicate the same video on both displays or change the second display to your primary display. This adapter is an ideal tool for multitasking, viewing large spreadsheets, editing documents, giving presentations at trade shows or watching movies and playing games on large screens.

You can add up to six U244-001-VGA adapters—each attached to its own USB 2.0 port—to a Windows computer or up to four on a Mac. Adding or removing a monitor is easy—no need to reboot the system afterward. No external power supply is necessary. First, install the drivers using the included CD. Then, connect the adapter to the display and the source using a VGA cable and the built-in USB 2.0 cable, respectively.

The U244-001-VGA supports high-definition video resolutions up to 1920 x 1080 (1080p) @ 60 Hz and features 128 MB DDR SDRAM of memory. Compatible with 32- and 64-bit Windows 2000 and later, 32- and 64-bit Intel Mac OS X 10.4 and later, and Ubuntu 14.04.2. This adapter also works with Surface™ tablets running Windows 8 Pro or later.

Features

Easy to Add Displays

- Extend video to a second monitor, duplicate the same video on both monitors or make the second monitor your primary display

Highlights

- Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Extend video to a second display or duplicate one video on both
- Add up to 6 adapters to connect a total of 7 displays (Windows)
- Plug and play—no external power supply needed
- Compatible with Windows®, Mac® and Ubuntu

System Requirements

- Computer with USB 2.0 port
- VGA monitor
- Windows 2000 or later (32- or 64-bit), Intel Mac OS X 10.4 or later (32- or 64-bit), Ubuntu 14.04.2 or Surface tablet running non-RT Windows 8 or 8.1
- Power PC-based Macs not supported

Package Includes

- U244-001-VGA USB 2.0 to VGA External Video Graphics Card Adapter
- Driver CD
- Owner's manual

- Ideal for multitasking, viewing spreadsheet data, editing documents, giving presentations, watching movies and playing video games
- Add up to 6 adapters for a total of 7 displays (Windows)
- Add up to 4 adapters for a total of 5 displays (Mac)
- No need to reboot system after adding or removing a monitor
- Plug and play—no external power supply needed

Vibrant, Superior Video Quality

- Supports high-definition video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Features 128 MB DDR SDRAM of memory
- Resumes automatically from hibernation and suspend modes

Broad Compatibility

- Works with 32- and 64-bit Windows 2000 and later
- Works with 32- and 64-bit Intel Mac OS X 10.4 and later
- Works with Surface tablets running Windows 8 Pro or later
- Works with Ubuntu 14.04.2

Specifications

OVERVIEW	
UPC Code	037332196514
Technology	USB 2.0 (High Speed); USB; VGA/SVGA
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p) @ 60 Hz
INPUT	
Bus Powered	Yes
Product Length (in.)	7
PHYSICAL	
Color	Black
Cable Jacket Rating	VW-1
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / in.)	0.90 x 5.10 x 5.50
Shipping Weight (lbs.)	0.40
Unit Dimensions (hwd / in.)	0.6 x 1.7 x 1.8



Unit Packaging Type	Box
Unit Weight (kg)	0.14
Unit Weight (lbs.)	0.3
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	4.4 BTU/Hr
Power Consumption (Watts)	1.3
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	HD15 (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>