

# AXIS P3225-V Mk II Network Camera

Streamlined and versatile HDTV 1080p fixed dome

AXIS P3225-V Mk II is a streamlined fixed dome that provides HDTV 1080p video. It features a varifocal lens and remote zoom and focus, which eliminates the need for hands-on fine tuning. Equipped with WDR – Forensic Capture to handle scenes with strong variations in light as well as Lightfinder technology for exceptional light sensitivity, this versatile camera provides outstanding video quality in both strong and poor light conditions. It supports Axis Zipstream technology that significantly reduces bandwidth and storage requirements.

- > **HDTV 1080p video quality**
- > **Remote zoom and focus**
- > **Axis Lightfinder technology**
- > **WDR – Forensic Capture**
- > **Axis Zipstream**



# AXIS P3225-V Mk II Network Camera

Camera	
<b>Image sensor</b>	Progressive scan RGB CMOS 1/3"
<b>Lens</b>	Varifocal, 3.0–10.5 mm, F1.4 Horizontal field of view: 92°–34° Vertical field of view: 50°–20° Remote focus and zoom, P-Iris control, IR corrected
<b>Day and night</b>	Automatically removable infrared-cut filter
<b>Minimum illumination</b>	HDTV 1080p 25/30 fps with WDR – forensic capture and Lightfinder: Color: 0.15 lux at 50 IRE, F1.4 B/W: 0.03 lux at 50 IRE, F1.4 HDTV 1080p 50/60 fps: Color: 0.3 lux at 50 IRE, F1.4 B/W: 0.06 lux at 50 IRE, F1.4
<b>Shutter time</b>	1/66500 s to 1 s
<b>Camera angle adjustment</b>	Pan ±180°, tilt -5 to +85°, rotation ±95°
Video	
<b>Video compression</b>	H.264 Baseline, Main and High Profile (MPEG-4 Part 10/AVC) Motion JPEG
<b>Resolution</b>	1920x1080 to 160x90
<b>Frame rate</b>	With WDR: 25/30 fps with power line frequency 50/60 Hz Without WDR: 50/60 fps with power line frequency 50/60 Hz
<b>Video streaming</b>	Multiple, individually configurable streams in H.264 and Motion JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264
<b>Multi-view streaming</b>	2 individually cropped out view areas
<b>Pan/Tilt/Zoom</b>	Digital PTZ, preset positions
<b>Image settings</b>	Compression, color, brightness, sharpness, contrast, local contrast, white balance, exposure control (including automatic gain control), exposure zones, fine tuning of behavior at different light levels, WDR – forensic capture: up to 120 dB depending on scene, text and image overlay, mirroring of images, privacy masks Rotation: 0°, 90°, 180°, 270°, including Corridor Format
Network	
<b>Security</b>	Password protection, IP address filtering, HTTPS <sup>a</sup> encryption, IEEE 802.1X <sup>a</sup> network access control, Digest authentication, User access log, Centralized Certificate Management
<b>Supported protocols</b>	IPv4/v6, HTTP, HTTPS <sup>a</sup> , SSL/TLS <sup>a</sup> , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP <sup>TM</sup> , SNMP v1/v2c/v3(MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, LLDP
System integration	
<b>Application Programming Interface</b>	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at <a href="http://www.axis.com">www.axis.com</a> AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S and ONVIF Profile G, specification at <a href="http://www.onvif.org">www.onvif.org</a>
<b>Analytics</b>	Included AXIS Video Motion Detection, active tampering alarm Supported AXIS Guard Suite including AXIS Motion Guard, AXIS Fence Guard, and AXIS Loitering Guard, AXIS Perimeter Defender AXIS Digital Autotracking, AXIS People Counter, AXIS Tailgating Detector, AXIS Direction Detector, AXIS Occupancy Estimator, AXIS Random Inspection, AXIS Queue Monitor Support for AXIS Camera Application Platform enabling installation of third-party applications, see <a href="http://www.axis.com/acap">www.axis.com/acap</a>
<b>Event triggers</b>	Analytics, edge storage events, virtual inputs through API
<b>Event actions</b>	Record video: SD card and network share Upload of images or video clips: FTP, SFTP, HTTP, HTTPS, network share and email
Pre- and post-alarm video or image buffering for recording or upload Notification: email, HTTP, HTTPS, TCP and SNMP trap Overlay text	
<b>Data streaming</b>	Event data
<b>Built-in installation aids</b>	Remote zoom, remote focus, pixel counter
General	
<b>Casing</b>	IP52-rated, IK08 impact-resistant, polycarbonate casing with hard-coated dome and dehumidifying membrane Encapsulated electronics and captive screws Color: white NCS S 1002-B For repainting instructions of casing and impact on warranty, contact your Axis partner.
<b>Mounting</b>	Mounting bracket with junction box holes (double-gang, single-gang, and 4" octagon) 1/4"-20 UNC tripod screw thread
<b>Sustainability</b>	PVC free
<b>Memory</b>	512 MB RAM, 256 MB Flash
<b>Power</b>	Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 2, max 4.8 W, typical 3.5 W
<b>Connectors</b>	RJ45 10BASE-T/100BASE-TX PoE
<b>Storage</b>	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see <a href="http://www.axis.com">www.axis.com</a>
<b>Operating conditions</b>	0 °C to 50 °C (32 °F to 122 °F) Humidity 10 to 85% RH (non-condensing)
<b>Storage conditions</b>	-40 °C to 65 °C (-40 °F to 149 °F)
<b>Approvals</b>	<b>EMC</b> EN 55022 Class B, EN 61000-6-1, EN 61000-6-2, EN 55024, EN 50121-4, IEC 62236-4, FCC Part 15 Subpart B Class A and B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 22 Class B, KCC KN32 Class B, KN35 <b>Safety</b> IEC/EN/UL 60950-1 <b>Environment</b> IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-14 IEC 60068-2-6 (vibration), IEC 60068-2-27 (shock), IEC 60068-2-78, IEC/EN 60529 IP52, IEC/EN 62262 IK08
<b>Dimensions</b>	Height: 101 mm (4 in) Ø 149 mm (5 7/8 in)
<b>Weight</b>	550 g (1.2 lb)
<b>Included accessories</b>	Installation Guide, Windows decoder 1-user license, mounting bracket, cable gasket, Resistox® T20 L-key, drill template, connector guard
<b>Optional accessories</b>	AXIS ACI Conduit Bracket B, AXIS ACI Conduit Adapters, AXIS T94K01L Recessed Mount Kit, AXIS T94K01D Pendant Kit, AXIS Skin Cover C, Black, AXIS Mounts, Smoked dome For more accessories, see <a href="http://www.axis.com">www.axis.com</a>
<b>Video management software</b>	AXIS Companion, AXIS Camera Station, Video management software from Axis Application Development Partners available on <a href="http://www.axis.com/vms">www.axis.com/vms</a>
<b>Languages</b>	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
<b>Warranty</b>	Axis 3-year warranty and AXIS Extended Warranty option, see <a href="http://www.axis.com/warranty">www.axis.com/warranty</a>

a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. ([www.openssl.org](http://www.openssl.org)), and cryptographic software written by Eric Young ([ey@cryptsoft.com](mailto:ey@cryptsoft.com)).

#### Environmental responsibility:

[www.axis.com/environmental-responsibility](http://www.axis.com/environmental-responsibility)