

Leyard TWA1.4

LED Video Wall

The Leyard® TWA1.4 is a fine pitch LED video wall display with a 1.4 millimeter pitch. The Leyard TWA1.4 delivers benefits unique to its “flat panel” design including enhanced image quality, a 16:9 form factor optimized for the most popular high resolutions, ease of installation and service, and outstanding flatness and uniformity. With a power-efficient design, the Leyard TWA1.4 significantly reduces power utilization while delivering a beautiful image.



SPECIFICATION	DETAIL
Product Name	TWA1.4
Pixel Pitch	1.49mm
LED Type	Commercial grade 3-in-1 Black SMD
Display Resolution	805 x 452
Pixel Density	450,000 / sq m 41,800 / sq ft
LEDs per Display	363,860
Module Resolution	161 x 113
Module Size	240 x 168.75mm
LEDs per Module	18,193
Modules/Display (W x H)	5 x 4
Brightness Max (cd / sq m)	800
Color Gamut	100% NTSC
Contrast Ratio	> 6,000:1
Brightness Uniformity	>97%
Color Uniformity	>97%
LED Refresh Rate	3,000 Hz
Color Temperature, Adjustable (k)	3,200 - 9,300
Viewing Angle, Horizontal	160°
Viewing Angle, Vertical	140°
LED Surround	Black Solder Mask

Video Inputs	2x HDMI in, 2x HDMI out; HDCP Compliant
Video Input Resolution Maximum	1920 x 1080 @ 60Hz
Frame Rate	50, 60Hz
Control Input Type	RS232 or Ethernet
Color Processing	16-bit
Service Access	Rear
LED Lifetime: Typical	100,000 hrs
Display Size (W x H x D)	1,200 x 675 x 100mm 47.24 x 26.57 x 3.94in
Display Diagonal	1,377mm 54.21in
Display Area	0.81 sq m 8.718 sq ft
Display Weight (per display)	30 kg 66.1 lb
Display Weight (per sq m)	37 kg / sq m 81.6 lbs / sq m
Line Voltage	100-240V AC, 50/60Hz autoranging
Power Consumption, Maximum (watts)	360 / Display 445 / sq m
Power Consumption, Typical (watts)	90 / Display 111 / sq m
Environment	Indoor
Power Supply	Single. Dual optional
Protection	IP30
Acoustic noise	Fanless Operation
Operating Temperature/Humidity (degrees F/C) 10-80% relative humidity, non-condensing	-10° to 40° C -14° to 104° F
Storage Temperature/Humidity (degrees F/C) 10-85% relative humidity, non-condensing	-20° to 60° C -4° to 140° F
Regulatory Compliance	NRTL, FCC Class A, CE Class A, WEEE, EN60950 and CISPR 22/2010

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 10/7/2016

© Copyright 2016 Planar Systems, Inc. All rights reserved