

HD-TVI 1080p Indoor/Outdoor Miniature Turret Color Camera

HT71TG 2.9mm fixed lens, dark grey housing

HT71TW 2.9mm fixed lens, white housing

Features

- 1/3" Progressive Scan CMOS, 2MP
- Compact size - only 2.36" in diameter!
- 12 IR LEDs
- Weather / Vandal resistant operation
- Cast aluminum construction
- Additional analog output for 960H
- Signal distance up to 1600 feet*
- Full OSD operation via UTC (TVI output only)
- IP66 compliant
- 12VDC operation
- 5 year warranty



Specifications

Image Sensor	1/3" Progressive Scan CMOS, 2MP
Resolution.....	1920 x 1080 @ 30fps
Minimum Illumination.....	0.00 lux (IR LED on)
Effective Pixels	1984 (H) x 1105 (V)
Total Pixels	2000 (H) x 1121 (V)
Electronic Shutter Speed.....	Auto / Manual
Number of IR LEDs	12
IR Range	35 ft. (depending on scene reflection)
Day/Night.....	Auto / Color / BW / Ext
Scanning System.....	Progressive
Synchronization	Internal
Communication.....	UTC
Frequency.....	15.734kHz (H) / 60Hz (V)
Video Output.....	1.0Vp-p / 75 ohms
S/N Ratio	More than 50dB
AGC.....	Auto
White Balance	Auto
Operating Temperature.....	14° F – 120° F
Power Supply	12VDC (power supply not included)
Power Consumption	100mA (IR off) / 200mA (IR on)
Certification.....	FCC, RoHS
Dimensions.....	2.36" (Dia.) x 2.15" (H)
Weight	10 oz.



Perfect for use in all vehicles or anywhere that a miniature, aesthetically pleasing, high resolution camera is desired.

Optional Accessory



PSW5
12VDC
Power Supply