

4XEM 2 Port HDMI Splitter Supports 3D 4K/2K

4XEM Part- **4XHDMI24K2K**



The 4XEM 2 port 4K HDMI splitter will connect your HD source with 2 HD display. Distribute and amplify your HDMI signal simultaneously to two displays. The 4XEM HDMI 1x2 splitter supports the highest video resolution 3840x2160 at 30Hz. With 10.2 Gbps video bandwidth. The 4XEM 2 port HDMI splitter and amplifier reduces the exchange of cables, helping reduce the wear and tear on your HDMI ports. The 2 port HDMI splitter delivers a pure signal while the fully shielded conductors provide complete immunity to EMI/RFI. When connecting any of your HDMI compatible devices, always trust 4XEM Connectivity!

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

Contact Todd Schaus 4XEM sales Rep
1-866-999-4936 Ext.104 tschaus@4xem.com




Features:

- One HDMI input signal split into four HDMI devices
- Support 3D
- Supports 4K/2K
- Supports CEC
- Supports deep color 30bit,36bit
- Supports Blue-Ray 24/50/60fs/HD-DVD-xvYCC
- Digital audio format, as DTS-HD/Dolby-trueHD/LPCM7.1/DTS/Dolby-AC3/DSD
- Supports signal retiming
- Supports up to 15 meters AWG26 HDMI standard cable length with an output up to 25metres AWG26 cable length
- No loss of quality
- installs in minutes
- Need DC5V/1A Power supply (included)



Application(s):

- Wireless Transfer
- Long Distance
- De-Cluttering
- Audio Transmission
- Video Transmission



4XEM Products Are Available At Your Favorite Online Retailers





DATA SHEET

SPECIFICATIONS:

HDMI version..... HDMI 1.4b

HDCP version.....HDCP1.4

HDMI resolution24/50/60fs/1080p/1080i/720p/576p/576i/480p/480i

Support video color format24bit/deep color
30bit,36bit,48bit

Support audio format.....DTS-HD/Dolby-trueHD/LPCM7.1/DTS/Dolby-AC3/DSD

Max bandwidth.....340MHz

Max baud rate.....10.2Gbps

Input/Output TMDs signal0.5~1.5Volts p-p(TTL)

Input/Output DDC signal 5Volts p-p (TTL)

Input cable distance.....≤15m AWG26 HDMI 1.4standard cable

Output cable distance.....≤25m AWG26 HDMI 1.4 standard cable

Max working current.....1.2A

Power adapter format..Input:AC (50HZ, 60HZ) 100V-240V; Output: DC5V/2A

Operating Temperature range..... (-15 to +55°C)

Operating Humidity range.....5 to 90%RH (No Condensation)

Dimension (L x W x H).....64x60x23 (mm)

Weight.....100g

* Product appearance and specifications are subject to change without notice.

* Same day shipping is only available for orders shipping within the United States.

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

**Contact Todd Schaus 4XEM sales Rep
1-866-999-4936 Ext.104 tschaus@4xem.com**

