

FHD 1080p **LED**

ECONOMY WIDE LED BLU



1080p Full HD	LED Back Light	300cd/m² Brightness	5000:1 Contrast	16.7 MILLION Display Color	178°/178° Viewing Angle	16:9 Aspect Ratio
-------------------------	--------------------------	--	---------------------------	--------------------------------------	-----------------------------------	-----------------------------

55RCE

BUILT TO RUN 24 X 7 X 365 CONTINUOUSLY

OVERVIEW

The ORION Images Wide LCD w/ LED BLU (backlight unit) high brightness displays are a truly professional experience in next generation technology using eco-friendly material (no mercury or halogen). This unit applies standby mode (less than 1W) to save energy.

FEATURES

- 55Inch 1920 x 1080p Full HD Maximum Resolution
- LED BLU (Back Light Unit) Display Monitor
- 300cd/m² High Brightness / 5000:1 Contrast Ratio
- 16 : 9 Wide Aspect Ratio
- 178° / 178° Viewing Angle
- BNC Video 2 In, BNC Video 1 Out, HDMI 1 In, VGA 1 In, Audio 1 In / 1 Out
- Display Aspect Auto / 16:9 / 4:3 / Zoom 1&2
- Optional Wall and Ceiling Mount Kits




SPECIFICATIONS


55RCE	
Display	
Screen Size	55 Inch
Max. Resolution	1920 x 1080 @ 60Hz
Pixel Pitch	0.630 x 0.630mm
Brightness	300cd/m ²
Contrast Ratio	5000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	178° / 178°
Display Color	16.7 Million
Response Time	< 6.5ms
Video System	NTSC / PAL
Interface	
Video In (BNC Type)	2 In
Video Out (BNC Type)	1 Out
HDMI In	1 In
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	1 In / 1 Out
Transmitter	
Remote Control	Yes
Audio	
Built-in Speakers	Yes (3W x 2)
Features	
Multi Language	English
General	
Outline Dimension (W x H x D)	50.19" x 29.52" x 3.98" (w/o stand)
Net Weight	80.63 lbs
Material Type	Metal
Material Color	Black
Desk Top Stand	Yes (Foot Stand)
Environment	
Consumption: < On	< 150W
Standby Mode	< 1W
Electrical Rating	AC100~240V (50/60Hz)
Operating Temperature	0° ~ 40° C / 32° ~ 104° F
Storage Temperature	-20° ~ 60° C / -4° ~ 140° F
Mounts	
VESA™ Mount Size	200 x 200mm, 700 x 200mm
Wall	WB-4663
Ceiling	CMH-01

*Design and specifications are subject to change without notice

INPUT INTERFACE



DIMENSIONS




FEATURE

Scan Size can be selected as AUTO / 16 : 9 / 4 : 3 / Panorama / Zoom



OPTIONAL MOUNTS



KEY PAD

