

Vertical Wall-Mount Server Rack - Solid Steel - 6U

Product ID: RK619WALLV



StarTech.com

This wall-mount bracket provides 6U of storage space to vertically mount your equipment on the wall. The 6U wall-mount rack is EIA-310-D compliant to ensure compatibility with any 19" rack-mount equipment, such as your power strips, telecommunication, network and A/V devices.

The 6U rack optimizes your working space by mounting equipment to your wall instead of taking up desk space or other surface area. It's perfect for your SoHo (small office, home office) environment, server room or any other location where available space is limited.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your expensive, mission-critical equipment. Also, because the wall mounting holes are positioned 16" apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring. Cage nuts and screws are also included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

To provide a suitable mounting solution for virtually any surface such as your wall, ceiling or desk, the 6U bracket features separate mounting patterns for both ceilings and walls. This means that you can mount the bracket vertically to your wall or horizontally to your ceiling or under your desk.

If you're looking for a mountable storage solution with fewer rack units, StarTech.com also offers a 1U wall-mount bracket, a 2U wall-mount bracket, a 3U wall-mount bracket and a 4U wall-mount bracket.

The RK619WALLV is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Install networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Use in your small office environment where you can't comfortably fit a full-sized rack

Features

- **NO ASSEMBLY REQUIRED:** For added convenience, this 6U wall mount patch panel bracket arrives fully assembled with cage screws and nuts for mounting equipment
- 6U
- **BUILT TO LAST:** Constructed to EIA-310 19in rack standards, the wall mount bracket features a solid steel design for ultimate durability
- EIA-310 19
- **VERSATILE FUNCTIONALITY:** This multi-use patch panel bracket enables you to mount your server or networking equipment vertically on a wall or horizontally under a desk for added versatility
-
- **STANDARDIZED HOLE SIZING:** Wall mounting holes are 16 inches center to center for greater stability, and mounting to standard wall studs
- 1640.6cm
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this wall mount patch panel bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance
- StarTech.com30IT

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	6U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)

Industry Standards EIA/ECA-310-E

Performance

Weight Capacity 200.0 lb [90.7 kg]

Special Notes / Requirements

Note Package includes 1" screws for mounting to wood surfaces, additional hardware will be required for other materials

Physical Characteristics

Color Black

Construction Material Steel

Product Measurements

Product Length 6.0 in [15.2 cm]

Product Width 19.9 in [50.5 cm]

Product Height 11.1 in [28.2 cm]

Weight of Product 2.9 lb [1.3 kg]

Packaging Information

Flat Pack (Assembly Required) No

Package Length 20.9 in [53.1 cm]

Package Width 11.7 in [29.7 cm]

Package Height 6.5 in [16.4 cm]

Shipping (Package) Weight 4.8 lb [2.2 kg]

What's in the Box

Included in Package

- 1 - Vertical Wallmount Bracket
- 16 - M5 Cage Nuts
- 16 - M5 Screws
- 6 - Wood Screws

1 - Instruction Manual

****Product appearance and specifications are subject to change without notice.***

