

2-Port USB 2.0 Desktop Extension Cable (M/2xF), 5 ft. (1.52 m)

MODEL NUMBER: **U024-005-DSK2**



Converts your computer's USB-A port to 2 USB-A ports and extends them up to 5 ft away. Ideal for connecting thumb drives, digital cameras and other USB-A devices.

Features

Expands an Existing USB-A Port to 2 Ports and Extends Them an Extra 5 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Features one USB 2.0 data/power port and one power-only port
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors for optimal signal quality
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

Specifications

OVERVIEW	
UPC Code	037332199348
Technology	USB; USB 2.0 (High Speed)

Highlights

- Features one USB 2.0 data/power port and one power-only port
- Supports data transfer rates up to 480 Mbps
- Premium foil and braid shielding
- Backward compatible with earlier USB generations
- Twisted 28/24 AWG data/power lines

System Requirements

- Computer, laptop or other device with USB-A port

Package Includes

- U024-005-DSK2 2-Port USB 2.0 Hi-Speed Desktop Extension Cable (M/2xF), 5 ft.



PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	4.5mm
Cable Jacket Rating	VW-1
Cable Length (ft.)	5
Cable Length (m)	1.5
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	13.49 x 10.01 x 1.27
Shipping Dimensions (hwd / in.)	5.31 x 3.94 x 0.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 5V 0.5A (2.5W)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>