

“Grand Prix” GX-Series Fire Rated Safes

The Gardex® Grand Prix line of UL® certified fire and impact-rated safes was designed for any business to properly protect critical documents from devastating fire. With a combination lock included standard, you can rest assured that the information vital to the operation of your business is safe from fire and prying eyes.

Choose from four sizes plus our over-sized ledger safe (GX-5020) Gardex® certified for 2 hours in a fire.

- 5 sizes ranging from 2 cubic feet up to more than 12 cubic feet of capacity
- UL® Class 350 1-hour fire and impact rating on all but the GX-5020 (manufacturers certified 2-hour fire rating)
- Gard-Lite Insulation — Exclusive and proprietary
- Caster base integral on all models
- Adjustable shelf / shelves included
- Mechanical Combination locks all models
- Textured Finish — durable and scratch-resistant. Available in beige only
- Gardex® 5-year warranty against manufacturers defects in material and workmanship
- Lifetime fire replacement warranty. Gardex® will replace your safe if it's damaged while protecting your vital records from a fire



Model GX-2, 2-shelf
Model GX-4, 4-shelf
 UL® Fire and Impact-rated Safes
 See chart below for all available models and sizes.

AVAILABLE MODELS

GX SERIES FIRE SAFES - U.L. LISTED 177°C (350°F) – 1 HOUR Fire and Impact Label								
Model	Outside dimensions inches (millimetres)			Inside dimensions inches (millimetres)			Weight	Capacity
	Height	Width	Depth	Height	Width	Depth	lb (kg)	ft³ (litres)
GX-1 1-shelf	24 (610)	18 1/2 (470)	18 1/2 (470)	17 1/2 (445)	15 1/2 (394)	12 1/2 (318)	168 (76)	2.2 (60)
GX-2 1-shelf	29 (737)	21 1/2 (545)	21 1/2 (545)	22 3/8 (568)	18 1/2 (470)	15 3/8 (390)	252 (114)	3.92 (111)
GX-3 3-shelves	39 (990)	26 1/2 (673)	26 1/2 (673)	32 1/4 (820)	23 1/2 (598)	20 3/8 (518)	480 (218)	9.36 (265)
GX-4 4-shelves	50 1/2 (1283)	26 1/2 (673)	26 1/2 (673)	42 1/4 (1073)	23 1/2 (598)	20 3/8 (518)	560 (254)	12.29 (348)

GX-5020

GX-5020 - Manufacturer Certified 177°C (350°F) – 2 HOUR Fire Label								
Model	Outside dimensions inches (millimetres)			Inside dimensions inches (millimetres)			Weight	Capacity
	Height	Width	Depth	Height	Width	Depth	lb (kg)	ft³ (litres)
GX-5020 3-shelves	60 (1525)	26 1/2 (673)	26 1/2 (673)	50 (1270)	20 (508)	20 (508)	880 (400)	11.57 (328)