



SLK-101C-M

Backlit Mobile Industrial Keyboard with QuickLock™

iKey's SlimKey® SLK-101C-M keyboard provides full-size versatility in a rugged, compact design. Designed for easy cleaning, the SLK-101C-M features an integrated "QuickLock®" to disable the keyboard functions during cleaning procedures. It also features green LED backlit keys for use in areas with minimal lighting.

Engineered for NEMA 4X protection from dust, water and corrosive liquids, the SlimKey SLK-101C-M is ideal for use in industrial, medical and material handling applications. Its large numeric pads allow for easy data entry, while its robust polycarbonate cases have built-in mounting holes for convenient vehicle use.

Features:

- 10-Key Numeric Pad
- 12 Function Keys
- Built-In Mounting Holes (8-32 Threaded Inserts in 2.5" x 2.5" and AMPS 1.188" x 1.5" Patterns)
- Green LED Backlit Keys
- MS Windows™ Function Keys
- USB configurations available
- Silicone Rubber
- Desktop
- Polycarbonate
- QuickLock®

Product Code SLK-101C-M

CERTIFICATIONS	NEMA 4X UL60950, FCC Part 15 Class B
SHOCK	3x11 ms pulses of 50g on each of 3 axis
CABLE	LENGTH: 10' straight USB (3 m)
KEY SWITCH	MATERIAL: Industrial silicone rubber LIFE: 10 million cycles TRAVEL: 0.055 in. (1.4mm) ACTUATION FORCE: 7.05 oz. +/- 1.06 oz. (200g +/- 30g) FEEDBACK: Tactile with mechanical snap
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2 kHz DURATION OF TEST PER AXIS: 3 hours
MOUNTING	VESA Mounting Pattern: 8-32 Threaded Inserts in 2.5" x 2.5" and 1.188" x 1.5" Patterns)
POWER	USB: 210mA@5V (from CPU port)
FLAMMABILITY	PRINTED CIRCUIT BOARD: 94 VO SILICONE OVERLAY: 94HB



COMPATABILITY	USB: All Windows and Macintosh OS
TEMPERATURE RANGE	STORAGE: -40C to +90C (-40F to +194F) OPERATING: -40C to +70C (-40F to +158F)
WEIGHT	2 lbs +/- 0.10 lbs (0.91 kg +/- 0.05 kg)
WARRANTY	1 Year Limited Warranty
HUMIDITY	100% Humidity Resistant
DIMENSIONS	14.74" x 5.69" x 1.61" (w-h-d) 374.4mm x 144.5mm x 40.9mm
MODEL NUMBERS	SLK-101C-M-USB With USB cable