

Heavy Duty 2-Post Rack - 12U

Product ID: 2POSTRACK12



This 2-post rack stands on your floor or desktop to provide 12U of storage space for EIA-310-D compliant 19" rack-mount devices, such as telecommunication and A/V equipment. The rack creates a robust storage solution, with support for a total load capacity of 160 kg (350 lb.).

Save space and cost, without losing weight capacity

This compact 2-post mounting solution offers a small footprint, and it's engineered to provide exceptional stability, with a total weight capacity of up to 160 kg (350 lb.). The rack fits in virtually any environment, and can be positioned on any surface, such as your floor, desk or table.

Save money, with a cost-effective, compact shipping package

The 2-post server rack comes in a flat-packed box to reduce shipping volume, which also significantly reduces your costs in shipping. The rack is packaged efficiently, so you can easily store it for deployment at a later date.

Hassle-free hardware installation, with tool-less clip nuts

To help make your equipment install easier, this rack includes tool-less clip nuts that seamlessly work with the punched round holes featured on this rack. The tool-less clip nuts provide an easy-to-install nut, unlike square cage nuts which can be a hassle.

The 2POSTRACK12 is backed by a lifetime StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility



Applications

- Use this cabinet to house your A/V equipment in a restaurant or bar, where space may be limited
- Rack-mount the equipment in your repair center or technology shop
- House equipment in audio-video editing rooms, or radio and television broadcast studios

Features

- Save space with a compact 2-post rack solution
- Get heavy-duty weight capacity up to 350 lb. (160 kg)
- Reduce your shipping costs with a flat-packed rack
- Easy equipment installation with tool-less clip nuts
- Maximize compatibility with EIA-310-D compliance
- 12U of rack space

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA RS310-D
	Mounting Options	Front Mount
	Rack Type	2-Post
	U Height	12U
	Wallmountable	No
Performance	Weight Capacity	160000 g [5648 oz]
Physical Characteristics	Product Height	611.1 mm [24.1 in]
	Product Length	304.8 mm [12 in]
	Product Weight	2.1 kg [4.6 lb]
	Product Width	517.4 mm [20.4 in]
Packaging Information	Shipping (Package) Weight	2.1 kg [4.6 lb]
What's in the Box	Included in Package	1 - right bracket
		1 - left bracket
		1 - top bracket
		1 - bottom bracket
		4 - rubber feet
		12 - 10-32 Phillips screws
		36 - 10-32 mounting screws
		36 - clip nuts
1 - instruction manual		

Product appearance and specifications are subject to change without notice.