


Key Features

SuperClear IPS Panel Technology | Seamless Viewing Experience | Versatile Connectivity | Ergonomic Design | Full HD 1080p Resolution



Product Description

With future-proof connectivity and advanced ergonomics, the ViewSonic® VG2253 is a productivity-boosting monitor perfect for corporate, government, and education environments. Designed with SuperClear® IPS panel technology for wide-angle viewing and incredibly vivid colors, this monitor also features a 3-sided thin-bezel design for a seamless viewing experience in multi-monitor setups. For maximum comfort and a customized fit, a robust fully ergonomic stand gives you tilt, pivot, swivel, and height-adjustable options. In addition, VDI client endpoints can be easily attached to the stand's integrated client mount, saving desktop space and minimizing cable clutter without interfering with ergonomic functionality. Extensive connectivity options include VGA, HDMI, DisplayPort, and Mini DisplayPort so that you can connect to a variety of HD and analog devices – today and tomorrow.



22" DISPLAY



IPS PANEL



1920 x 1080 RESOLUTION

Contact Sales

- call: 888.881.8781
- email: salesinfo@viewsonic.com
- visit: viewsonic.com

Display:

Type:	IPS
Colors:	16.7M
Color Space Support:	6-bit+A-FRC
Static Contrast Ratio:	1000:1
Viewing Angles:	178° horizontal, 178° vertical
Resolution:	1920 x 1080
Viewable Area (in.):	21.5
Dynamic Contrast Ratio:	20,000,000:1
Backlight Life (Hours):	30,000
Response Time (GTG):	5ms
Light Source:	WLED
Brightness:	250 cd/m2
Panel Surface:	Anti-glare, Hard coating (3H)
Aspect Ratio:	16:9
Display Size (in.):	22

Compatibility:

PC Resolution (max):	1920 x 1080
----------------------	-------------

Connector:

USB 3.0 Type A(2), USB 3.0 Type B(1), VGA(1), HDMI 1.4(1), Display Port(1), Mini Display Port(1)

Audio:

Internal Speakers:	2W (x2)
--------------------	---------

Power:

Eco Mode (Conserve):	13W
Eco Mode (optimized):	15W
Consumption (typical):	17W
Consumption (max):	41W
Voltage:	AC 100-240V (universal), 50-60Hz
Stand-by:	0.5W

Additional Hardware:

Kensington Lock Slot:	1
-----------------------	---

Controls:

Physical Controls:	1,2, Up, Down, Power
On Screen Display:	Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Advanced Image Adjust, Setup Menu, Memory Recall (See user guide for complete OSD functionality)

Operating Conditions:

Temperature:	32-104° F (0-40° C)
Humidity (non-condensing):	20-90%

Mount:

VESA Compatible:	100 x 100 mm
------------------	--------------

Video Signal:

Frequency Horizontal:	15 ~ 86KHz
Frequency Vertical:	24 ~ 76Hz

Video Input:

Analog Sync:	Separate Sync / Composite Sync / Sync on Green
Digital Sync:	TMD5, PCI-E

Ergonomics:

Height Adjust (mm):	135
Swivel:	360°
Pivot:	90°
Tilt (Forward/Back):	6° / 25°

Weight (imperial):

Net (lbs):	11.1
Net Without Stand (lbs):	6.7
Gross (lbs):	14.9

Weight (metric):

Net (kg):	5.1
Net Without Stand (kg):	3
Gross (kg):	6.8

Dimensions (imperial) (WxHxD):

Packaging (in.):	26.2 x 15.2 x 7.4
Physical (in.):	19.7 x 20.0 x 8.6
Physical Without Stand (in.):	19.7 x 11.9 x 1.8

Dimensions (metric) (WxHxD):

Packaging (mm):	665 x 394 x 187
Physical (mm):	499 x 509 x 218
Physical Without Stand (mm):	499 x 302 x 47

General:

Regulations: cULus, FCC-B, ICES003, Energy Star 7.0, EPEAT Gold, MX-CoC, Mexico Energy

PACKAGE CONTENTS: LCD Display, Power Cable (1.5m), Mini DP to DP Cable (1.5m), USB3.0 Upstream Cable (1.5m), Quick Start Guide, ViewSonic Wizard CD-ROM

Recycle/Dispose: Please dispose of in accordance with local, state or federal laws.

Warranty: Three-year limited warranty on parts, labor and backlight

UPC: 766907856316

Accessories:

CB-00008948, CB-00010555, CB-00010684, CB-00010958, LCD-CABLE-001, LCD-WMK-001, VSPF2150, cb-00011486