



# Xerox® VersaLink® C400 Color Printer and Xerox® VersaLink® C405 Color Multifunction Printer

Revolutionary. Future-proof. Value-packed.

# Xerox® VersaLink® C400 Color Printer and Xerox® VersaLink® C405 Color Multifunction Printer

The VersaLink C400 and C405 revolutionize workplace productivity with next generation features and easy, instant cloud and mobile connectivity. Built for the way you work today, and ready for where you grow tomorrow—with all the flexibility and versatility your business needs to work better with minimal IT support and maximum security.

## Powerful performance and peace of mind.

Right out of the box, you'll count on your VersaLink C400 or C405 to consistently and flawlessly perform the tasks that make your business work more efficiently. From IT-free installation wizards, to step-by-step configuration options, you're ready to go—hassle free.

VersaLink devices are loaded with features and time-saving Xerox technologies designed to speed up information sharing and reduce inefficient workflows. Ensure information accuracy with Scan and Fax preview<sup>1</sup>, and do more with scanned documents with built-in optical character recognition (OCR)<sup>1</sup>.

When it comes to safeguarding critical documents and data, VersaLink devices deliver a spectrum of stringent security features, including Secure Print and card authentication to control access.

With the VersaLink C400 and C405, you can be confident that your documents will look their best—making you look your best—giving you the confidence you need when presenting to your customers.

## Easy, efficient and entirely new.

With the customizable, capacitive 5-inch color touchscreen, you can tap, swipe and pinch your way through tasks and functions with mobile-like ease.

Preloaded Xerox® ConnectKey® Apps help optimize office efficiency, and on-screen access to the extensive Xerox® App Gallery provides expanded functionality—like the Xerox® Easy Translator Service app<sup>1</sup>, which quickly translates scanned documents into numerous languages.

Speed through tasks by saving common settings as presets for simple, single-touch job setup. With Simple ID, individual users and groups enter a user ID and password once, and then enjoy fast, secure, easy access to task-specific presets and commonly used apps on a personalized home screen.

## Freedom, and app-based functionality.

The VersaLink C400 Color Printer and VersaLink C405 Color Multifunction Printer gives you the freedom to work where and how you want—with out-of-the-box direct connectivity to Google Drive™, Microsoft® OneDrive® and DropBox™, and access to additional options through the Xerox® App Gallery.

The ability to connect and print from multiple devices is key for today's worker, and VersaLink devices meet the challenge with optional Wi-Fi and Wi-Fi Direct, plus Apple® AirPrint®, Google Cloud Print™, Xerox® Print Service Plug-in for Android™, Near Field Communication (NFC) Tap-to-Pair and Mopria®.

Learn more about why Xerox is the only choice for today's mobile professionals by visiting [www.xerox.com/mobile](http://www.xerox.com/mobile).

To learn more about VersaLink device features, go to [www.xerox.com/VersalinkEG](http://www.xerox.com/VersalinkEG)

<sup>1</sup> VersaLink C405 only

### Xerox® VersaLink® C400 Quick Facts


- Print up to 36 ppm Letter / 35 ppm A4
- NFC Tap-to-Pair and optional Wi-Fi and Wi-Fi Direct
- Standard 700-sheet paper capacity / Maximum 1,250 sheets
- 150-sheet Bypass Tray
- Up to 600 x 600 x 8 dpi

#### WxDxH:

19.3 x 19.2 x 15.7 in. /  
491 x 488 x 399 mm

#### Weight:

57 lb / 26 kg



### Xerox® VersaLink® C405 Quick Facts

- Print up to 36 ppm Letter / 35 ppm A4
- 50-sheet Single-pass Duplex Automatic Document Feeder (DADF)
- NFC Tap-to-Pair and optional Wi-Fi and Wi-Fi Direct
- Standard 700-sheet paper capacity / Maximum 1,250 sheets
- 150-sheet Bypass Tray
- Up to 600 x 600 x 8 dpi

#### WxDxH:

17 x 21.3 x 23.6 in. / 432 x 540 x 599 mm

#### Weight:

72 lb / 33 kg





### Choose the option best for your business:

- 1 A 50-sheet Single-pass Duplex Automatic Document Feeder (DADF) scans two-sided originals for copy, scan and fax jobs.
- 2 Card Reader Bay with embedded USB port.<sup>2</sup>
- 3 A front-side USB port<sup>2</sup> allows users to quickly print from or scan to<sup>3</sup> any standard USB memory device.
- 4 250-sheet output tray with tray-full sensor.
- 5 150-sheet Bypass Tray handles media sizes from 3 x 5 in. to 8.5 x 14 in. / 76.2 x 127 mm to 216 x 356 mm.
- 6 With the 550-sheet paper tray, standard paper capacity totals 700 sheets (including Bypass Tray).
- 7 Optional 550-sheet paper tray increases the total paper capacity to 1,250 sheets.
- 8 Optional stand provides storage for toner cartridges, paper and other supplies.

<sup>2</sup> USB ports can be disabled; <sup>3</sup> VersaLink C405 only.



Xerox® VersaLink® C400 Color Printer  
Print.



Xerox® VersaLink® C405 Color Multifunction Printer  
Print. Copy. Scan. Fax. Email.

### Introducing touch screen superiority.

Meet our tiltable, 5-inch capacitive color touch screen—the user interface that sets a higher standard for customization, personalization and versatility.

By presenting a familiar “mobile” experience—with support for gestural input and task-focused apps that share a common look and feel—fewer steps are needed to complete even the most complex jobs.

A highly intuitive layout guides you through every task from start to finish, with a natural hierarchy placing critical functions near the top of the screen and commonly used options front and center. Don't like where a function or app is located? Customize the layout to make it yours.

This unmatched balance of hardware technology and software capability helps everyone who interacts with the VersaLink C400 Color Printer and VersaLink C405 Color Multifunction Printer get more work done, faster.



# Xerox® VersaLink® C400 Color Printer and Xerox® VersaLink® C405 Color Multifunction Printer

Device Specifications	VersaLink C400/N	VersaLink C400/DN	VersaLink C405/N	VersaLink C405/DN
Speed	Up to 36 ppm color and black-and-white (Letter) / 35 ppm color and black-and-white (A4)			
Duty Cycle <sup>1</sup>	Up to 80,000 pages / month <sup>1</sup>			
Processor / Memory	1.05 GHz Dual-Core / 2 GB			
Connectivity	Ethernet 10/100/1000 Base-T, High-speed USB 3.0, Wi-Fi 802.11n and Wi-Fi Direct with optional Wi-Fi Kit (concurrent wired and wireless connections supported), NFC Tap-to-Pair			
Controller Features	Unified Address Book (C405), Configuration Cloning, Scan Preview (C405), Xerox Extensible Interface Platform®, Xerox® App Gallery, Xerox® Standard Accounting, Online Support (accessed from the user interface and print driver)			
Paper Handling	Standard	NA		
		<b>Single-pass Duplex Automatic Document Feeder (DADF):</b> 50 sheets; Custom Sizes: 5.5 x 5.5 in. to 8.5 x 14 in. / 140 x 140 mm to 216 x 356 mm		
		<b>Bypass Tray:</b> 150 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm		
Optional	<b>Tray 1:</b> 550 sheets; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm			
	<b>Tray 2:</b> 550 sheets; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm			
Paper Output	250 sheets			
Automatic Two-sided Printing	N/A	Standard	N/A	Standard
Print and Copy	Resolution	<b>Print:</b> Up to 600 x 600 x 8 dpi		
		<b>Copy:</b> Up to 600 x 600 dpi		
First-print-out Time	As fast as 13 seconds color / 12 seconds black-and-white			
First-copy-out Time	As fast as 11 seconds color / 8 seconds black-and-white			
Page Description Languages	PCL®5e / PCL 6 / PDF / XPS / TIFF / JPEG / HP-GL / Adobe® PostScript® 3™			
Print Features	Print from USB, Secure Print, Sample Set, Personal Print, Saved Job, Xerox® Earth Smart Driver Settings, Job Identification, Booklet Creation, Store and Recall Driver Settings, Bi-directional Real-time Status, Scaling, Job Monitoring, Application Defaults, Two-sided Printing (as default), Skip Blank Pages, Draft Mode			
Mobile Printing	Optional	Apple® AirPrint®, Google Cloud Print™, Xerox® Print Service Plug-in for Android™, Mopria® Print Service Plug-in for Android™		
		Visit <a href="http://www.xerox.com/officemobileapps">www.xerox.com/officemobileapps</a> for a list of downloadable apps available for smartphones and mobile devices.		
		@PrintByXerox®, Wi-Fi Direct Printing <sup>3</sup> , Xerox® Mobile Print Solution <sup>3</sup> , Xerox® Mobile Print Cloud <sup>3</sup> , Xerox® Mobile Link App (C405) <sup>2</sup>		
Printer/MFP Cloud Connectors <sup>2</sup>	Print from/Scan to <sup>4</sup> Google Drive, One Drive, DropBox, Microsoft 365, Box, DocuShare			
Cloud Services	NA	Xerox® Easy Translator Service, Xerox® Healthcare MFP		
Additional printer/MFP apps and cloud services available. Visit <a href="http://www.xerox.com/appgallery">www.xerox.com/appgallery</a> for a growing selection of apps.				
Scan	Scan Destinations	Scan to USB, Scan to Email, Scan to Network (FTP or Browse SMB)		
	Scan Features	NA	<b>File Formats:</b> PDF, PDF/A, XPS, JPEG, TIFF; <b>Convenience Features:</b> Scan to Home, Searchable PDF, Single/Multi-Page PDF / XPS / TIFF / Password Protected PDF, Linearized PDF / PDF/A	
Fax	Fax Features <sup>5</sup>	Walk-up Fax (includes LAN Fax, Direct Fax, Fax Forward to Email), Fax dialing via Unified Address Book (up to 2,000 contacts)		
Security	Standard	Firmware Verification, Security Certificates, Automatic Self-Signed Certificate Creation, Certificate Path Validation, Certificate Revocation Settings, Smart Card Enablement (CAC/PIV/.NET), FIPS 140-2, SSL/TLS, Port Filtering, IP Address Filtering, Domain Filtering, Cisco® TrustSec Identity Services Engine (ISE) Integration, HDD Overwrite, 256-bit Encryption, Secure Print, Secure Fax (C405), Secure Scan (C405), Secure Email (C405), Network Authentication, SNMPv3, Audit Log, Access Controls, Role Based Permissions, Convenience Authentication		
	Optional	Xerox® PrintSafe Software		
Accounting	Standard	Xerox® Standard Accounting (Print), Network Accounting Enablement		Xerox® Standard Accounting (Copy, Print, Scan, Fax, Email), Network Accounting Enablement
	Optional	Equitrac Express®, Equitrac Office®, YSoft® SafeQ®, other network accounting solutions available through various Xerox Business Innovation Partners		

<sup>1</sup> Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis; <sup>2</sup> Free option (download from Xerox® App Gallery to your printer/MFP); <sup>3</sup> Purchasable option; <sup>4</sup> Scan to available for C405 only; <sup>5</sup> Analog phone line required.

## Device Management

Xerox® Embedded Web Server, Xerox® CentreWare® Web, Email Alerts, Apple® Bonjour®

## Print Drivers

Windows® 7, 8, 10 Server 2000, Server 2003, Server 2008, Server 2008 R2 Server 2012, Mac OS® version 10.9 and higher, Citrix, Redhat® Enterprise, Linux®, IBM® AIX® 5, HP-UX® 11iv2, Oracle® Solaris 9, 10, Fedora Core 12-15, SUSE®, Xerox® Global Print Driver®, Xerox® Mobile Express Driver®

## Font Capability

136 PostScript fonts; 82 PCL fonts

## Media Handling

Single-pass Duplex Automatic Document Feeder: 16 lb. Bond – 45 lb. cover / 60 – 125 gsm; Bypass Tray and Trays 1 and 2: 16 lb. bond – 80 lb. cover / 60 – 220 gsm

## Operating Environment

Temperature: Storage: 32° to 95° F / 0° to 35° C; Operating: 50° to 90° F / 10° to 32° C; Humidity: 10% to 85%; Sound pressure levels: C400: Printing (Color): 53.1 dB(A), Standby: 29.2 dB(A); C405: Printing (Color): 52.3 dB(A), Standby: 28.7 dB(A); Sound power levels: C400: Printing (Color) 6.88 B(A), Standby: 5.0 B(A); C405: Printing (Color): 6.88 B(A), Standby: 5.0 B(A); Boot Time (from Off to UI Ready): as fast as 60 seconds, Warm-up Time (from Sleep to UI Ready): as fast as 6 seconds

Configurations vary by geography.

For more detailed specifications, go to [www.xerox.com/VersalinkC400Specs](http://www.xerox.com/VersalinkC400Specs) or [www.xerox.com/VersalinkC405Specs](http://www.xerox.com/VersalinkC405Specs).

For more information, visit us at [www.xerox.com/office](http://www.xerox.com/office).

©2017 Xerox Corporation. All rights reserved. Xerox®, Xerox and Design®, CentreWare®, Global Print Driver®, Mobile Express Driver®, Phaser®, Scan to PC Desktop®, WorkCentre® and Xerox eConcierge® are trademarks of Xerox Corporation in the United States and/or other countries. As an ENERGY STAR® partner, Xerox Corporation has determined that this product meets the ENERGY STAR guidelines for energy efficiency (DN configurations). ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. The information in this brochure is subject to change without notice. 2/17 BR20530 VC4BR-01UA

## Electrical

Power: Voltage: 110-127 VAC +/- 10%, Frequency: 50/60 Hz +/- 3 Hz, 10 A; Voltage: 220-240 VAC +/- 10%, Frequency: 50/60 Hz +/- 3 Hz, 6 A; Power consumption: C400: Standby: 76 watts or less, Printing: 705 watts or less, Sleep: 4 watts or less; C405: Standby: 82 watts or less; Printing: 750 watts or less, Sleep: 4 watts or less; ENERGY STAR® qualified (DN configurations)

## Dimensions (WxDxH)

C400: 19.3 x 19.2 x 15.7 in. / 491 x 488 x 399 mm; Weight: 57 lb. / 26 kg; C405: 17 x 21.3 x 23.6 in. / 432 x 540 x 599 mm; Weight: 72 lb. / 33 kg

## Certifications

To view the latest list of certifications, go to [www.xerox.com/OfficeCertifications](http://www.xerox.com/OfficeCertifications)

## Supplies

Extra High Capacity Print Cartridges:

Black: 10,500 pages std. pages<sup>1</sup> 106R03524  
Cyan: 8,000 pages std. pages<sup>1</sup> 106R03526  
Magenta: 8,000 pages std. pages<sup>1</sup> 106R03527  
Yellow: 8,000 pages std. pages<sup>1</sup> 106R03525

High Capacity Print Cartridges:

Black: 5,000 pages std. pages<sup>1</sup> 106R03512  
Cyan: 4,800 pages std. pages<sup>1</sup> 106R03514  
Magenta: 4,800 pages std. pages<sup>1</sup> 106R03515  
Yellow: 4,800 pages std. pages<sup>1</sup> 106R03513

Standard Capacity Print Cartridges:

Black: 2,500 pages std. pages<sup>1</sup> 106R03500  
Cyan: 2,500 pages std. pages<sup>1</sup> 106R03502  
Magenta: 2,500 pages std. pages<sup>1</sup> 106R03503  
Yellow: 2,500 pages std. pages<sup>1</sup> 106R03501

Routine Maintenance Items:

Imaging Unit (includes 4 imaging units):  
60,000 std. pages each<sup>2</sup> 108R01121  
Waste Cartridge: 30,000 std. pages<sup>2</sup> 108R01124

## Options

550-sheet Feeder 097S04400  
Productivity Kit with 320 GB HDD 097S04914  
Stand 497K13660  
Wireless Network Adapter (Wi-Fi Kit) 497K16750  
External Card Reader / RFID Kit (C400) 497K18380  
Internal Card Reader / RFID Kit (C405) 497K18120

<sup>1</sup> Average standard pages. Declared Yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.

<sup>2</sup> Approximate pages. Declared yield based on an average job size of 3 A4- / letter-size pages. Yield will vary depending on job run length and media size and orientation.

