

Serie | 4 Washing Machines

WAN24001GB

Automatic washing machine

Automatic washing machine with
EcoSilence Drive™: quiet operation and
durability that you can rely on.



- **EcoSilence Drive™**: extremely energy-efficient and quiet in operation with a 10-year warranty.
- **VarioPerfect™**: takes 65% less time or uses 50% less energy – delivers total flexibility.
- **Noise Level 54dB/74dB**: quiet washing and spinning.
- Easy operation with LED-Display and convenient control dial.
- **ActiveWater™**: saves water and costs thanks to a 2-step automatic load adjustment system.

Technical Data

Construction type :	Free-standing
Door hinge :	Left
Color / Material body :	White
Length of electrical supply cord (cm) :	210
Height for building under :	850.00
Height of the product (mm) :	848
Dimensions of the product (mm) :	848 x 598 x 550
Wheels :	No
Net weight (kg) :	69.0
Drum volume (l) :	55
Main colour of product :	White
Door Frame :	white-black grey
Noise level washing (dB(A) re 1 pW) :	54
Connection rating (W) :	2300
Current (A) :	10
Voltage (V) :	220-240
Frequency (Hz) :	50
Cord Included :	Yes
Plug type :	GB plug
Length of drain hose (in) :	59.05
Length of supply hose (in) :	59.05
Appliance Dimensions (h x w x d) (inches) :	x x
Dimensions of the packed product (in) :	33.85 x 25.19 x 25.19
Net weight (lbs) :	152
Gross weight (lbs) :	154
Length of drain hose :	150.00
Length of supply hose :	150.00
Gross weight (kg) :	70.0
Connection rating (W) :	2300
Current (A) :	10
Voltage (V) :	220-240
Frequency (Hz) :	50
Approval certificates :	CE, VDE
Water protection system :	Multiple water protection
Number of Options :	4
Spin speed options :	Variable
Digital countdown indicator :	Yes
Drying progress indicator :	LED, LED-display



Optional accessories

- WMZ20490 : Platform with pull-out
- WMZ2200 : Floor securing component
- WMZ2380 : Extension for cold water inlet /AquaStop

Serie | 4 Washing Machines

WAN24001GB

Automatic washing machine

Automatic washing machine with EcoSilence Drive™: quiet operation and durability that you can rely on.

- EcoSilence Drive
- VarioPerfect

Performance

- Energy Efficiency Class: A+++ -10%
- -10% more economical (157kWh/year) than the standard value (174 kWh/year) of energy efficiency class A+++ in category 7 kg according to the EU-order 1061/2010
- Capacity: 7 kg
- Maximum spin speed: 1200 rpm
Remaining moisture: 55 %
- B spin class
- Energy consumption :157 kWh per year, based on 220 standard washing cycles
- Energy consumption: standard 60 °C cotton programme 0.85 kwh full load and 0.69 kwh partial load and 40 °C cotton programme 0.51 kwh partial load
- Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.
- Water consumption 9020 litres per year, based on 220 standard washing cycles
- Programme time:60 °C cotton programme 200 min at full load 200 min at partial load and 40 °C cotton programme 200 min partial load
- Weighted power consumption off-mode / left-on mode: 0.12 W / 0.5 W
- Duration of the left-on mode: 15 min
- Drum volume: 55 litres
- Noise level washing : 54dB (A) re 1pW: Noise level spinning:74dB (A) re 1 pW

Programmes/functions

- Fully electronic control dial for all wash and special programmes
- Touch control buttons: Start delay, start/pause with reload function, SpeedPerfect, EcoPerfect, Spin speed reduction
- Special programmes: Aqua Plus, Mixed Load, Super Quick 15/30, Handwash/Wool, Delicates 30°C
- Safeguard monitoring system adjusts load distribution and programme settings to protect clothes

Key features

- Reload function: Be flexible in adding laundry items even after start of the wash cycle.
- VarioPerfect: speed or energy efficiency with perfect wash performance every time
- EcoSilence drive with 10 year warranty
- AntiVibration Design - for more stability and quietness

Additional features

- Large display for programme progress indication, spin speed, remaining time, 24 hour end time delay and load recommendation.
- 3D AquaSpa wash system with cascade for faster water penetration
- Reload facility
- Automatic load adjustment system
- Foam detection system
- Buzzer to indicate the end of cycle
- Multiple Water Protection
- Divider for Liquid Detergent
- Metal door catch
- Child lock

Technical Information

- Slide-under installation
- Dimensions (H X W X D): 84.8 x 59.8 x 55 cm
- Large white door with 180° opening and 30 cm porthole