

Product data sheet

Specifications



Rack PDU, Metered, 1U, 15A, 100/120V, (8) 5-15



AP7800B

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

| | |
|----------------------------------|--|
| Product or Component Type | PDU |
| PDU Type | Metered |
| Cord length | 12 ft (3.7 m) |
| Number of cables | 1 |
| Provided Equipment | Cord retention bracket(s) Installation guide Rack Mounting brackets User Manual |

Complementary

| | |
|---------------------------------|-----------------------|
| Input Voltage | 100 V 120 V |
| Height | 1.7 in (4.4 cm) |
| Width | 17.5 in (44.4 cm) |
| Output Voltage | 120 V |
| Depth | 4.02 in (10.2 cm) |
| Net Weight | 3.81 lb(US) (1.73 kg) |
| mounting location | Front Rear |
| Mounting preference | No preference |
| Input Plug Type | NEMA 5-15P |
| Mounting Mode | Rack-mounted |
| Rack units | 1U |
| Mounting position | Horizontal |
| Line Rated Current | 12 A |
| Input current limits | 15 A |
| Load Capacity | 1440 VA |
| Input Frequency | 50/60 Hz |
| Outlet type and quantity | 8 NEMA 5-15R |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|--|--|
| Product Certifications | cUL Listed CSA METI Denan UL Listed VCCI |
| Standards | FCC Part 15 class A ICES-003 UL 60950 |
| Ambient Air Temperature for Operation | 23.0000000000...113.0000000000 °F (-5...45 °C) |
| Relative Humidity | 5...95 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | -13.0000000000...149.0000000000 °F (-25...65 °C) |
| Storage Relative Humidity | 5...95 % |
| Storage altitude | 0...50000 ft (0.0000000000...15240.0000000000 m) |

Ordering and shipping details

| | |
|--------------------------|---------------------------|
| Category | 11309-APC RESALE PRODUCTS |
| Discount Schedule | APC1 |
| GTIN | 731304331452 |
| Returnability | No |
| Country of origin | PH |

Packing Units

| | |
|-------------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.5 in (6.4 cm) |
| Package 1 Width | 13.3 in (33.7 cm) |
| Package 1 Length | 18.5 in (47 cm) |
| Package 1 Weight | 6.42 lb(US) (2.91 kg) |

Contractual warranty

| | |
|-----------------|---------------------------|
| Warranty | 2 years repair or replace |
|-----------------|---------------------------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back RoHS/REACH

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
