

# Data Sheet

## FUJITSU Notebook LIFEBOOK A557 HD/FHD

### Your Essential Everyday Partner

The FUJITSU Notebook LIFEBOOK A557 delivers the right balance of essential business features offering a slim and light design for daily computing tasks at home or in the office. Its 39.6 cm (15.6-inch) outdoor-friendly anti-glare HD/FHD display offers a comfortable viewing for daily routines. The new textured cover combines professional looks with enhanced scratch resistance for everyday use. Convenient data entry is ensured with the num pad.

#### Powerful performance and essential security

Made to power your work day

- Latest 7th generation Intel® Core™ i5 processors, fast DDR4 memory and TPM 2.0 functionality

#### Reliable connectivity

Enjoy smoother video streaming and data transfer with a better coverage away from the router

- Intel® WLAN ac supporting Intel® Wireless Display technology, Bluetooth 4.0 Low Energy

#### Everyday security

Keep your data highly secure and protect yourself against virus attacks and other security threats

- Integrated BIOS and Intel® TPM 2.0 functionality

#### Rich choice of interfaces

Connect to your external monitor, the network or your headset with ease. The SD card slot allows you to extend the storage capacity or simply transfer data and pictures to your notebook

- HDMI, VGA, LAN and Audio port, SD card slot



# Components

Base unit	LIFEBOOK A557 i5 HD	LIFEBOOK A557 i5 FHD
<b>Operating systems</b>		
Operating system	Windows 10 Pro Windows 10 Home	Windows 10 Pro Windows 10 Home
<b>Memory modules</b>		
	4 GB (1 module(s) 4 GB) DDR4, 2,133 MHz, PC4-2133, SO DIMM	
	8 GB (1 module(s) 8 GB) DDR4, 2,133 MHz, PC4-2133, SO DIMM	
	16 GB (1 module(s) 16 GB) DDR4, 2,133 MHz, PC4-2133, SO DIMM	
<b>Hard disk drives (internal)</b>		
	SSD SATA III, 512 GB, 2.5-inch	
	SSD SATA III, 256 GB, 2.5-inch	
	SATA, 5,400 rpm, 500 GB, 2.5-inch, S.M.A.R.T.	
	SATA, 5,400 rpm, 1 TB, 2.5-inch, S.M.A.R.T.	
	DVD Super Multi	
<b>Multimedia</b>		
Camera	Built-in webcam (HD) with Status LED	Built-in webcam (Full HD) with Status LED
Camera notes	0.92 megapixels	1920x1080, 2.0 megapixel

## Base unit

Base unit	LIFEBOOK A557 i5 HD	LIFEBOOK A557 i5 FHD
<b>General system information</b>		
Processor	Intel® Core™ i5-7200U processor  (2 Cores / 4 Threads, 2.5 GHz, up to 2.9 GHz, 3 MB, Intel® HD Graphics 620)	
Chipset	Integrated	
Supported capacity RAM (min.)	4 GB	
Supported capacity RAM (max.)	32 GB	
Memory slots	2 DIMM (DDR4)	
Memory notes	Dual channel support DDR4 - 2133 MHz	
LAN	10/100/1,000 MBit/s Realtek RTL8111H	
Integrated WLAN	Intel Dual Band-AC7265 ac/b/g/n incl. 4.0 BT	
BIOS features	InsydeH20 Bios	
Audio type	On board	
Audio codec	Realtek ALC255	
Audio features	2x built-in speakers (stereo), Sound volume control via function key (down: Fn+F8; up: Fn+F9)	
Color	Black	Black
Material	Matt	Matt
<b>Display</b>		
Display	39.6 cm (15.6-inch), LED backlight, (HD), Anti-glare display, 1,366 x 768 pixel, 220 cd	39.6 cm (15.6-inch), LED backlight, (Full HD), Anti-glare display, 1,920 x 1,080 pixel, 250 cd
Display notes	ISO 9241-307 - Pixel class II eDP I/F	ISO 9241-307 - Pixel class II eDP I/F
Aspect ratio	16:9	16:9
Brightness - typical	220 cd	250 cd

**General system information**

Base unit	LIFEBOOK A557 i5 HD	LIFEBOOK A557 i5 FHD
Max. resolution external display	1,920 x 1,200 pixel	1,920 x 1,200 pixel
Graphics features	DirectX® 12	DirectX® 12
Graphics notes	Shared memory depending on main memory size	Shared memory depending on main memory size
Shared video memory	up to 1,695 MB	up to 1,695 MB

**Interfaces**

DC-in	1
Audio: line-in / microphone	audio in/out combi
Internal microphones	1x digital mic
USB 2.0 total	1
USB 3.0 total	3 (1 x Anytime USB Charge Functionality - depending on BIOS setting)
VGA	1
HDMI	1
Ethernet (RJ-45)	1
Memory card slots	SD/SDHC/SDXC

**Keyboard and pointing devices**

Spill-resistant isolated keyboard with number block  
 Touchpad  
 Status LED  
 Power Button

**Wireless technologies**

Antennas	WLAN x2
Bluetooth	v4.0
Integrated WLAN	Intel Dual Band-AC7265 ac/b/g/n incl. 4.0 BT
WLAN encryption	WEP, WPA, WPA2
WLAN notes	Import and usage according to country-specific regulations.

**Power supply**

AC Adapter	19 V / 90 W (4.74 A), 100 V - 240 V, 50 Hz - 60 Hz, Standard Adapter, 0.320 kg, 126x50x30 mm
Rated voltage range	100 V - 240 V (AC Input)
Rated frequency range	50 Hz - 60 Hz
1st battery	Li-Ion battery 6-cell, 4500 mAh, 48 Wh
Runtime 1st battery	tbd.
Battery notes	Battery life may vary depending on product model, configuration, applications, power management settings and features utilized. Battery recharge time depends on usage.

**Noise emission**

Noise emission	Please refer to the Eco Declaration	Please refer to the Eco Declaration
----------------	-------------------------------------	-------------------------------------

**Dimensions / Weight / Environmental**

Dimensions (W x D x H)	378 x 256 x 30.9 mm 14.88 x 10.08 x 1.22 inch
Weight	2.2 kg
Weight (lbs)	4.85 lbs
Weight notes	Weight may vary depending on actual configuration
Operating ambient temperature	5 - 35 °C (41 - 95 °F)
Operating relative humidity	20 - 80 %

**Product**

Compliance link	<a href="http://globalsp.ts.fujitsu.com/sites/certificates">http://globalsp.ts.fujitsu.com/sites/certificates</a>
-----------------	---

**Additional Software**

Additional software (preinstalled)	Adobe® Reader® (pdf reader) McAfee Internet Security and Antivirus Software (60 days trial version) Microsoft Office (buy license to activate the pre-installed Microsoft Office)
------------------------------------	---

**Additional Software**

Additional software (optional)	Nero Essentials XL Recovery DVD for Windows® CyberLink PowerDVD DVD (playback software for DVD)
--------------------------------	---

Additional software (included as a CD/DVD)	Drivers & Utilities DVD (DUDVD)
--	---------------------------------

**Manageability**

Manageability technology	WoL (Wake on LAN) PXE 2.1 Boot code
--------------------------	--

Manageability link	<a href="http://www.fujitsu.com/fts/manageability">http://www.fujitsu.com/fts/manageability</a>
--------------------	---

**Security**

Physical Security	Kensington Lock support	Kensington Lock support
-------------------	-------------------------	-------------------------

System and BIOS Security	TPM 2.0 functionality ( Intel® Platform Trust Technology)	TPM 2.0 functionality ( Intel® Platform Trust Technology)
--------------------------	---	---

User Security	User and supervisor BIOS password Hard disk password	User and supervisor BIOS password Hard disk password
---------------	---	---

**Warranty**

Warranty Terms & Conditions	<a href="http://support.ts.fujitsu.com/warranty">http://support.ts.fujitsu.com/warranty</a>
-----------------------------	---

**Product Support Services - the perfect extension**

Recommended Service	9x5, Onsite Response Time: Next Business Day
---------------------	--

Service Weblink	<a href="http://ts.fujitsu.com/Supportservice">http://ts.fujitsu.com/Supportservice</a>
-----------------	---

## Recommended Accessories

**Casual Backpack 16**



The Casual Backpack 16 is designed to fit an up to 15.6-inch widescreen notebook. It provides additional storage area, extra-large compartments and zip able pockets to store everything you need for work, school or travel including. This also includes an expandable file storage as well as a large separate zip-compartment to store books, accessories, and more. A small front pocket and two side mesh pockets complete the backpack. Shoulder straps and a top handle are padded for pleasant carrying comfort.

Order Code:  
S26391-F1192-L167

**Wireless Mouse W1200**



The Wireless Mouse W1200 uses the latest wireless 2.4 GHz technology, and a high-resolution 1000 dpi optical sensor to give you the precision and reliability you need. Sporting a compact design with a stylish black finish, the W1200 wireless mouse is well suited to all environments and to each user whether right or left handed.

Order Code:  
S26381-K462-L100

**SOUNDSYSTEM DS E2000 Air**



The new more powerful SOUNDSYSTEM DS E2000 Air gives you impressive, well-balanced sound throughout the frequency band. It is an unbeatable USB speaker set with a surprisingly small form factor. The robust satellite speakers are decorated with a deluxe piano finish and the base is adorned with warm ambient lighting.

Order Code:  
S26391-F7128-L600

**UC&C USB Value Headset**



The FUJITSU UC&C USB Value Headset is a lightweight bi-aural full-size stereo headset with high wearing comfort. This Lync-tested USB-Headset has an appropriate Inline-Controller which supports easy call management. A noise cancelling microphone facilitates undisturbing clear phone calls.

Order Code:  
S26391-F7139-L20

# More information

## Fujitsu OPTIMIZATION Services

In addition to FUJITSU Notebook LIFEBOOK A557 HD/FHD, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

### Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

### Computing Products

[www.fujitsu.com/global/products/computing/](http://www.fujitsu.com/global/products/computing/)

### Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about FUJITSU Notebook LIFEBOOK A557 HD/FHD, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website. [www.fujitsu.com/fts/mobile](http://www.fujitsu.com/fts/mobile)

## Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



**Green  
Policy  
Innovation**

## Copyrights

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2016 Fujitsu Technology Solutions GmbH

## Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

## CONTACT

Fujitsu Technology Solutions GmbH  
Website: [www.fujitsu.com/fts](http://www.fujitsu.com/fts)  
2016-10-14 CE-EN

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)  
© 2016 Fujitsu Technology Solutions GmbH