MC573dn Specifications



INCREASE PRODUCTIVITY, NOT YOUR COSTS – BY BRINGING LARGE OFFICE WORKFLOW APPLICATIONS TO YOUR SMALL-TO-MEDIUM SIZED OFFICE OR WORKGROUP

The MC573dn smart MFP utilizes reliable OKI LED print technology to produce excellent HD color output with a customizable scan / print document platform and secure cloud integration. Featuring SENDYS Document Explorer Lite with optional connectivity to Office 365™, Google Drive™ and DropBox™.

Key Features

- HD Color LED print technology with 7" Color LCD touch screen
- Google Cloud Print 2.0 ready enabling printing on the move and direct printing using Local Mode
- OKI's smart Extendable Platform 2 (sXP2)
- 1GB RAM memory, ensuring trouble-free printing of graphics-intensive documents
- Large 1,410-sheet paper capacity with optional 2nd and 3rd trays
- Smart MFP with duplex printing, scanning, copying, and faxing

Advanced Connectivity

- Print and scan direct with front facing USB port
- Wireless Direct offers safe simultaneous connection of wired and wireless networking
- Gigabit Ethernet enables fast transfer of large color files across the network
- Google Cloud Print 2.0 ready enabling printing on the move and direct printing using local mode
- Compatible with Apple AirPrint® for printing from smartphones and tablets
- Optional Wireless LAN Module available



Simple to set-up, use, and own

- Self-help and troubleshooting direct from touch screen
- Video guidance for installation and changing consumables
- As new features become available, update the device via the OKI portal





Cost and energy saving

- Print marketing materials in-house with outstanding print quality and media flexibility
- Deep Sleep mode saves energy, Auto-Off mode automatically powers down to less than 0.5W when not in use
- Toner Save to reduce cost, when printing draft or internal documents
- Duplex printing to reduce paper usage
- Robust and long-lasting OKI LED technology

Cloud Enabled MFP

- Connectivity to Office 365; Google Drive;
 DropBox via optional connectors
- Productivity workflow solutions to meet your specific business needs
- Operates from a customizable 7" color LCD touch screen
- Access to document management software SENDYS Explorer LITE at no cost
- Run third-party applications, such as PaperCut MF™; SENDYS; Drivve Image; among others
- Software development kit (SDK) available for rapid implementation of a custom solution



Security Features

- Keep documents confidential with Private Print (encrypted data transmission) and optional Card Release, so users can view all print jobs before selecting which ones to print
- Internet Protocol Security (IPSec) compliance, ensuring documents are safely sent and received

Letter / A4	1
Color / Mono	✓
Print / Copy / Scan / Fax	✓
1 – 20 users / Small Workgroup	✓

MC573dn COLOR MFP

Print Speed	Up to 31ppm Color/Mono ¹
Time to First Page	7.5 seconds Color/Mono¹
Processor	ARM Processor 667 MHz
Print Resolution	up to 1200 x 1200 dpi
Monthly Duty Cycle	Maximum 60,000 pgs/month Recommended up to 6,000 pgs/month
Operator Panel	7" Color Touch Panel
Memory	1GB RAM; 3GB eMMC (Program + font area: 0.25GB, Data Storage Area: 2.75GB)
Scanner	
Scan Speed	As fast as 30ipm
Optical Resolution	600 x 600 dpi
Document Input	50 sheet Reverse Automatic Document Feeder (RADF), flatbed scanner
Address Book	LDAP, 1000 locations, 32 Group Addresses
Format	S/M-PDF, S/M-Secure PDF, S/M-TIFF (RAW/JPEG/MMR Compressed), JPEG (color, grayscale only), XPS, S/M-Hi compression PDF, PDF/A
Scan-to Copy	Email, Shared folder (CIFS/FTP/HTTP), USB, Local PC, Remote scan
	Up to 31cpm Color/Mono
First Copy Out	Less than 12 sec Color / Mono
Copy Resolution	Up to 600 x 600 dpi
Copy Scaling	25% – 400%
Max Copies	999
Fax Speed	Duplex, ID Card, Collate, Mixed Originals, Edge Erase, Watermark ITU-T G3 (Super G3) up to 33.6kbps, Approx. 2 seconds/page
Fax Resolution	Std, Fine, Ex-Fine, Photo
Connectivity	RJ11x2 (Line/Tel), PSTN, PBX Line
Fast Dialing	40 one-touch dials (8x5 using shift key); 1000 speed dials
Fax Memory	256MB (Approx. 8,000 pgs)
Fax Function	Fax Preview, Automated Delivery, Redial, TEL/TAD/FAX auto switching, Block Junk Fax, Edge Erase, PC Fax, Internet Fax (T.37), Background Removal
Interface and Software	
Connectivity	USB 2.0 Device, 10Base-T/100Base-TX/1000Base-T, Host USB x 2 (front); Wireless (Option) IEEE802.11a/b/g/n
Printer Languages	PCL6 (XL3.0) and PCL5c, Postscript 3 (emulation), IBM-PPR, EPSON-FX, XPS, PDF (V1.7)
Network Protocols	TCP/IPv4&v6, NetBIOS over TCP, DHCP, DHCPv6, BOOTP, HTTP, HTTPS, DNS, DDNS, WINS, UPNP, Bonjour, SMTP, SMTPS, POP3, SNMPv1&v3, SNTP, IPP, IPPS, WSD Print, WSD Scan, LLTD, IEEE802.1X, LPR, Port9100, Telnet, FTP, FTPS, IPSec, AirPrint, Google Cloud Print 2.0, WLAN IEEE802.11a/b/g/n, WEP, WPA(Personal, Enterprise), WPA2(Personal, Enterprise)
Operating Systems	Vista (32-bit & 64-bit) / Server 2008 (32-bit & 64-bit) / Windows 7 (32-bit & 64-bit) / Server 2008 R2 (64-bit) / Windows 8 (32-bit & 64-bit) / Server 2012 (64-bit) / Windows 8.1 (32-bit & 64-bit) / Server 2012 R2 (64-bit) / Windows 10 (32-bit & 64-bit); Linux PPD; Mac OS X 10.8.5 to 10.11
Utility Suite	Configuration Tool ⁵ , Color Correct Utility, Color Swatch Utility ⁵ , Driver Installer ⁵ , Firmware Update Tool, Front End Installer ⁵ , LPR Utility ⁵ B, Network Card Setup ⁶ , Network Extension ⁵ , PDF Print Direct ⁵ , Print Job Accounting Client, Profile Assistant ⁶ , PS Gamma Adjuster, Scanner Driver (ICA) ⁶ , smart PrintSuperVision5, Template Manager ⁵ , Universal FAX Driver ⁵ , Universal Scanner Driver (TWAIN) ⁵ , Universal Scanner Driver

ne	

Printer Fonts	Scalable: 87 PCL fonts, 80 PostScript fonts
Bitmap Fonts	4 PCL fonts (Line Printer, OCR-A/B, USPS ZIP Barcode)
Barcode	10 types of one dimension with 26 variations: UPC-A, UPC-E, EAN/JAN-8, EAN/JAN-13, Interleaved2of5, Code39, Code 128, EAN/UCC-128, CODABAR, ZIP+4POSTNET; 2 types of two dimensions: PDF417, QR code

Paper Handling

i aper nanaang		
Input Capacity	350 sheets of 80gsm Standard (250-sheet Main Tray + 100-sheet Multi-Purpose Tray); 1,410 sheets Max (with Optional 530-sheet 2nd & 3rd Trays)	
Paper Sizes	Main Tray from 3.9" x 5.8" to 8.5" x 14"; Multi-Purpose Tray from 2.5" x 3.5" to 8.5" x 52" banners; Duplex/Optional Trays from 5.8" x 8.3" to 8.5" x 14"	
Paper Weight	Main Tray / Duplex / Option Trays 16-47lb Bond (64-176gsm); Multi-Purpose Tray 16-58lb Bond (64-220gsm)	
Paper Output Capacity	Main Output Bin 150 sheets face down	
Duplex (2-sided) Printing	Yes	

Environmental

Size (WxDxH)	16.8" x 22.7" x 18.6" (427mm x 576mm x 472mm)
Weight	Approx. 68 lbs (31 kg)
Acoustic Noise	Operating 54dBA (print/copy); Standby 37dBA; Power Save Inaudible
Power Consumption	Typical: 670W; Max: 1240W; Idle: 100W; Power Save: <20W; Deep Sleep: <1.5W; Auto-Off: <0.5W

Warranty

7	
Printer	1-Year On Site ²
LED Printheads	5-Year limited warranty ²

OKIcare® WARRANTY ENHANCEMENT PROGRAMS (ORDER NUMBERS)

2-Year On-Site	38043112
3-Year On-Site	38043113
4-Year On-Site	38043114
5-Year On-Site	38043115

lote: All Warranty Enhancement Program options extend the <u>total warranty coverage period</u> from the late of purchase to the number of years listed for each order number above.

H/W

MC573dn, 120V 62447301

Consumables (Order Numbers)

Toner cartridges ³ (3,000 pages)	Cyan: 46490503; Magenta: 46490502; Yellow: 46490501
Toner cartridge ³ (3,500 pages)	Black: 46490504
High capacity toner cartridges³ (6,000 pages)	Cyan: 46490603; Magenta: 46490602; Yellow: 46490601
High capacity toner cartridge ³ (7,000 pages)	Black: 46490604
Image drums ⁴ (30,000)	Cyan: 46484103; Magenta: 46484102; Yellow: 46484101; Black: 46484104

Options (Order Numbers)	
530-sheet 2nd/ 3rd Paper Tray	46361801
Cabinet w/ Casters	46567702
IEEE802.11a/b/g/n Wireless	45830201










$Specifications\ are\ subject\ to\ change\ without\ notice.$



© 2019 Oki Data Americas, Inc. OKI Reg. T.M., M.D., Oki Electric Industry Co., Ltd. Adobe Reg. T.M., PostScript 3 T.M., Adobe Systems, Inc. PCL Reg. T.M., Hewlett-Packard Co. Windows, Windows Vista Reg. T.M., Microsoft Corp. XPS Reg. T.M., Dell, Inc. Mac Reg T.M., Apple Inc. Harlequin Reg. T.M., MultiRIP, DirectPrint, T.M., Global Graphics Software Ltd. EFI Reg. T.M., Electronics for Imaging, Inc. AirPrint and the AirPrint logo are trademarks of Apple Inc. Google Cloud Print is a

Oki Data Americas, Inc.

USA

8505 Freeport Pkwy., Suite 600 Irving, TX 75063 Tel: 800.OKI.DATA (800.654.3282) Fax: 856.222.5320

www.oki.com/us

Canada

5800 Hurontario St., Suite 1020 Mississauga, Ontario L5R 4B9 Tel: 905.755.5800 Fax: 905.755.5840

www.oki.com/ca



trademark of Google Inc.

¹ Published performance results based on

laboratory testing. Individual results may apply. ² Available in the U.S. and Canada only.

³ Average A4 continuous print page yield in accordance with ISO/IEC 19798. Individual results may vary. Printer shipped with toner for 2,000

A4 pages. ⁴ Estimated average life, based on 3 pages per job.

⁵ Windows only.

⁶ Mac OSX only.