



19" Double Section Wallmount Cabinet

6U, Flatpack, Black, 600 mm (23.62") depth

Part No.: **713825**

Intellinet Double-Section wallmount cabinets offer you a flexible solution for your network installations. Since they ship flat-pack (unassembled)*, they save you space and money. High quality features include a 4MM toughened glass door, cold-rolled galvanized steel and antistatic powder coating on all panels. The rear door access to the back of the cabinet makes cabinet and component exchange a breeze.

*Completely assembled versions are available in certain countries.

Features:

- Flat Pack Design
- Ideal for 19" rackmount applications
- Maximum static load of 30 kg
- Cable entry via rear or top panel
- 4MM toughened glass door
- Rear door for easy access to back of cabinet
- Reversible Front door
- Cold-rolled, galvanized SPCC steel with up to 1.5 mm thickness
- Antistatic powder coating on all panels
- Ships Flatpacked
- Three-Year Warranty

Specifications:

General

- 19"
- Height: 6U
- Color: Black RAL7021

- Complies with: ANSI/EIA RS-310-D; IEC60297-2; DIN41494, Part 1; DIN41494, Part 7

Dimensions

- 327 (h) x 540 (w) x 600 (d) mm
- 12.87 (h) x 21.26 (w) x 23.62 (d) in

Package Contents

- 2 Rail frames
- Top, Bottom, Front, Back & Side Panels
- Installation hardware



