

## Duplex Singlemode 9/125 Fiber Patch Cable (LC/LC), Push/Pull Tabs, 3 m (10 ft.)

MODEL NUMBER: N370-03M-T



Premium singlemode fiber optic cabling transmits fast, clear data signals through your LAN with data transfer speeds up to 10 Gbps.

### Features

#### Fast, Clear Data Transmission Through Your LAN

- Data transfer speeds up to 10 Gbps
- Ideal for network equipment that requires singlemode fiber optic patch cables
- Attenuation loss meets or exceeds latest industry standards

#### LC Connectors with Push/Pull Tabs

- Push/pull tab connectors easy to install and remove with one hand
- Sturdy dual LC connectors tested to meet stringent insertion loss standards

#### Superior Construction for Error-Free Signal Transfer

- 9/125 duplex (zipcord) fiber made from glass
- Beveled edge on glass ends for easy plug insertion
- Yellow-colored for identification as singlemode
- FDDI- and OFNR-rated

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332202772 |
| Technology | Singlemode   |

### Highlights

- Attenuation loss meets or exceeds latest industry standards
- 9/125 duplex (zipcord) fiber made from glass
- LC male connectors meet insertion loss standards
- FDDI- and OFNR-rated
- Push/pull tab connectors install/remove with one hand

### System Requirements

- Fiber optic hardware or NIC card requiring singlemode duplex cable with LC/LC connectors

### Package Includes

- N370-03M-T Duplex Singlemode 9/125 Fiber Patch Cable, Push/Pull Tabs, 3 m



|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Optical Mode                        | OS2                                 |
| <b>PHYSICAL</b>                     |                                     |
| Color                               | Yellow                              |
| Clad Diameter                       | 125 micron                          |
| Core Diameter                       | 9 micron                            |
| Number of Fibers                    | 2                                   |
| Cable Length (ft.)                  | 9.8                                 |
| Cable Length (m)                    | 3                                   |
| Cable Length (in.)                  | 118.1                               |
| Shipping Dimensions (hwd / cm)      | 22.86 x 17.78 x 1.27                |
| Shipping Dimensions (hwd / in.)     | 9.00 x 7.00 x 0.50                  |
| Shipping Weight (kg)                | 0.02                                |
| Shipping Weight (lbs.)              | 0.05                                |
| <b>ENVIRONMENTAL</b>                |                                     |
| Operating Temperature Range         | -4 to 140 °F (-20 to 60 °C)         |
| Storage Temperature Range           | -4 to 140 °F (-20 to 60 °C)         |
| <b>COMMUNICATIONS</b>               |                                     |
| Network Speed                       | 10Gbps                              |
| <b>CONNECTIONS</b>                  |                                     |
| Side A - Connector 1                | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| Side A - Connector 2                | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| Side B - Connector 1                | LC DUPLEX (MALE) WITH PULL/PUSH TAB |
| <b>SPECIAL FEATURES</b>             |                                     |
| Push/Pull Tabs                      | No                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                     |
| Approvals                           | FDDI and OFNR rated                 |
| <b>WARRANTY</b>                     |                                     |
| Product Warranty Period (Worldwide) | Lifetime limited warranty           |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>