

HSM Pure 530

Small office shredder

Perfect for the workplace



- Made for everyday office use by 1 to 6 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Powerful motor allows for continuous operation
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Light barrier for automatic start/stop
- Mobile on castors
- Separate collecting bag for the sorted separation of the shredded material
- High quality wooden cabinet door
- Timeless machine design in trendy white
- Optional automatic external oiler for cross cut ensures long time cutting performance and quality
- Uses a 34 gallon capacity shred bag; Part #HSM1815



HSM Part#	HSM2351	HSM2353
Cutting type	Strip cut	Cross cut
Cutting size	1/4"	3/16" x 11/8"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	28 - 30	16 - 18
Cutting Speed	12.8 ft / min	12.8 ft / min
Throat opening	11.8"	11.8"
Motor power (horsepower)	0.67 hp	0.67 hp
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	28" x 19.5" x 14.25"	28" x 19.5" x 14.25"
Weight	60 lbs	65 lbs
Shred-bin volume	21 gal	21 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.