

HSM Pure 630

Solid and reliable paper shredder

Ideal for small work groups



- Made for office use by 6 to 11 users
- High quality materials and "Made in Germany" quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Powerful motor allows for continuous operation
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Light barrier for automatic start/stop
- Mobile on castors
- Separate collecting bag for the sorted separation of the shredded material
- High quality wooden cabinet door
- Optional automatic external oiler for cross cut ensures long time cutting performance and quality
- Timeless machine design in trendy white
- Uses a 34 gallon capacity shred bag; Part #HSM1815



HSM Part#	HSM2361	HSM2363
Cutting type	Strip cut	Cross cut
Cutting size	1/4"	3/16" x 11/8"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	40 - 42	25 - 27
Cutting Speed	17 ft / min	17 ft / min
Throat opening	11.8"	11.8"
Motor power (horsepower)	0.79 hp	0.79 hp
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	35" x 24.4" x 19"	35" x 24.4" x 19"
Weight	105 lbs	119 lbs
Shred-bin volume	34.3 gal	34.3 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.