

GCS62HDPKIT

2-Port HD Cable KVM with DisplayPort Adapters




2-Port Cable HDMI / DisplayPort KVM Switch

- Switch between two computers with the push of a button
 - Offers the flexibility to mix and match computer connections: HDMI and DisplayPort
 - Includes 2 x DisplayPort to HDMI adapters
 - No external power needed
 - Cost effective, Plug-N-Play solution
-
- Connect and control two HD or DisplayPort USB 2.0 interface computers with a single keyboard and mouse
 - Full 1080p and up to 1920 x 1200 @ 60Hz
 - Port switching via remote switch button, mouse or hotkeys
 - Hotkeys allows independent KVM and audio switching between computers
 - Includes 2.1 stereo sound and microphone support
 - USB 2.0 Peripheral Sharing via mouse port. Connect a powered USB Hub to expand your USB connectivity*
 - USB mouse and keyboard emulation for error-free boot-up and instantaneous recognition when switching computers
 - Power-On Detection – If one of the computers is powered off, it will automatically switch to the next powered-on computer
 - Re-programmable hotkey activation for keyboards without a scroll lock key
 - Keyboard emulation can be disabled to support gaming keyboard's special keys
 - Mouse emulation can be disabled to support mice with special keys
 - Digital Audio support
-
- HDCP Compliant
 - Multi OS platform support
 - Works with game consoles
 - Mac and Sun keyboard support
 - Firmware upgradeable
 - Plug-n-play; no software required
 - DisplayPort to HD Adapters:
 - Converts your DisplayPort to HDMI so you can connect to your HDMI projector, TV or monitor
 - Works with computer systems using DisplayPort
 - Compliant with Displayport Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
 - Support full DisplayPort link tracking
 - Supported resolutions:
 - Full HD 1080p
 - 1920x1200
 - Compliant with DVI 1.0 up to 1.65Gbps
 - Support interrupt request output for expansion function
 - Support Deep Sleep Mode (suspend mode)

*Mouse emulation must be disabled for this feature to function correctly





Requirements

Package Contents

- | | |
|--|--|
| <ul style="list-style-type: none"> • Console: • 1 x HDMI display • 1 x standard 104 key wired USB keyboard • 1 x standard 2 or 3 button wired USB mouse • • Computers: • 1 x HDMI or DisplayPort • 2 x USB ports • • Operating Systems: • Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10 • Mac OS® X 9 to 10.x • Oracle® Solaris • Linux®, Unix and other USB supported systems* | <ul style="list-style-type: none"> • 1 x GCS62HU • 2 x DisplayPort to HDMI Adapters • 1 x Installation Guide • 1 x Warranty Card |
|--|--|

**Additional drivers and support may be needed*

***IOGEAR's Display Emulation Technology provides the EDID support for Windows® 7*

Specifications

Function	GCS62HDPKIT
Computer Connections	
Direct	2
Console Connectors	
Monitor	1 x HDMI Female
Audio	1 x 3.5mm Mini Stereo Jack Female (Green)
Microphone	1 x 3.5mm Mini Stereo Jack Female (Pink)
Keyboard	1 x USB Type A Female
Mouse	1 x USB Type A Female
CPU Connectors	
Monitor	2 x HDMI Male; 2 x DisplayPort Male (with adapter)
Audio	2 x 3.5mm Mini Stereo Jack Male (Green)
Microphone	2 x 3.5mm Mini Stereo Jack Male (Pink)
Keyboard	2 x USB Type A Male (Purple)
Mouse	2 x USB Type A Male (Black)
LEDs	
On Line	2 x Green
Emulation	
Keyboard	USB
Mouse	USB
Scan Interval	3, 5, 10, 20 seconds (Default 5 seconds)
Environment	
Storage Temperature	-20~60°C
Operation Temperature	0~50°C
Humidity	0~80%; Non-condensing
Housing	
Case	Plastic
Video Resolution	1080p; 1920x1200
Port Selection	Remote Switch, Hotkey, and Mouse

Dimensions	GCS62HDPKIT
POP Information	
10" Peg Hook	5
6" Peg Hook	3
Unit Dimensions	
Height	2.5" (6.35cm)
Depth	1" (2.54cm)
Length	3.125" (7.93cm)
Unit Package Dimensions	
Width	6.5" (16.51cm)
Height	9.25" (23.49cm)
Depth	2.75" (6.99cm)
Master Carton	
Width	16" (40.64cm)
Height	9.5" (24.13cm)
Depth	7.5" (19.05cm)
Master Carton Qty.	6
Weight	
Master Carton Wt.	8.6lb (3.91kg)
Unit Pack Wt.	1.3lb (0.59kg)
Unit Wt.	.94lb (0.43kg)