

GCS922MDPKIT

## 2-Port USB DVI Cable KVM with MiniDisplayPort Adapters Bundle



### 2-Port Cable DVI / Mini DisplayPort KVM Switch

- Switch between two computers with the push of a button
- Offers the flexibility to mix and match computer connections: DVI and Mini DisplayPort
- Includes 2 x Mini DisplayPort to DVI adapters
- No external power needed
- Cost effective, Plug-N-Play solution


### DVI and Mini DisplayPort Mix & Match Solution

IOGEAR's DVI and Mini DisplayPort KVM Solution simplifies the method of sharing two computers using one DVI monitor, keyboard and mouse. This bundle is perfect for a home office or small / medium size business, as it offers the flexibility of choosing between DVI and/or Mini DisplayPort connections. Take advantage of your existing computers, and use the included Mini DisplayPort adapters to view your content on a DVI projector, monitor, or display. Streamline and develop efficient workstations to eliminate multiple desktop setups.


- Connect and control two DVI-D or Mini DisplayPort USB 2.0 interface computers with a single keyboard and mouse
- USB mouse port can be used for USB peripheral sharing, such as external storage drive
- Computer Selection via push-button Remote Port Selector
- Video resolution – up to 1920 x 1200 @60Hz
- Supports USB hot-plugging
- Power supply not required
- Mini DisplayPort to DVI Adapters:
  - Converts your Mini DisplayPort to DVI so you can connect to your DVI projector, TV or monitor.
  - Works with Apple® iMac® or MacBook®
  - Compliant with Mini DisplayPort Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
  - Support full Mini DisplayPort link tracking
  - Supported resolutions:
    - Full HD 1080p
    - 1920x1200
  - Compliant with DVI 1.0 up to 1.65Gbps
  - Support interrupt request output for expansion function
  - Support Deep Sleep Mode (suspend mode)



**Solution 1**



**Solution 2**



**Requirements**

**Package Contents**

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• <b>Console:</b></li> <li>• 1 DVI display</li> <li>• 1 set of USB keyboard and mouse</li> <li>•</li> <li>• <b>Computers:</b></li> <li>• 1 DVI-D Port or Mini DisplayPort</li> <li>• 1 USB Ports</li> <li>•</li> <li>• <b>Operating Systems:</b></li> <li>• Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10</li> <li>• Mac OS 9 to 10.x</li> <li>• Oracle® Solaris</li> <li>• Linux®, Unix and other USB supported systems*</li> </ul> | <ul style="list-style-type: none"> <li>• 1 x GCS922U</li> <li>• 2 x Mini DisplayPort to DVI Adapters</li> <li>• 1 x Quick Start Guide</li> <li>• 1 x Warranty</li> </ul> |
|---|--|

\*Additional drivers and support may be needed

## Specifications

Function	GCS922MDPKIT	Dimensions	GCS922MDPKIT
<b>Computer Connections</b>		<b>POP Information</b>	
Direct	2	10" Peg Hook	5
<b>Console Connectors</b>		6" Peg Hook	3
Monitor	1 x DVI-D Female	<b>Unit Dimensions</b>	
Keyboard	1 x USB Type A Female	Height	1.06" (2.69cm)
Mouse	1 x USB Type A Female	Depth	4.06" (10.3cm)
<b>CPU Connectors</b>		Length	3.44" (8.74cm)
Monitor	2 x DVI-D Male; 2 x Mini DisplayPort Male (adapters)	<b>Unit Package Dimensions</b>	
Keyboard & Mouse	2 x USB Type A Male	Width	6.13" (15.6cm)
<b>LEDs</b>		Height	8.81" (22.4cm)
On Line	2 x Green	Depth	2.25" (5.72cm)
<b>Video Resolution</b>		<b>Master Carton</b>	
1900x1200 @60Hz		Width	6.75" (17.1cm)
<b>Environment</b>		Height	15" (38.1cm)
Storage Temperature	-20-60°C	Depth	8" (20.3cm)
Operation Temperature	0-50°C	Master Carton Qty.	6
Humidity	0-80%; Non-condensing	<b>Weight</b>	
<b>Port Selection</b>		Master Carton Wt.	7.2lb (3.27kg)
Remote Switch		Unit Pack Wt.	1.1lb (0.5kg)
<b>Cable Length</b>		Unit Wt. w/accessories	0.85lb (0.39kg)
2 x 4ft. ea KVM cables; 1 x 6ft. Remote Switch		Unit Wt.	0.75lb (0.34kg)
<b>Cable Type</b>			
Bonded USB KVM			
<b>Housing</b>			
Case	Plastic		