

# Data Sheet

## FUJITSU Tablet LIFEBOOK T937

### Top Performer with a Twist

The FUJITSU Tablet LIFEBOOK T937 is a versatile 2 in 1 Ultrabook™ for demanding professionals with new dynamic work styles. Its ultra-thin, durable magnesium housing, just 19.8 mm height, and super lightweight design enable you to travel in comfort. With a simple flip of the super crisp, rotatable 33.8 cm (13.3-inch) FHD display with pen and touch support you can switch to tablet mode. The new backlit keyboard layout, enterprise-grade security features, pull-out LAN connector and embedded 4G/LTE let you work securely wherever you are. With the optional port replicator, maximum convenience in the office is ensured.

#### Tablet and Ultrabook™ in one

Give your work a personal touch and enjoy the benefits of precise handwriting recognition and multiple-touch

- Bi-directional rotatable 33.8 cm (13.3-inch) display with dual digitizer allows audit-proof pen and touch input, or with the keyboard



#### Ultimate mobility

Be available anytime anywhere with wireless connectivity and additional features that ease your life

- Optional 4G/LTE (incl. GPS), WLAN, Bluetooth, fast charging user-exchangeable battery, durable SSD options



#### Highest security

Protect your company data against unauthorized third-party access

- SmartCard reader, Palm Vein sensor, fingerprint sensor, OPAL encrypted drives and Trusted Platform Module (TPM)

#### Ergonomic working

Maximize your productivity with ultimate convenience and comfort features for business users

- Super high resolution Full HD (1920 x 1080) display options, backlit keyboard and optional port replicator



# Components

<b>Base unit</b>	LIFEBOOK T937
<b>Operating systems</b>	
<b>Operating system</b>	Windows 10 Pro. Fujitsu recommends Windows 10 Pro. Windows 10 Home
<b>Microsoft OS support information</b>	This system receives full support from Microsoft with Windows 10/Windows 10 Pro only. For any other Microsoft OS installed, this device has limited support from Microsoft. For more information, please see Microsoft's Support Lifecycle FAQ.
<b>Processor</b>	Intel® Core™ i7-7600U processor (3.9 GHz, up to 3.9 GHz, 4 MB) Intel® Core™ i5-7300U processor (3.5 GHz, up to 3.5 GHz, 3 MB) Intel® Core™ i5-7200U processor (3.1 GHz, up to 3.1 GHz, 3 MB)
	*Processor only for retail, SMB, education and government
	Intel® Core™ vPro™ Processor - Best Platform for Businesses of all sizes
	Intel® Core™ Processor with Intel® Small Business Advantage - Smart Platform for Unmanaged Small Business
<b>Memory modules</b>	4 GB (1 module(s) 4 GB) DDR4, 2,133 MHz, SO DIMM 8 GB (1 module(s) 8 GB) DDR4, 2,133 MHz, SO DIMM 16 GB (1 module(s) 16 GB) DDR4, 2,133 MHz, SO DIMM
<b>Hard disk drives (internal)</b>	SSD SATA III, 512 GB, OPAL capable SSD SATA III, 256 GB, OPAL capable SSD SATA III, 128 GB, OPAL capable PCIe-SSD, 512 GB, OPAL capable PCIe-SSD, 256 GB, OPAL capable
<b>Hard disk notes</b>	One Gigabyte equals one billion bytes, when referring to hard disk drive capacity. Accessible capacity may vary, also depending on used software. Up to 20 GB of HDD space is reserved for system recovery Internal storage interface: M.2 SATA
<b>Interface add on cards/components (optional)</b>	
<b>3G/4G (optional)</b>	LTE Sierra Wireless EM7455
<b>WLAN (optional)</b>	Import and usage according to country-specific regulations.
<b>Display</b>	33.8 cm (13.3-inch), LED backlight, (Full HD), Glare, magnesium, 1,920 x 1,080 pixel, 1,000:1,330 cd/m <sup>2</sup> 33.8 cm (13.3-inch), LED backlight, (Full HD), Anti-glare display, magnesium, 1,920 x 1,080 pixel, 1,000:1,330 cd/m <sup>2</sup>
<b>Multimedia</b>	
<b>Camera</b>	Built-in webcam (HD) with Status LED

## Base unit

<b>Base unit</b>	LIFEBOOK T937
<b>General system information</b>	
<b>Chipset</b>	Integrated in CPU
<b>Supported capacity RAM (max.)</b>	16 GB
<b>Memory slots</b>	1 DIMM (DDR4)
<b>Memory notes</b>	DDR4 - 2133 MHz
<b>LAN</b>	Built-in 10/100/1,000 MBit/s Intel® I219V
<b>LAN notes</b>	Intel I219-LM for AMT

**General system information**

<b>BIOS features</b>	InsydeH20 Bios
<b>Audio type</b>	On board
<b>Audio codec</b>	Realtek ALC255
<b>Audio features</b>	2x digital array microphones, 2x built-in speakers (stereo)
<b>Display</b>	33.8 cm (13.3-inch), (Full HD), Anti-Glare or Glare options, 1,920 x 1,080 pixel, 700:1, FHD - 330 cd/m <sup>2</sup>
<b>Display notes</b>	Wide-view high-bright LED display (for enhanced outdoor viewing). With magnesium display lid. Integrated ambient light sensor for automatic backlight adjustment to the working environment.
<b>Sensors</b>	3-axis Accelerometer Gyroscope Ambient Light Sensor Magnetic Field Sensor Compass
<b>Aspect ratio</b>	16:9
<b>Brightness - typical</b>	FHD - 330 cd/m <sup>2</sup>
<b>Contrast - typical</b>	700:1
<b>Digitizer / Touch Technology</b>	Wacom Digitizer for pen (AES) input plus capacitive 10 finger multi-touch screen
<b>Ambient light sensor</b>	Integrated
<b>Ambient light sensor notes</b>	While enabled, the ambient light sensor automatically adjusts the display backlight

**Graphics**

<b>Base unit</b>	LIFEBOOK T937
<b>TFT resolution (HDMI)</b>	up to 1,920 x 1,200
<b>TFT resolution (VGA)</b>	up to 1,920 x 1,200
<b>TFT resolution (DVI on Port Replicator)</b>	up to 1,920 x 1,200
<b>TFT resolution (DisplayPort on Port Replicator)</b>	up to 2,560 x 1,600
<b>Graphics brand name</b>	Intel® HD Graphics 620
<b>Graphics features</b>	3 Display Support (2 external, 1 internal)
<b>Graphics notes</b>	Shared memory depending on main memory size and operating system

**Interfaces**

<b>DC-in</b>	1
<b>Audio: line-out / headphone</b>	1 (combo port with Audio line-in)
<b>Audio: line-in / microphone</b>	1 (combo port with Audio line-out)
<b>Internal microphones</b>	2 (digital)
<b>USB 3.1 Gen2 total</b>	2 (incl. 1x Anytime USB Charge functionality, left side) Gen 1
<b>USB Type-C</b>	1
<b>VGA</b>	1
<b>HDMI</b>	1
<b>Ethernet (RJ-45)</b>	1
<b>Memory card slots</b>	1 SD up to 2GB, SDHC up to 32GB, SDXC up to 128GB
<b>SmartCard slot</b>	1 (optional)
<b>SIM card slot</b>	1 (only for models with integrated 4G/LTE)

**Port Replicator interfaces (optional)**

<b>DisplayPort</b>	1 (up to 2560 x 1600)
<b>Notes</b>	Port replicator supports 0-Watt functionality (made4you). Display port is shared with DVI - exclusive usage

**Keyboard and pointing devices**

	Backlit isolation keyboard Number of keyboard keys: 85, Keyboard pitch: 19 mm, Keyboard stroke: 1.2 mm Multi gesture touchpad with integrated mouse button functionality Tablet Pen, stored in pen garage Touch-screen
<b>Input devices (optional)</b>	Keyboard with multi gesture touchpad and 2 mouse buttons

**Wireless technologies**

<b>Antennas</b>	2x dual band for WLAN, 2x for LTE, Bluetooth shared with WLAN
<b>Bluetooth</b>	V 4.1
<b>WLAN encryption</b>	WEP, WPA, WPA2
<b>WLAN notes</b>	Import and usage according to country-specific regulations.
<b>Integrated LTE or UMTS</b>	LTE Sierra Wireless EM7455 (Cat. 6) (optional)
<b>LTE/UMTS/GPS notes</b>	Including GPS functionality Import and usage according to country-specific regulations.
<b>GPS</b>	Embedded in 3G/4G module if configured with WWAN

**Power supply**

<b>AC Adapter</b>	19 V / 65 W (3.42 A), 100 V - 240 V, 50 Hz - 60 Hz, 3-pin (grounded) slim and light AC-Adapter
<b>AC adapter</b>	19 V / 65 W (3.42 A)
<b>Notes</b>	65W AC Adapter for usage with system/ min. 90W AC Adapter for usage with Port Replicator
<b>Rated voltage range</b>	100 V - 240 V (AC Input)
<b>Rated frequency range</b>	50 Hz - 60 Hz
<b>1st battery options</b>	Lithium polymer battery 4-cell, 50 Wh
<b>Battery features</b>	Rapid Charge
<b>Runtime 1st battery</b>	up to 10 h
<b>Battery charging time</b>	~ 120min
<b>Battery notes</b>	Battery runtime information is based on worldwide acknowledged BAPCo® MobileMark® 2014 (office productivity). Refer to <a href="http://www.bapco.com">www.bapco.com</a> for additional details. The BAPCo® MobileMark® Benchmark provides results that enable direct product comparisons between manufacturers. It does not guarantee any specific battery runtime which actually can be lower and may vary depending on product model, configuration, application and power management settings. The battery capacity decreases slightly with every re-charge and over its lifetime.

**Dimensions / Weight / Environmental**

<b>Dimensions (W x D x H)</b>	318 x 224 x 19.8 mm back (w/o rubber feet) mm 12.64 x 9.25 x 0.76 back inch
<b>Weight</b>	from 1.3 kg
<b>Weight (lbs)</b>	3.5 lbs
<b>Weight notes</b>	Weight may vary depending on actual configuration (including battery pack)
<b>Operating ambient temperature</b>	5 - 35 °C (41 - 95 °F)
<b>Operating relative humidity</b>	Running: 20 - 80% (relative humidity); Packed: 20 - 80% (relative humidity)
<b>Product</b>	
<b>Compliance link</b>	<a href="http://globalsp.ts.fujitsu.com/sites/certificates">http://globalsp.ts.fujitsu.com/sites/certificates</a>

**Additional Software**

<b>Additional software (preinstalled)</b>	Adobe® Reader® (pdf reader) CyberLink YouCam (webcam software) Fujitsu Display Manager Fujitsu DeskUpdate (driver and utility tool) ShockSensor Utility Power Saving Utility Fujitsu Plugfree Network (network management utility) EasyGuide online user documentation Microsoft Office (buy license to activate the pre-installed Microsoft Office)
<b>Additional software (optional)</b>	Recovery DVD for Windows® Drivers & Utilities DVD (DUDVD) optional CyberLink PowerDVD BD (playback software for Blu-ray Disc™) CyberLink PowerDVD DVD (playback software for DVD) CyberLink YouCam (webcam software) Nero (backup and burning software)

**Manageability**

<b>Manageability technology</b>	DeskUpdate Driver management PXE 2.1 Boot code Wake up from S5 (off mode) WoL (Wake on LAN)
---------------------------------	--

**Manageability**

<b>Manageability software</b>	DeskView Client DeskView Instant BIOS Management
<b>DeskView components</b>	Inventory Management BIOS Management Driver Management Security Management Alarm Management
<b>Supported standards</b>	WMI (Windows Management Instrumentation) PXE (Preboot Execution Environment) DMI (Desktop Management Interface) SMBIOS (System Management BIOS) WBEM (Web Based Enterprise Management) CIM (Common Information Model) BootP (made4you)
<b>Manageability link</b>	<a href="http://www.fujitsu.com/fts/manageability">http://www.fujitsu.com/fts/manageability</a>

**Security**

<b>Physical Security</b>	Kensington Lock support
<b>System and BIOS Security</b>	Absolute Persistence® technology capable BIOS EraseDisk (optional) Optional: Trusted Platform Module (TPM 2.0)
<b>User Security</b>	Hard disk password User and supervisor BIOS password Embedded fingerprint sensor (optional) Workplace Protect (secure authentication solution) Smartcard reader (integrated) Integrated palm vein sensor (optional)

**Warranty**

<b>Warranty Terms &amp; Conditions</b>	<a href="http://support.ts.fujitsu.com/warranty">http://support.ts.fujitsu.com/warranty</a>
<b>Product Support Services - the perfect extension</b>	
<b>Recommended Service</b>	9x5, Onsite Response Time: Next Business Day
<b>Service Weblink</b>	<a href="http://ts.fujitsu.com/Supportservice">http://ts.fujitsu.com/Supportservice</a>

## Recommended Accessories

Order Code:  
S26391-F1657-L110



<b>Microsaver® DS Ultra thin</b>		The Fujitsu Kensington MicroSaver® DS Ultra-Thin notebook lock is the ultimate defense for even the thinnest notebooks. The patented T-bar locking mechanism along with an advanced carbon-tempered steel cable design provides excellent security. It also includes Kensington Master Access so you can manage an unlimited number of locks with a single master key.	Order Code: S26361-F1650-L900
----------------------------------	---	--	----------------------------------

**Sneaker Sleeve 14**



The Sneaker Sleeve 14 protects notebooks with up to 14-inch screens. The front half of the bag has dedicated compartments for your notebook, power cord, office supplies and personal items. The back half of the bag has an expanding, divided compartment for your files.

Order Code:  
S26391-F1194-L401

**Wireless Notebook Mouse WI410**



The Wireless Notebook Mouse WI410 is the perfect mouse for road warriors who don't want to bother with cables. It is compact enough to easily slip into a notebook bag or briefcase without getting in the way. It features two buttons and a scroll wheel which can also be used as a third button.

Order Code:  
S26381-K464-L100

**UC&C USB Headset Stereo H650e**



The UC&C USB Headset Stereo H650e is the ultimate in style and functionality. Long, uncomfortable work calls are a thing of the past thanks to the cushioned ear pads and crystal clear sound. Adjustable headband and microphone provides the perfect fit for everyone. Optimized for Microsoft® Lync™ the headset displays a red 'in-call' LED to let your co-workers know when you're available, thus helping to boost office productivity.

Order Code:  
S26391-F7139-L10

# More information

## Fujitsu OPTIMIZATION Services

In addition to FUJITSU Tablet LIFEBOOK T937, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

## Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

## Computing Products

[www.fujitsu.com/global/products/computing/](http://www.fujitsu.com/global/products/computing/)

## Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about FUJITSU Tablet LIFEBOOK T937, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.

[www.fujitsu.com/fts/tabletpc](http://www.fujitsu.com/fts/tabletpc)

## Copyrights

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2017 Fujitsu Technology Solutions GmbH

## Disclaimer

Technical data are subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.



## CONTACT

Fujitsu Technology Solutions GmbH

Website: [www.fujitsu.com/fts](http://www.fujitsu.com/fts)

2017-03-01 CE-EN

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2017 Fujitsu Technology Solutions GmbH