

ImageScan Pro® 820ix / 830ix

The right scanner for the job.

20ppm ▶▶

ImageScan Pro® 820ix
20ppm ADF Scanner
Model #DS820ix-AS
\$389⁹⁵

30ppm ▶▶▶

ImageScan Pro® 830ix
30ppm ADF Scanner
Model #DS830ix-AS
\$449⁹⁵



**45-Day
Free Trial**

**Nuance®
Power PDF
Software**

Adjust the automatic document feeder to easily scan different media sizes.

Simple three-button interface to select a scan job and start a scan.

Introducing the new and improved, ImageScan Pro® 820ix / 830ix

Depending on your need for speed, the ImageScan Pro 820ix and 830ix scan at 20 and 30 pages per minute (ppm) respectively and handle up to 3,000 pages per day making them our most cost effective ADF scanners when you have a single document or a stack of paper to digitize.

Capture clear images of everything from legal-size documents to letter size pages to insurance and ID cards. Paper or plastic doesn't matter.

Ideal industries:



Healthcare



Insurance



Banking & Finance



Real Estate & Construction



Professional Services & Consulting



Government & Legal



©2017 Ambir Technology, Inc. All rights reserved. The Ambir logo and ImageScan Pro are registered trademarks of Ambir Technology, Inc. Features, specifications and bundled software application(s) and/or version numbers of software applications are subject to change without notice. Windows is a registered trademark of Microsoft Corporation in the United States and other countries. All trademarks and registered trademarks are the property of their respective owners.

ImageScan Pro® 820ix / 830ix

Shouldn't your tools work as hard as you do?

Work smarter with the added efficiency of 2-sided (duplex scanning) in black and white, grayscale or color to any of the most popular file formats like JPG, TIFF or PDF. The enhanced TWAIN driver adds compatibility to countless business and productivity applications. Bundled with our easy to use utility AmbirScan ADF and a 45-day trial of Nuance Power PDF, you will be scanning documents with ease within minutes.

The 2-year warranty and US-based technical support and customer service combined with user-replaceable pads and rollers will allay any concerns about downtime or finding help when you need it most.

Durable, fast, productive.
Ambir and you.

Collapsible document trays ensure the ImageScan Pro 820ix/830ix fits on even the most crowded desks.



Every Ambir scanner comes with comprehensive, U.S.-based phone & online chat support.

Out of the box ability to scan crisp clean images, with advanced settings available for the most difficult scan jobs.

Specifications

Scanning Speed

820ix 20 ppm / 40 ipm (Monochrome Speed Duplex, 200 dpi)
20 ppm / 40 ipm (Color Speed Duplex, 200 dpi)

830ix 30 ppm / 60 ipm (Monochrome Speed Duplex, 200 dpi)
25 ppm / 50 ipm (Color Speed Duplex, 200 dpi)

ADF Capacity

50 Sheets (18 lb, 70 g/m²)
Note: Maximum ADF capacity varies, depending upon paper weight.

Scanning Features

Configurable Scan Buttons, Scan Functions: Scan to PDF, Scan to File Location, Scan to Application, Scan to FTP, Scan to Email, Scan to Printer

Image Processing: Auto Crop, Auto Deskew, Blank Page Removal, Page Rotation, Image Edge Fill, Remove Punch Holes, Continuous Scan, Multi-image Output, Advanced Threshold Adjustments

Counter Utility: Automatically counts the number of scans for feed roller and pad module replacements

Product Dimensions & Weight

10.36" x 5.19" x 5.83"
(263mm x 132mm x 148mm)

4.2 lbs (1.9 kgs)

Acceptable Paper Thickness

14 to 28 lbs (50 to 105 g/m²)

Acceptable Paper Sizes

Max: 8.5" x 200" (216mm x 5080mm)
Min: 2.5" x 2" (63.5mm x 50.8mm)

Plastic Card Scanning

Cards up to 1.2mm thick

Daily Duty Scans (sheets)

Up to 3,000

Optical Resolution

600 x 600 dpi

Scan Modes

Auto, Color (input 48-bit/output 24-bit)
Grayscale (input 16-bit/output 8-bit)
Black & White (1-bit)

Warranty

2 Year Limited Warranty

Service Options

1 Year Extended Warranty
(EW510-Y1), ImageScan Pro® 800 Series

Maintenance Kit, Post-Warranty – AmbirScan Repair Program