

**iQ300**  
**SN236W00MG white**  
**Dishwasher 60cm**  
**Freestanding ,**



**A++**

- ✓ Up to 66% faster dishwashing and drying to a gleaming shine with varioSpeed Plus.
- ✓ At the press of a button, the autoProgramme controls the entire dishwashing process for brilliant results.
- ✓ Very efficient dishwashing in energy efficiency class A++.
- ✓ aquaStop for a lifetime guarantee against water damage.

**Features**

**Technical Data**

Cleaning performance : A  
 Water consumption (l) : 9.5  
 Total annual energy consumption (kWh) 220 days : 205  
 Total annual water consumption (l) 220 days : 2090  
 Construction type : Free-standing  
 Removable work top : Yes  
 Door panel options : Not possible  
 Height of removable worktop (mm) : 815  
 Height of the product (mm) : 845  
 Adjustable feet : Yes - front only  
 Maximum adjustability feet (mm) : 20  
 Adjustable plinth : No  
 Net weight (kg) : 48.0  
 Gross weight (kg) : 53.0  
 Connection rating (W) : 2400  
 Current (A) : 13  
 Voltage (V) : 220-240  
 Frequency (Hz) : 60; 50  
 Length of electrical supply cord (cm) : 175  
 Plug type : GB plug  
 Length inlet hose (cm) : 165  
 Length outlet hose (cm) : 190  
 Hidden heating element : Yes  
 : Button suspension, Childlock appliance  
 Water softener (kWh) : Yes  
 Adjustable upper basket : Rackmatic 3-stage  
 Cup Shelf : 2  
 3rd Rack : 3rd Rack 1.1  
 Silverware Basket : Standard  
 Optional accessories : SZ72010, SZ73640  
 Included accessories 2 : baking-sheet spray head grey  
 Number of place settings : 14  
 Color / Material body : White  
 Color / Material top : White  
 Brand : Siemens  
 Product name / Commercial code : SN236W00MG  
 Number of place settings : 14  
 Energy efficiency class - NEW (2010/30/EC) : A++  
 Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 266  
 Energy consumption (kWh) : 0.93  
 Power consumption in left-on mode (W) - NEW (2010/30/EC) : 0.10  
 Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.10  
 Water consumption annual (l/annum) - NEW (2010/30/EC) : 2660  
 Drying performance : A  
 Reference programme : Eco  
 Total cycle time of reference programme (min) : 210  
 Duration of the left-on mode - NEW (2012/30/EC) (min) : 0  
 Noise level (dB(A) re 1 pW) : 46  
 Installation type : Built-under  
 Panel ready : No  
 Connection rating (W) : 2400  
 Current (A) : 13  
 Voltage (V) : 220-240  
 Frequency (Hz) : 60; 50  
 Energy Star Qualified : No  
 NSF certified : No  
 Plug type : GB plug  
 Required cutout/niche size for installation (in) : x x  
 Dimensions of the packed product (in) : 34.64 x 26.37 x 26.77  
 Net weight (lbs) : 105

**iQ300****SN236W00MG white****Dishwasher 60cm****Freestanding ,**

Features
<b>Performance</b> <ul style="list-style-type: none"><li>• Energy Efficiency Class: A++</li><li>• 14 place settings with varioDrawer on 3rd level</li><li>• Energy consumption in Eco 50 programme: 266 kWh per year, based on 280 standard cleaning cycles</li><li>• Water consumption in Eco 50 programme: 2660 litres per year, based on 280 standard cleaning cycles</li><li>• Programme time in Eco 50 programme: 210 minutes</li><li>• A rated performance for washing and A for drying</li><li>• Noise level dB (A) re 1pW: 46 dB</li><li>• Power consumption off-mode / left-on mode: 0.1 W / 0.1 W</li></ul>
<b>Programmes/functions</b> <ul style="list-style-type: none"><li>• 6 programmes: Intensive 70 °C, Auto 45-65 °C, Eco 50 °C, Glass 40 °C, Quick wash 45 °C, Pre-Rinse</li><li>• 3 special options: varioSpeed Plus, halfLoad, extraDry</li><li>• Machine Care - 30 cycle reminder to run cleaning programme</li></ul>
<b>Flexible design elements</b> <ul style="list-style-type: none"><li>• varioFlex baskets</li><li>• varioDrawer</li><li>• 3 stage rackMatic height-adjustable top basket</li><li>• 2 foldable plate racks in top basket</li><li>• 4 foldable plate racks in bottom basket, and 2 foldable cup racks in bottom basket</li></ul>
<b>Innovations and technology</b> <ul style="list-style-type: none"><li>• hydroDry hygienic and efficient drying</li><li>• dosageAssist detergent dispenser</li><li>• iQDrive motor</li><li>• Automatic detergent-aware system</li><li>• hydroSensor, loadSensor</li></ul>
<b>Design features</b> <ul style="list-style-type: none"><li>• Time delay: 1-24 hours with Remaining programme time indicator (minutes), water inlet indicator</li><li>• Internal water protection system</li><li>• LED salt refill indicator, LED rinse aid refill indicator</li><li>• Self-cleaning filter system with 3 piece corrugated filter</li><li>• Child safety - childproof door lock, Child safety - Tamperproof controls</li><li>• Dimensions (HxWxD): 84.5 x 60 x 60cm</li><li>• Efficiency information relates to the Eco 50 programme. This programme is suitable for cleaning normally soiled tableware and is the most efficient programme in terms of combined energy and water consumption.</li></ul>