

Serie | 6 Washing Machines

WAT28371GB Automatic washing machine

A+++

Washing machines with EcoSilence Drive™: enjoy supremely quiet operation and excellent durability.

- **EcoSilence Drive™:** extremely energy-efficient and quiet in operation with a 10-year warranty.
- Energy efficiency class A+++
- **VarioPerfect™:** takes 65% less time or uses 50% less energy – delivers total flexibility.
- **Allergy+/ECARF Quality Seal:** specially developed for the needs of allergy sufferers.
- **WaveDrum:** gentle washing thanks to a unique drum structure.
- Super Quick 30/15 washes, rinses and spins in just 30 minutes, if required in 15 minutes also.

Technical Data



Construction type :	Free-standing
Height of removable worktop (mm) :	848
Dimensions of the product (mm) :	848 x 598 x 590
Net weight (kg) :	70.0
Connection rating (W) :	2300
Current (A) :	10
Voltage (V) :	220-240
Frequency (Hz) :	50
Approval certificates :	CE, VDE
Length of electrical supply cord (cm) :	160
Washing performance class :	A
Door hinge :	Left
Wheels :	No
EAN code :	4242005039500
Capacity cotton (kg) - NEW (2010/30/EC) :	9.0
Energy efficiency class - NEW (2010/30/EC) :	A+++
Energy consumption annual (kWh/annum) - NEW (2010/30/EC) :	152
Power consumption in off-mode (W) - NEW (2010/30/EC) :	0.12
Power consumption in left-on mode - NEW (2010/30/EC) :	0.43
Water consumption annual (l/annum) - NEW (2010/30/EC) :	11220
Spin drying performance class :	B
Maximum spin speed (rpm) - NEW (2010/30/EC) :	1379
Average washing time cotton 40C (partial load) - NEW (2010/30/EC) :	270
Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC) :	275
Average washing time cotton 60C (partial load) - NEW (2010/30/EC) :	270
Duration of the left-on mode - NEW (2012/30/EC) (min) :	15
Noise level washing (dB(A) re 1 pW) :	49
Noise level spinning (dB(A) re 1 pW) :	75
Installation type :	Free-standing



4 242005 039500

Optional accessories

WMZ2200 : Floor securing component
WMZ2380 : Extension for cold water inlet /Aquastop

Serie | 6 Washing Machines

WAT28371GB

Automatic washing machine

Washing machines with EcoSilence Drive™: enjoy supremely quiet operation and excellent durability.

Performance

- Energy efficiency class: A+++
- Capacity: 9 kg
- Maximum spin speed: 1400 rpm
- B spin class
- Energy consumption :152 kWh per year, based on 220 standard washing cycles
- 30% more economical (152kWh/year) than the standard value (217 kWh/year)
- Energy consumption: standard 60 °C cotton programme 0.92 kwh full load and 0.6 kwh partial load and 40 °C cotton programme 0.42 kwh partial load
- Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.
- Weighted power consumption off-mode / left-on mode: 0.12 W / 0.43 W
- Duration of the left-on mode: 15 min
- Water consumption 11220 litres per year, based on 220 standard washing cycles
- Programme time:60 °C cotton programme 275 min at full load 270 min at partial load and 40 °C cotton programme 270 min partial load
- Drum volume: 70 litres
- Noise level washing : 49dB (A) re 1pW: Noise level spinning:75dB (A) re 1 pW

Programmes/functions

- Touch control buttons: start/pause with reload function, Spin speed reduction, Aqua Plus, SpeedPerfect, EcoPerfect and 24 hours Start delay
- Special programmes: Shirts, Sportswear, Mixed Load, Drain / Spin, Allergy +, Super Quick 15/30, Handwash/Wool, Delicates 30°C
- Safeguard monitoring system adjusts load distribution and programme settings to protect clothes

Key features

- Fully electronic control dial for wash programmes, temperature and special programmes
- ECARF Seal of Quality: allergy-friendly product
- VarioPerfect: speed or energy efficiency with perfect wash performance every time
- ActiveWater: water management system
- EcoSilence drive with 10 year warranty
- AntiVibration Design - for more stability and quietness
- Reload function: Flexibility in adding laundry items into the drum, even after the wash cycle has started.

Additional features

- Large LED-Display for programme status indication, temperature selection, spin speed, remaining time and 24 hours end time delay, load recommendation and consumption indication
- WaveDrum: gentle and efficient washing
- 3D AquaSpa wash system with cascade for faster water penetration
- Reload facility
- Easy cleaning detergent drawer
- Divider for Liquid Detergent
- Flow-through sensor for optimum water use
- Multiple Water Protection
- Continuous load adjustment
- Overdosage indication
- Foam detection system
- Child lock
- Buzzer to indicate the end of cycle

Technical Information

- Dimensions (H X W X D): 84.8 x 59.8 x 59 cm
- Slide-under installation
- Large white-black grey door with 171° opening and 32cm porthole opening