

IMMERSIVE IMAGERY FOR PRODUCTIVE PROFESSIONALS.



Lenovo™

VIEWING PERFECTION + EXCEPTIONAL CONVENIENCE

Immersive imagery, borderless screen and features for ultimate convenience. The Lenovo™ ThinkVision® P24h Monitor delivers exquisite detail across the 23.8" QHD (2560 x 1440) IPS-type screen, featuring factory-calibrated accuracy, flicker-free display and innovative TÜV eye comfort certification. The elegant design is enhanced with convenient one-cable connection for video, power and data. It's a perfect display solution for professionals and creatives alike.

WHY YOU SHOULD BUY THE LENOVO THINKVISION P24h MONITOR



Convenient one-cable connection

A single USB-C™ cable delivers video (DisplayPort™ 1.2), data (USB 3.0) and power to a notebook, tablet or smartphone. Plus, 5 digital ports make device connectivity easy.



Impressive QHD performance

QHD (2560 x 1440) resolution means exquisite detail across the 23.8" borderless IPS-type screen (1.77x more pixels than FHD). 99% sRGB color gamut ensures accuracy and consistency.



Elegant and user-friendly

90° pivot design and a compact footprint make this a perfectly stylish display for any home or office environment - perfect for multi-screen applications.

THE LENOVO THINKVISION P24h MONITOR IS BEST SUITED FOR

1 | Designers, engineers and other creative professionals who demand the most accurate, consistent color for highly-detailed work.

2 | Power users whose high-performance devices and advanced software require a display that enables maximum productivity.

3 | Young, technology-focused professionals who value the versatility of a monitor that delivers consistent performance with a variety of devices.



ThinkVision P24h MONITOR



SPECIFICATIONS

DISPLAY		DIMENSIONS (W x D x H)	
Panel Size	23.8" Wide	Size Packed (mm)	635 x 188 x 422
Panel Type	IPS	Size Packed (inches)	25" x 7.4" x 16.61"
Backlight	WLED	Size Unpacked with Stand (mm)	540.2 x 261.75 x 373.4
Resolution	2560 x 1440	Size Unpacked with Stand (inches)	21.26" x 10.3" x 14.7"
Aspect Ratio	16:9	Size Unpacked without Stand (Monitor Head Only) (mm)	540.2 x 46.45 x 325.98
Anti-Glare	Yes	Size Unpacked without Stand (Monitor Head Only) (inches)	21.26" x 1.82" x 12.83"
Borderless Screen	Yes	Stand Base Footprint Area (mm / inches)	250 x 250 / 9.84" x 9.84"
Screen Dimensions (W x H) (mm)	526.848 (H) x 296.352 (V)	Weight Packed	Starting at 19.73 lbs (8.95 kg)
Maximum Brightness (Typical)	300 cd/m ²	Weight Unpacked	Starting at 12.54 lbs (5.69 kg)
Viewing Angle (H/V at CR 10:1)	178°/178°	Weight Monitor Head Only	Starting at 8.42 lbs (3.82 kg)
Contrast Ratio (Typical)	1000:1		
Dynamic Contrast Ratio	3M:1	POWER CONSUMPTION	
Pixel Pitch (mm)	0.2058	Typical	24 W
Color Gamut (CIE 1931)	99% sRGB	Maximum	120 W
Display Colors (Typical)	16.7 Million	Sleep-Mode	<0.5 W
Response Time	4/6/14 ms (G-to-G)	Off-Mode	<0.5 W
		Power Supply	Internal
		Power Voltage	90 VAC - 264 VAC
SIGNAL INPUT			
Video Input Signals	2 x HDMI™ 1.4 + USB-C™ + DisplayPort™ 1.2 + DisplayPort™-Out		
Video Cables Supplied (Length)	USB-C™ - USB-C™ Cable (1.8 m)		
SIGNAL INTERFACE / PERFORMANCE			
Audio	Audio-Out		
OSD Languages	English, French, Italian, German, Spanish, Japanese, Chinese, Russian		
MECHANICAL		COMPLIANCE	
Tilt Angle (Front / Back)	-5° / 30°	Arsenic-Free Glass	Yes
Cable Management	Yes	PVC-Free	Yes
Kensington® Lock	Yes	Mercury-Free	Yes
VESA® Mounting	Yes (100 mm)	EPEAT™	Gold
Bezel Color	Raven Black	ENERGY STAR® Rating	7.0
Bezel Width		TCO	7.0
Top (mm / inches)	2 / 0.08"	TCO Edge	2.0
Bottom (mm / inches)	22 / 0.87"	TÜV Eye Comfort Certification.	Yes
Sides (mm / inches)	2 / 0.08"	RoHS (EU 2002/95/EC)	Yes
		China Energy Efficiency Standard	Tier 2
		Windows Certification	Windows 7 / Windows 10



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkServer, ThinkVantage and ThinkVision. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecom/ periodically for the latest information on safe and effective computing. ©2017 Lenovo. All rights reserved.