

# Data Sheet

## FUJITSU Tablet STYLISTIC R727

### Unlimited Usability and Productivity with 2 in 1

The FUJITSU Tablet STYLISTIC R727 with a 31.8 cm (12.5-inch) anti-glare display transforms into a full performance and full productivity notebook by simply attaching the strong yet slim magnetic keyboard. Its magnesium-aluminum housing delivers durability for business pros on the move, presenting in tablet mode or working in notebook mode anywhere you like. With the sensitive display you can naturally use a digital pen for notes or signatures on the tablet. Enterprise-grade connectivity like 4G/LTE, manageability and security features like encrypted drives and NFC-based authentication allow you to do your job wherever you want; all in confidence that your data is secure.

#### Powerful and responsive 2 in 1

Business tablet, business notebook, one device

- Transform a tablet into a full-fledged notebook by simply attaching the magnetic keyboard and unfolding the integrated tablet stand

#### Mobility first

Smart features for dynamic work styles

- Anti-glare display, durable yet thin & light magnesium-aluminum housing, flexible input options, UC&C capabilities, long runtime of up to 10 hours

#### Go-anywhere connectivity

Smart features let you do your job wherever you want

- Optional embedded 4G/LTE and NFC

#### Enterprise-grade manageability and security

Future-proof security features and remote management capabilities keep data safe

- Embedded NFC for contactless SmartCard authentication, encrypted drives, TPM and remote BIOS manageability

#### Best-in-class office comfort

Switch to a full desktop-like experience in no time

- Cradle to attach peripherals in the office



# Components

## Operating systems

<b>Operating system pre-installed</b>	Windows 10 Pro. Fujitsu recommends Windows 10 Pro. Windows 10 Home	Windows 10 Pro. Fujitsu recommends Windows 10 Pro. Windows 10 Home	Windows 10 Pro. Fujitsu recommends Windows 10 Pro. Windows 10 Home	Windows 10 Pro. Fujitsu recommends Windows 10 Pro. Windows 10 Home
<b>Operating system notes</b>	MS OS support information: Systems with 7th generation Intel processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see MS Support Lifecycle.	MS OS support information: Systems with 7th generation Intel processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see MS Support Lifecycle.	MS OS support information: Systems with 7th generation Intel processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see MS Support Lifecycle.	MS OS support information: Systems with 7th generation Intel processor receive support from Microsoft with Windows 10 Home / Windows 10 Pro only. For more information, please see MS Support Lifecycle.
*Processor only for retail, SMB, education and government				

## Hard disk drives (internal)

SSD SATA III, 512 GB, M.2 module, OPAL capable  
 SSD SATA III, 256 GB, M.2 module, OPAL capable  
 SSD SATA III, 128 GB, M.2 module, OPAL capable

## Hard disk notes

One Gigabyte equals one billion bytes, when referring to hard disk drive capacity.  
 Accessible capacity may vary, also depending on used software.  
 Up to 20 GB of HDD space is reserved for system recovery  
 Internal storage interface: M.2 SATA

## Interface add on cards/components (optional)

### Multimedia

**Camera** Front camera 2 megapixel, rear camera 5 megapixel with autofocus

# Base unit

## General system information

<b>Processor</b>	Intel® Core™ i3-7100U processor  (2 Cores / 4 Threads, up to 2.3 GHz)	Intel® Core™ i5-7200U processor  (2 Cores / 4 Threads, up to 2.8 GHz)	Intel® Core™ i5-7300U processor  (2 Cores / 4 Threads, up to 3.0 GHz)	Intel® Core™ i7-7600U processor  (2 Cores / 4 Threads, up to 3.4 GHz)
<b>Chipset</b>	Integrated in CPU	Integrated in CPU	Integrated in CPU	Integrated in CPU
<b>Supported capacity RAM</b>	4 GB	8 GB	8 GB	16 GB
<b>Memory slots</b>	LPDDR3 (1600 MHz)	LPDDR3 (1600 MHz)	LPDDR3 (1600 MHz)	LPDDR3 (1600 MHz)
<b>LAN</b>	Built-in 10/100/1,000 MBit/s Intel® I219V	Built-in 10/100/1,000 MBit/s Intel® I219V	Built-in 10/100/1,000 MBit/s Intel® I219LM	Built-in 10/100/1,000 MBit/s Intel® I219LM
<b>LAN notes</b>	LAN connector via optional cradle or optional USB adapter cable	LAN connector via optional cradle or optional USB adapter cable	LAN connector via optional cradle or optional USB adapter cable	LAN connector via optional cradle or optional USB adapter cable
<b>Integrated WLAN</b>	Intel Dual Band Wireless-AC8265	Intel Dual Band Wireless-AC8265	Intel Dual Band Wireless-AC8265	Intel Dual Band Wireless-AC8265
<b>BIOS features</b>	InsydeH20 Bios	InsydeH20 Bios	InsydeH20 Bios	InsydeH20 Bios
<b>Audio type</b>	On board	On board	On board	On board
<b>Audio codec</b>	Realtek ALC255	Realtek ALC255	Realtek ALC255	Realtek ALC255

## General system information

<b>Audio features</b>	2x digital array microphones, 2x built-in speakers (stereo)	2x digital array microphones, 2x built-in speakers (stereo)	2x digital array microphones, 2x built-in speakers (stereo)	2x digital array microphones, 2x built-in speakers (stereo)
<b>Display</b>				
<b>Display</b>	31.8 cm (12.5-inch),PLS (Plane to Line Switching),(Full HD),Anti-glare display,1,920 x 1,080 pixel,700:1,400 cd	31.8 cm (12.5-inch),PLS (Plane to Line Switching),(Full HD),Anti-glare display,1,920 x 1,080 pixel,700:1,400 cd	31.8 cm (12.5-inch),PLS (Plane to Line Switching),(Full HD),Anti-glare display,1,920 x 1,080 pixel,700:1,400 cd	31.8 cm (12.5-inch),PLS (Plane to Line Switching),(Full HD),Anti-glare display,1,920 x 1,080 pixel,700:1,400 cd
<b>Display notes</b>	ISO 9241-307 - Pixel class II Viewing angle: Left/Right 89°, Top 89°, Bottom 89°; 30ms response time; Integrated ambient light sensor for automatic backlight adjustment to the working environment.	ISO 9241-307 - Pixel class II Viewing angle: Left/Right 89°, Top 89°, Bottom 89°; 30ms response time; Integrated ambient light sensor for automatic backlight adjustment to the working environment.	ISO 9241-307 - Pixel class II Viewing angle: Left/Right 89°, Top 89°, Bottom 89°; 30ms response time; Integrated ambient light sensor for automatic backlight adjustment to the working environment.	ISO 9241-307 - Pixel class II Viewing angle: Left/Right 89°, Top 89°, Bottom 89°; 30ms response time; Integrated ambient light sensor for automatic backlight adjustment to the working environment.
<b>Sensors</b>	3-axis Accelerometer Gyroscope Ambient Light Sensor Magnetic Field Sensor Compass	3-axis Accelerometer Gyroscope Ambient Light Sensor Magnetic Field Sensor Compass	3-axis Accelerometer Gyroscope Ambient Light Sensor Magnetic Field Sensor Compass	3-axis Accelerometer Gyroscope Ambient Light Sensor Magnetic Field Sensor Compass
<b>Aspect ratio</b>	16:9	16:9	16:9	16:9
<b>Brightness - typical</b>	400 cd	400 cd	400 cd	400 cd
<b>Contrast - typical</b>	700:1	700:1	700:1	700:1
<b>Digitizer / Touch Technology</b>	TPK Touch Panel for active pen input plus capacitive 10-finger multi-touch screen	TPK Touch Panel for active pen input plus capacitive 10-finger multi-touch screen	TPK Touch Panel for active pen input plus capacitive 10-finger multi-touch screen	TPK Touch Panel for active pen input plus capacitive 10-finger multi-touch screen
<b>Ambient light sensor</b>	Integrated	Integrated	Integrated	Integrated
<b>Ambient light sensor notes</b>	While enabled, the ambient light sensor automatically adjusts the display backlight	While enabled, the ambient light sensor automatically adjusts the display backlight	While enabled, the ambient light sensor automatically adjusts the display backlight	While enabled, the ambient light sensor automatically adjusts the display backlight
<b>Viewing angle (h/v) - typical</b>	178°/178°	178°/178°	178°/178°	178°/178°

## Graphics

<b>TFT resolution (HDMI)</b>	up to 4,096 × 2,160	up to 4,096 × 2,160
<b>TFT resolution (VGA)</b>	1,920 x 1,080 pixel	1,920 x 1,200 pixel
<b>Max. resolution external display</b>	4,096 x 2,304 pixel	4,096 x 2,304 pixel
<b>Max. resolution display port</b>	4,096 x 2,304 pixel	4,096 x 2,304 pixel
<b>Graphics brand name</b>	Intel® HD Graphics 620	Intel® HD Graphics 620
<b>Graphics features</b>	3 Display Support (2 external, 1 internal)	3 Display Support (2 external, 1 internal)
<b>Graphics notes</b>	Shared memory depending on main memory size and operating system	Shared memory depending on main memory size and operating system

## Interfaces

<b>DC-in</b>	1
<b>Audio: line-out / headphone</b>	1 (combo port with Audio line-in)
<b>Audio: line-in / microphone</b>	1 (combo port with Audio line-out)
<b>Internal microphones</b>	2 (digital)
<b>USB 3.1 Gen1 (USB 3.0) total</b>	1 (Anytime USB-charge)
<b>VGA</b>	1 (via optional cradle or optional conversion cable)
<b>mini DisplayPort</b>	1
<b>HDMI</b>	1 (via optional cradle or optional DP conversion cable)
<b>Ethernet (RJ-45)</b>	1 (via optional cradle or optional conversion cable)
<b>Memory card slots</b>	1 microSD up to 2GB microSDHC up to 32GB microSDXC up to 128GB Speed Class: up to UHS-I

**Interfaces**

<b>SIM card slot</b>	1 (MicroSIM - only for models with integrated 4G/LTE)
<b>Interface Module notes</b>	VGA and HDMI via conversion cables (mini DP to VGA and mini DP to HDMI), Ethernet via conversion cable (USB to RJ-45)

**Wireless technologies**

<b>Antennas</b>	2x dual band for WLAN, 2x for 4G/LTE, Bluetooth shared with WLAN, 1 x NFC
<b>Bluetooth</b>	Bluetooth 4.2 LE
<b>Integrated WLAN</b>	Intel Dual Band Wireless-AC8265
<b>WLAN encryption</b>	WEP, WPA, WPA2
<b>WLAN notes</b>	Import and usage according to country-specific regulations.
<b>Integrated LTE or UMTS</b>	LTE Sierra Wireless EM7305 (Cat. 3) (optional)
<b>LTE/UMTS/GPS notes</b>	Including GPS functionality Import and usage according to country-specific regulations.
<b>NFC</b>	optional
<b>GPS</b>	Embedded in 3G/4G module if configured with WWAN

**Power supply**

<b>AC adapter</b>	19 V / 65 W (3.42 A)
<b>Rated voltage range</b>	100 V - 240 V (AC Input)
<b>Rated frequency range</b>	50 Hz - 60 Hz
<b>1st battery</b>	Lithium polymer battery 4-cell, 34 Wh
<b>Runtime 1st battery</b>	up to 10h slate only and 9h incl. keyboard (Productivity Workload MobileMark® 2014)
<b>Battery charging time</b>	~ 3h
<b>Battery notes</b>	Battery runtime information is based on worldwide acknowledged BAPCo® MobileMark® 2014 (office productivity). Refer to <a href="http://www.bapco.com">www.bapco.com</a> for additional details. The BAPCo® MobileMark® Benchmark provides results that enable direct product comparisons between manufacturers. It does not guarantee any specific battery runtime which actually can be lower and may vary depending on product model, configuration, application and power management settings. The battery capacity decreases slightly with every re-charge and over its lifetime.

**Dimensions / Weight / Environmental**

<b>Dimensions (W x D x H)</b>	319 x 9.5 x 201 mm 12.55 x 0.37 x 7.91 inch
<b>Weight</b>	from 830 g slate only / 1170g incl. keyboard
<b>Weight (lbs)</b>	slate only from 1,83 lbs / incl. keyboard 2,58 lbs
<b>Weight notes</b>	Weight may vary depending on actual configuration (including battery pack)
<b>Operating ambient temperature</b>	Running: 5 - 35 °C; Packed -15 - 60 °C
<b>Operating relative humidity</b>	Running: 20 - 85%; Packed 8 - 85% (relative humidity, non-condensing)
<b>Product</b>	STYLISTIC R727
<b>Germany</b>	GS (planned)
<b>Europe</b>	CE! EN 60950
<b>Global</b>	ENERGY STAR® 6.1 EPEAT® Gold (dedicated regions) (planned) RoHS (Restriction of hazardous substances) WEEE (Waste electrical and electronic equipment) IT-Eco-Declaration Microsoft Operating Systems (HCT / HCL entry / WHQL)
<b>Compliance link</b>	<a href="https://sp.ts.fujitsu.com/sites/certificates">https://sp.ts.fujitsu.com/sites/certificates</a>

**Additional Software**

<b>Additional software (preinstalled)</b>	Waves MaxxAudio (audio enhancer) LTE / UMTS Connection Manager (if configured with 4G/LTE or 3G/UMTS) Fujitsu Plugfree Network (network management utility) Fujitsu Anytime USB Charge Utility Fujitsu Battery Utility Fujitsu Function Manager Fujitsu DeskUpdate (driver and utility tool) Microsoft Office (buy license to activate the pre-installed Microsoft Office) McAfee Internet Security and Antivirus Software (60 days trial version)
---	--

<b>Additional software (optional)</b>	Recovery DVD for Windows® Drivers & Utilities DVD (DUDVD) optional CyberLink PowerDVD BD (playback software for Blu-ray Disc™) CyberLink PowerDVD DVD (playback software for DVD) CyberLink YouCam (webcam software) Nero (backup and burning software)
---------------------------------------	--

**Manageability**

<b>Manageability technology</b>	PXE 2.1 Boot code Wake up from S5 (off mode) WoL (Wake on LAN)
---------------------------------	--

<b>Supported standards</b>	WMI PXE BootP (made4you)
----------------------------	--------------------------------

<b>Manageability link</b>	<a href="http://www.fujitsu.com/fts/manageability">http://www.fujitsu.com/fts/manageability</a>
---------------------------	---

**Security**

<b>System and BIOS Security</b>	Optional: Trusted Platform Module (TPM 2.0) EraseDisk (optional)	Optional: Trusted Platform Module (TPM 2.0) EraseDisk (optional)	Optional: Trusted Platform Module (TPM 2.0) EraseDisk (optional)	Optional: Trusted Platform Module (TPM 2.0) EraseDisk (optional)
<b>User Security</b>	Hard disk password User and supervisor BIOS password Workplace Protect (secure authentication solution)	Hard disk password User and supervisor BIOS password Workplace Protect (secure authentication solution)	Hard disk password User and supervisor BIOS password Workplace Protect (secure authentication solution)	Hard disk password User and supervisor BIOS password Workplace Protect (secure authentication solution)

**Warranty**

<b>Warranty period</b>	2 years (for countries within EMEA)
<b>Warranty type</b>	Collect & Return Service / Bring-in Service (depending on country)
<b>Warranty Terms &amp; Conditions</b>	<a href="http://support.ts.fujitsu.com/warranty">http://support.ts.fujitsu.com/warranty</a>

**Product Support Services - the perfect extension**






<b>Recommended Service</b>	9x5, Onsite Response Time: Next Business Day
<b>Spare Parts availability</b>	5 years after end of product life
<b>Service Weblink</b>	<a href="http://ts.fujitsu.com/Supportservice">http://ts.fujitsu.com/Supportservice</a>

## Recommended Accessories

**Cradle STYLISTIC R series**

The cradle for STYLISTIC R series allows you switch from mobile to desktop productivity mode in one click. Enjoy a complete desktop experience with a FUJITSU display, wireless mouse and keyboard or magnetic keyboard and work comfortably on spreadsheets or presentations. Available ports: HDMI, DisplayPort, VGA, 2x USB 3.0, LAN, Audio (1x in / 1x out), DC-In, Kensington lock support.

Order Code:  
S26391-F2167-L100

			Order Code: S26391-F6097-L363
<b>Sneaker Sleeve 14</b>		The Sneaker Sleeve 14 protects notebooks with up to 14-inch screens. The front half of the bag has dedicated compartments for your notebook, power cord, office supplies and personal items. The back half of the bag has an expanding, divided compartment for your files.	Order Code: S26391-F1194-L401
<b>Active Pen for STYLISTIC R726</b>		Annotate and fill in forms on your tablet with the premium, real size FUJITSU Active Pen. Navigate, erase and right-click with the function button. Includes a battery and a pen holder to attach to the keyboard or tablet.	Order Code: S26391-F2169-L100
<b>VGA Conversion Adapter ( Mini Display Port to VGA)</b>		Connect and present on demand from your STYLISTIC Tablet with the FUJITSU VGA Conversion Cable. From the mini Display Port on your Tablet to the VGA port on the projector or display. (Picture similar to product)	Order Code: S26391-F2169-L200
<b>HDMI Conversion Adapter (mini DP to HDMI)</b>		The FUJITSU HDMI Conversion Cable lets you connect your STYLISTIC tablet to projectors and screens that have a modern HDMI interface. (Picture similar to product)	Order Code: S26391-F2169-L300
<b>LAN Conversion Cable (USB to LAN)</b>		The FUJITSU LAN Conversion Cable allows you to connect your STYLISTIC tablet to a wired network connection. (Picture similar to product)	Order Code: S26391-F2169-L400

# More information

## Fujitsu OPTIMIZATION Services

In addition to FUJITSU Tablet STYLISTIC R727, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

### Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

### Computing Products

[www.fujitsu.com/global/products/computing/](http://www.fujitsu.com/global/products/computing/)

### Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about FUJITSU Tablet STYLISTIC R727, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.  
[www.fujitsu.com/fts/tabletpc](http://www.fujitsu.com/fts/tabletpc)

## Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment/>



## Copyrights

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

© 2017 Fujitsu Technology Solutions GmbH

## Disclaimer

Technical data are subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

## CONTACT

Fujitsu Technology Solutions GmbH  
Website: [www.fujitsu.com/fts](http://www.fujitsu.com/fts)  
2017-05-01 CE-EN

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)  
© 2017 Fujitsu Technology Solutions GmbH