



BT-870-TP

BT-870-TP Dual Connectivity Keyboard

The BT-870-TP keyboard by iKey is our new dual connectivity keyboard. Connect with USB or Bluetooth®. This keyboard has a built-in touchpad and is made of industrial silicone rubber.

This fully-sealed keyboard is designed to meet IP67 and NEMA 4X specifications, meaning it is resistant to dirt, dust, water, ice and corrosives. Built with an industrial silicone rubber keypad and a rugged ABS polycarbonate case, the BT-870-TP is easy to clean with disinfectants. The compact design and internal Bluetooth® module make the BT-870-TP highly portable. In addition, its red LED backlighting is ideal for nighttime or ambient-light use.

- A MicroUSB cable is included to recharge the keyboard and turn it into a wired USB keyboard when necessary.
- Includes 75mm VESA and 1.188" x 1.5" AMPS mounting patterns

BT-870-TP is an ideal fit for mobile, material handling, food and beverage processing, medical, and other environments where rugged flexibility and/or wireless connection is a necessity. It is rated IP67. This wireless keyboard is ideal for hospitals and other medical settings and can be considered a “health care configuration” model. The BT-870-TP is available for immediate order. See more at ZDNet.com: www.zdnet.com/article/ikey-ships-samsung-dex-centralized-law-enforcement-mobile-solution/

Other models: BT-870-TP-SLIM for slim thin profile(SLIM®)

Product Code BT-870-TP

Product Code	BT-870-TP
Certifications	IP67
Shock	3 x 11 ms pulses of 50g on each of 3 axis



Key Switch	MATERIAL: Industrial Silicone Rubber LIFE: Greater than 10 Million Cycles Travel: 0.055in. ACTUATION FORCE: 7.03oz +/-1.06oz (200g +/- 30g) FEEDBACK: Tactile with Mechanical Snap
Vibration	POWER SPECTRAL DENSITY .04G/HZ FREQUENCY RANGE: 20Hz-2Khz DURATION OF TEST PER AXIS: 3 hours
Power	Rechargeable Lithium Ion Battery
Temperature Range	STORAGE: -40°;F TO +149°;F (-40°;C to +65°;C). OPERATING: 32°;F to +140°;F (0°;C to +60°;C)
Weight	2.0 lbs +/- 0.010 lbs (0.91 kg +/-0.05 kg)
Warranty	One Year
Humidity	100% Humidity Resistant
Tapped Screw Inserts	8-32 x 1/4"
Dimensions	12.01" x 7.75" x 2.03" (w-h-d)
Model Numbers	BT-870-TP and BT-870-SLIM