

GCS72MDPKIT

2-Port USB VGA Cable KVM with Mini DisplayPort Adapters




2-Port Cable VGA / Mini DisplayPort KVM Switch


- Switch between two computers with the push of a button
 - Offers the flexibility to mix and match computer connections: VGA and Mini DisplayPort
 - Includes 2 x Mini DisplayPort to VGA adapters
 - No external power needed
 - Cost effective, Plug-N-Play solution
-
- Switch between two computers with the push of a button
 - Offers the flexibility to mix and match computer connections: VGA and Mini DisplayPort
 - Includes 2 x Mini DisplayPort to VGA adapters
 - No external power needed
 - Cost effective, Plug-N-Play solution
 - One USB keyboard, USB mouse, and VGA monitor control two computers
 - Max resolution: 2048 x 1536, DDC2B
 - 2.1 Stereo audio and microphone support
 - 3' long molded-in cables to simplify setup
 - Compatible with PC, MAC and SUN operating platforms
 - Supports Windows XP or higher, Mac OS 9.0 or higher, Sun Solaris 9 or higher
 - Full Mac keyboard support
-
- Supports programmable mice
 - 2 x Mini DisplayPort to VGA Adapters convert your Mini DisplayPort to VGA:
 - Works with Apple® iMac® or MacBook®
 - Compliant with Mini DisplayPort Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
 - Support full Mini DisplayPort link tracking
 - Supported resolutions:
 - Full HD 1080p
 - 1920x1200
 - VGA, SVGA, XGA, SXGA and UXGA at 162 MHz pixel rate
 - Support interrupt request output for expansion function
 - Support Deep Sleep Mode (suspend mode)



Solution 1



Solution 2



Requirements

Package Contents

- | | |
|--|--|
| <ul style="list-style-type: none"> • Console: • 1 x VGA display • 1 x standard 104 key wired USB keyboard • 1 x standard 2 or 3 button wired USB mouse • • Computers: • VGA or Mini DisplayPort port • USB ports • 3.5mm audio port (optional) • • Operating Systems: • Windows Vista®, Windows® 7, Windows® 8.1, Windows® 10 • Mac OS 9 to 10.x • Oracle® Solaris • Linux®, Unix and other USB supported systems* | <ul style="list-style-type: none"> • 1 x 2-Port USB Cable KVM • 2 x Mini DisplayPort to VGA Adapters • 1 x Quick Start Guide • 1 x Warranty Card |
|--|--|

*Additional drivers and support may be needed

Specifications

Function	GCS72MDPKIT	Dimensions	GCS72MDPKIT
Computer Connections		POP Information	
Direct	2	10" Peg Hook	4
Console Connectors		6" Peg Hook	2
Monitor	VGA	Unit Dimensions	
Keyboard	USB	Height	6" (15.24cm)
Mouse	USB	Depth	7" (17.78cm)
CPU Connectors		Length	2" (5.08cm)
Monitor	2 x VGA; 2 x Mini DisplayPort (with adapters)	Unit Package Dimensions	
Keyboard & Mouse	2 x USB	Width	6.25" (15.87cm)
LEDs		Height	8.87" (22.54cm)
On Line	Green	Depth	2.25" (5.72cm)
Video Resolution	2048x1536 (VGA), 1920x1200 (with adapters)	Master Carton	
Port Selection	Remote Pushbutton	Width	8" (20.32cm)
Cable Type	Bonded USB KVM	Height	7" (17.78cm)
Cable Length	2 x 3ft each	Depth	15.25" (38.74cm)
Housing		Master Carton Qty.	6
Case	Plastic	Weight	
		Master Carton Wt.	7.52lb (3.42kg)
		Unit Pack Wt.	1.14lb (0.52kg)
		Unit Wt. w/accessories	0.92lb (0.42kg)
		Unit Wt.	0.82lb (0.37kg)