

**AOC Monitors
USB Powered
Portable Monitor**

USB Series
15.6", 1920 x 1080 Full HD

I1659FWUX



16" Class USB powered Full HD monitor, sleek design and fast USB 3.0 connection

The I1659FWUX USB powered portable LED backlit monitor is a must-have laptop or desktop accessory. The widescreen monitor receives both power and signal via a single USB 3.0 cable for plug-and-play connection; it does not require a power cord or VGA cable, and comes with a foldable flexi-stand for maximum flexibility.

Key Features:

- 15.6" 1920x1080 Full HD Resolution
- IPS Display for wide viewing angles and truer colors
- Ultra-slim and lightweight with stylish piano-black glossy design
- Auto-pivot feature for viewing in landscape or portrait mode according to display's orientation
- Perfect accessory for the frequent traveler or on-the-go presentation
- USB 3.0 Technology for USB-powered for plug-and-play connection
- USB 3.0 achieves high transfer rates and delivers high-quality images
- Foldable flexi-stand for landscape and portrait mode
- Built-in Display Link technology for multiple USB monitors connection

Sleek Design, Fast Connections

The new and improved USB monitor from AOC is sleeker in design and faster with its USB 3.0 connection. The new USB 3.0 achieves high transfer rates with its total of six wires in the data cable, and delivers high quality images.



Designed with a piano-black glossy finish, this USB monitor has a 15.6" diagonally viewable image. The I1659FWUX offers a 700:1 contrast ratio, 11 ms response time, and a beautiful 1920x1080 Full HD resolution at 60Hz.



The I1659FWUX USB Monitor has a foldable flexi-stand for viewing in landscape or portrait mode. Landscape mode is ideal for presentations and Excel sheets, while the Portrait mode conveniently gives you an easy vertical view of your instant messaging program, or sidebars such as search results. This monitor has the unique auto-pivot feature that automatically adjusts the image according to the display's orientation, so you will never have to change settings as you switch between landscape and portrait mode.

Ultra Lightweight and Slim Portability at Its Best

It's ultra-lightweight and slim for great portability, making it perfect for business presentations, the frequent traveler, photo frame applications, and dual monitor setups on-the-go. The I1659FWUX USB Monitor is the solution for the frequent traveler who needs to pack multiple displays, as it easily fits into a backpack or the carry case that comes with the USB monitor.

The I1659FWUX USB Monitor now comes with VESA 75x75 mm Mount Compliant feature, allowing you to easily mount the USB monitor to any wall as long as you have the right wall mount arm and bracket.



Built-in DisplayLink Technology for multiple USB monitors connection

If necessary, multiple USB monitors can be simultaneously connected to a single laptop to function as a multi-monitor PC or Mac, thanks to the built-in DisplayLink USB graphics. Simply installing DisplayLink software on the PC or Mac allows you to easily add multiple USB monitors for external displays without unnecessary extra hardware. The I1659FWUX USB Monitor gives you multiple external displays for your laptop without any complications.

I1659FWUX Specification

Cabinet Color	Piano-Black Glossy
Panel	TFT Active Matrix LCD 15.6" Class Widescreen, 16:9 Aspect Ratio 15.6" Viewable Image Size, Diagonal
Pixel Pitch	0.18 (H) mm x 0.18 (v) mm
Display Area	344.16 mm x 193.59 mm
Brightness	220 cd/m2 (typ)
Contrast Ratio	700:1 (static)
Response Time	25ms (gtg)
Viewing Angle	Horizontal: 160 Degrees (CR>10) Vertical: 160 Degrees (CR>10)
Scanning Frequency	Horizontal: 67.5KHz Vertical: 60Hz
Optimal Resolution Recommended	1920x1080@60Hz 1920x1080@60Hz
Supported Resolutions	(All in extended mode) 640x480@60Hz, 800x600@60Hz, 1024x768@60Hz, 1366x768@60Hz, 1920x1080@60Hz
Color Depth	262K colors
Input Signal	1 x USB 3.0
User Control	NA
Adjustability	Tilt: 15°~30°
Power Source	PC USB 5V
Power Consumption	8W (typical), Standby: .5W
Regulations	cTUVus, CE, FCC, RoHS, EPEAT, Energy Star®, Windows 8/10 compatible
Other Features	Ultra Slim, Foldable Flexi-Stand, Low Power Consumption, Smart UI to adjust USB monitor via PC software, Better Picture Quality via USB 3.0 technology, VESA 75x75mm Wall Mount Compliant ¹
Dimensions (WxHxD mm)	Monitor w/ base: 232.7 x 371.9 x 35.5 Carton: 442 x 295 x 85
Dimensions (WxHxD inches)	Monitor w/ base: 9.16 x 14.64 x 1.40 Carton: 17.4 x 11.61 x 3.35
Weight (Net)	2.64 lbs (1.2 kgs) Net
Weight (Gross)	3.88 lbs (1.76 kgs) Gross
Loading Qty w/pallet	20' = 2352 pcs. 40' Std = 4704 pcs.
UPC Code	685417713981
What's in the Box	15.6" Monitor, USB 3.0 Cable, Carry Case, QSG

1. Wall mount arm & bracket not included. Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. AOC shall not be liable for technical or editorial errors or omissions contained herein. All other trademarks are property of their respective owners. For more information, visit us.aoc.com or call 888-838-6388